

PRODUCT SPECIFICATION

Printed: 2/10/2014

Page 1 of 1

Catalog : PO138

Polysorbate 80, NF

CAS# : 9005-65-6

Test	Limit	
	Min.	Max.
COMPOSITION OF FATTY ACIDS	TO PASS TEST	
HYDROXYL VALUE	65 - 80	
SAPONIFICATION VALUE	45 - 55	
SPECIFIC GRAVITY @ 25°C	1.06 - 1.09	
VISCOSITY @ 25°C	300 - 500 cs	
ACID VALUE	--	2.0
DIOXANE	--	10 ppm
ETHYLENE OXIDE	--	1 ppm
HEAVY METALS	--	10 ppm
PEROXIDE VALUE	--	10
RESIDUE ON IGNITION	--	0.25 %
WATER	--	3.0 %
IDENTIFICATION	TO PASS TEST	
CERTIFIED KOSHER		
RETEST DATE		
RESIDUAL SOLVENTS	TO PASS TEST	