

PRODUCT SPECIFICATION

Printed: 2/10/2014

Page 1 of 1

Catalog : P1315

Potassium Hydroxide, Pellets, Reagent, ACS

CAS# : 1310-58-3

Formula : KOH

Formula Weight : 56.11

Test	Limit	
	Min.	Max.
ASSAY (KOH)	85 %	--
POTASSIUM CARBONATE (K ₂ CO ₃)	--	2.0 %
CHLORIDE (Cl)	--	0.01 %
NITROGEN COMPOUNDS (as N)	--	0.001 %
PHOSPHATE (PO ₄)	--	5 PPM
SULFATE	--	0.003 %
HEAVY METALS (as Ag)	--	0.001 %
IRON (Fe)	--	0.001 %
NICKEL (Ni)	--	0.001 %
CALCIUM (Ca)	--	0.005 %
MAGNESIUM (Mg)	--	0.002 %
SODIUM (Na)	--	0.05 %
IDENTIFICATION	TO PASS TEST	
RETEST DATE		