

BuildPro™ Models

All TM series tables have 5/8 thick plate, Ø5/8 holes in a 2" grid pattern and slot of 1.7".



6-1/2' L Table

	Part No.	Table Height	Tabletop Dimension	Plate Thickness	Hole Diameter	Slot Width	Table Capacity (LBS.)	Table Weight (LBS.)
STANDARD	TMA57838	36"	78" x 38" (6-1/2' x 3')	5/8"	Ø5/8	1.7"	4,400	680
	TMB57838	30"						672
	TMC57838	24"						661
NITRIDED	TMA57846	36"	78" x 46" (6-1/2' x 4')	5/8"	Ø5/8	1.7"	4,400	764
	TMQA57838	36"						680
	TMQB57838	30"						672
	TMQC57838	24"						661
	TMQA57846	36"	78" x 46" (6-1/2' x 4')	5/8"	Ø5/8	1.7"	4,400	764



4' L Table

	Part No.	Table Height	Tabletop Dimension	Plate Thickness	Hole Diameter	Slot Width	Table Capacity (LBS.)	Table Weight (LBS.)
STANDARD	TMA54738	36"	47" x 38" (4' x 3')	5/8"	Ø5/8	1.7"	2,600	420
	TMB54738	30"						415
	TMC54738	24"						408
NITRIDED	TMA54746	36"	47" x 46" (4' x 4')	5/8"	Ø5/8	1.7"	2,600	471
	TMQA54738	36"						420
	TMQB54738	30"						415
	TMQC54738	24"						408
	TMQA54746	36"	47" x 46" (4' x 4')	5/8"	Ø5/8	1.7"	2,600	471

New Models

Not enough space for a full Welding Table? We developed the Half Table just for you!

Same robust BuildPro™ frame, with half the plates of the 4' table (3 plates) for a space-saving, heavy duty work platform that suits your work space. It is especially suited for robot weld stations for small parts. The compact and light tops make shuttle table mounting easier. Place the Half Table in a fixed location, or on a heavy duty rolling cart for mobility around the shop.



3' L Half Table

	Part No.	Table Height	Tabletop Dimension	Plate Thickness	Hole Diameter	Slot Width	Table Capacity (LBS.)	Table Weight (LBS.)
STANDARD	TMA52238	36"	38" x 22"	5/8"	Ø5/8	1.7"	1,300	253
	TMB52238	30"						248
NITRIDED	TMQA52238	36"	38" x 22"	5/8"	Ø5/8	1.7"	1,300	253
	TMQB52238	30"						248



4' L Aluminum Table

	Part No.	Table Height	Tabletop Dimension	Plate Thickness	Hole Diameter	Slot Width	Table Capacity (LBS.)	Table Weight (LBS.)
ALUMINUM	TMA74738	36"	47" x 38" (4' x 3')	5/8"	Ø5/8	1.7"	4,400	265
	TMB74738	30"						260
	TMA77838	36"	78" x 38" (6-1/2' x 3')	5/8"	Ø5/8	1.7"	4,400	422
	TMB77838	30"						414