

ICECUT 250™ AND ICECUT 250P™

NEW

Power and versatility, now available
in a more compact size



 **WALTER**
Surface Technologies
Only the best.™

Icecut 250™

Order no. 39-D 250

Lightweight, powerful with variable speed

The powerful, intuitive and lightweight ICECUT 250™ is a truly versatile machine, especially for its size.



Icecut 250P™

Order no. 39-D 251

Drill faster and easier on pipe-related jobs

The double magnet ICECUT 250P™ sets up fast for pipe applications and is curved surface-ready.



Aerospace



Agriculture



Construction



Energy



Field maintenance



Food and beverage



Military



Naval



Manufacturing



Pharmaceutical



Transportation



Underground transportation

Order No.	39-D 250	39-D 251
Watts	1550	1500
Speed	2-speeds + Reversible	2-speeds + Reversible
Dynamax variable speed control	YES	YES
No load RPM	100-500 RPM	100-500 RPM
Rated Current	15 amps	15 amps
Core cutter capacity (diameter)	2 3/4"	2 3/4"
Core cutter capacity (depth)	3" (w/ 2-piece pilot pin)	3" (w/ 2-piece pilot pin)
Twist drill capacity (diameter)	1/2"	1/2"
Tapping function	YES, up to 3/4" - 16	YES, up to 3/4" - 16
Weight	34.1 lbs	39.6 lbs
Swivel and sliding magnet	NO	NO
Max drill point pressure	3035 lbs (1376 kg)	3035 lbs (1376 kg)
Reversible handle	YES, TOOL-FREE press button	YES, TOOL-FREE press button
Powerguard motor overload protection	20A	20A
Powerguard electronic overload protection	27A	27A
Short-Circuit protection	YES, Integrated Fuse	YES, Integrated Fuse
Accudrill LED torque display	YES, Intergrated Ampmeter	YES, Intergrated Ampmeter
Magnetic field sensor Material & thickness detector	NO	(Permanent Magnet)
Tool free guard	Metal, sliding	Metal, sliding
Wiring	Internal	Internal
Lubrication	Internal thru feed, on motor head	Internal thru feed, on motor head
Control board	Centered, S/S switches with LEDs	Centered, S/S switches with LEDs
Handle	1 reversible on main housing,	1 pistol grip 1 reversible on main housing, 1 pistol grip
Arbor	Morse Taper 2 shank; 3/4" Weldon	Morse Taper 2 shank; 3/4" Weldon
Maintenance	Easy access to carbon brushes	Easy access to carbon brushes
Total Stroke	5.5"	5.5"

FOR MORE INFORMATION, TO SCHEDULE A FREE DEMO OR TO ORDER:

United States:

Phone: (800) 522-0321 | Fax (866) 274-4435

Email: OrderDesk.US@walter.com

Canada:

Phone: (888) 592-5837 | Fax (866) 581-1121

Email: csr@walter.com

Available at :



Only the best.™

Walter Surface Technologies Inc. © 2019 All Rights Reserved. Walter Surface Technologies and Bio-Circle logos are trademarks or registered trademarks of Walter Surface Technologies Inc. Other company, product or service names may be trademarks or service marks of Walter Surface Technologies or others. 98-D 253 (01-19)