

# World Amenities

## bodyography® blanc Safety Data Sheet

SDS No.: SHG2019011501  
Issue Date: May 5th, 2019  
Version No.: 1.0

According to Regulation (EC) No. 1907/2006(REACH) with its amendment Commission Regulation (EU) 2018/830.

### Section 1 Identification of the substance/mixture and of the company/undertaking

#### 1.1 Product identifier:

Identification on the label/Trade Name: Body Wash

Additional identification: Not available

#### 1.2 Relevant identified uses of the substance and uses advised against:

Relevant Identified uses: Clean hands, skin or face

Uses advised against: Not Applicable

#### 1.3 Details of the supplier of the safety data sheet:

Supplier: World Amenities

Address: 8260 Camino Santa Fe, Suite A, San Diego, CA 92121

Telephone:

Fax: 619-276-7661

Email:

1.4 Emergency telephone Number: 619-276-7660

Association/Organization:

Emergency Tel No.:

### Section 2 Hazards Identification

#### 2.1 Classification of the substance/mixture:

Not classified as Hazardous according to Regulation (EC) No. 1272/2008 and their amendments.

Not classified as dangerous Good for transport purposes.

#### 2.2 Label elements:

Hazard Pictograms: Not Applicable

Signal Words: Not Applicable

Hazard Statements: Not Applicable

Supplementary statement: Not Applicable

Precautionary statements Prevention: Not Applicable

Precautionary statements Response: Not Applicable

Precautionary statements Storage: Not Applicable

Precautionary statements Disposal: Not Applicable

#### 2.3 Other hazards:

REACH - Art. 57 - 59: The mixture does not contain Substances of Very High Concern (SVHC) at the SDS print date.

### Section 3 Composition/information on ingredients

Product Name: Soap  
Version #: 1.0

Revision date: N/A

MSDS EU  
1 / 8

**3.1 Substance/Mixture:**

See "Composition on ingredients" in Section 3.2

**3.2 Mixtures of Ingredient(s):**

INCI Name	%	CAS No.	EC No.	Index No.	REACH No.	Classification according to Regulation (EC) No. 1272/2008(CLP)
Sodium Palmate	< 75.00	61790-79-2	263-162-3	N/A	N/A	Not Classified
Sodium Palm Kernelate	< 20.00	61789-89-7	263-097-0	N/A	N/A	Not Classified
Aqua (Water)	< 15.00	7732-18-5	231-791-2	N/A	N/A	Not Classified
Parfum (Fragrance)	1.20	N/A	N/A	N/A	N/A	No Components in the fragrance trigger the classification of this mixture
Glycerin	< 1.00	56-81-5	200-289-5	N/A	N/A	Not Classified
Sodium Chloride	< 1.00	7647-14-5	231-598-3	N/A	N/A	Not Classified
Citric Acid	< 1.00	5949-29-1	201-069-1	N/A	N/A	Eye Irritation Category2; H319
Tetrasodium EDTA	< 0.20	64-02-8	200-573-9	N/A	N/A	Acute Toxicity (Oral) Category 4, Eye Irritation Category 2; H302, H319

Allergen List: Limonene, Butylphenyl Methylpropional, Linalool

**Section 4 First aid measures****4.1 Description of first aid measures:**

<b>Inhalation:</b>	If fumes, aerosols or combustion products are inhaled , removed from contaminated area. Other measures are usually unnecessary
<b>Skin contact:</b>	If skin or hair contact occurs, flush skin and hair with running water(and soap if available). Seek medical attention in event of irritation
<b>Eyes contact:</b>	If this product comes in contact with eyes, wash out immediately with water. If irritation continues, seek medical attention. Removal of contact lenses after eye injury should only be undertaken by skilled personnel
<b>Ingestion:</b>	Immediately give a glass of water. First aid is not generally required. If in doubt, contact a poisons information centre or a doctor

**4.2 Most important symptoms and effects, both acute and delayed:**

See Section 11

**4.3 Indication of any immediate medical attention and special treatment needed:**

Treat symptomatically

**Section 5 Fire-Fighting measures****5.1 Extinguishing media:****Suitable extinguishing media:** Dry chemical, CO<sub>2</sub>, water spray or alcohol-resistant foam.**Unsuitable extinguishing media:** Not available.**5.2 Special hazards arising from the substance or mixture**

Avoid contamination with oxidising agents i.e. nitrates, oxidising acids, chlorine bleaches, pool chlorine etc as ignition may result.

**5.3 Advice for fire-fighters:**

Fire-fighters: Alert fire brigade and tell them location and nature of hazard. Wear breathing apparatus plus protective gloves.

Fire/Explosion Hazard: Combustion products include: carbon monoxide(CO), carbon dioxide(CO<sub>2</sub>), other pyrolysis products typical of burning organic material.**Section 6 Accidental release measures**

## 6.1 Personal precautions, protective equipment and emergency procedures:

See Section 8

## 6.2 Environmental Precautions:

See Section 12

## 6.3 Methods and material for Containment and Cleaning up:

Minor spills: Clean up all spills immediately. Avoid contact with skin and eyes.  
Major spills: Clear area of personnel and move upwind. Alert fire brigade and tell them location and nature of hazard.

## 6.4 Reference to other sections:

See Section 8 for information on personal protection equipment.

## 6.5 Additional information:

Not applicable.

## Section 7 Handling and storage

### 7.1 Precautions for safe handling:

#### 7.11 Safe Handling:

Limit all unnecessary personal contact. Wear protective clothing when risk of exposure occurs.

#### 7.12 Fire and explosion protection:

See Section 5.

#### 7.13 Other information:

Store in original containers. Keep containers securely sealed.

### 7.2 Conditions for safe storage, including any incompatibilities

#### 7.21 Suitable container:

paper box, sachet, pleat wrapped

#### 7.22 Storage Incompatibility:

Avoid reaction with oxidising agents

### 7.3 Specific end uses

See Section 1.2

## Section 8 Exposure Controls/Personal Protection

### 8.1 Control parameters:

#### DERIVED NO EFFECT LEVEL(DNEL):

Not Available

#### PREDICTED NO EFFECT LEVEL(PNEC):

Not Available

#### OCCUPATIONAL EXPOSURE LIMITS(OEL):

Not Available

#### INGREDIENT DATA

Source	Ingredient	Material Name	TWA	STEL	PEAK	NOTES
Workplace Exposure Limits(WELs)	Glycerin	Glycerol,mist	10mg/m3	Not Available	Not Available	Not Available

### 8.2 Exposure controls:

#### 8.2.1 Appropriate engineering controls:

Engineering controls are used to remove a hazard or place a barrier between the worker and the hazard. Well-designed engineering controls can be highly effective in protecting workers and will typically be independent of worker interactions to provide this level of protection.

#### 8.2.2 Individual protection measures, such as personal protective equipment:



**Eye/face protection:**

Safety glasses with side shields; chemical goggles. Contact lenses may pose as special hazard; soft contact lenses may absorb and concentrate irritants.

**Hands/feet protection:**

The selection of suitable gloves does not only depend on the material, but also on further marks of quality which vary from manufacturer to manufacturer.

Where the chemical is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

Experience indicates that the following polymers are suitable as glove materials for protection against undissolved, dry solids, where abrasive particles are not present.

**Body protection:**

See other protection below

**Other protection:**

No special equipment needed when handling small quantities.

Otherwise, overalls.

**Respiratory protection:**

Respirators may be necessary when engineering and administrative controls do not adequately prevent exposures.

**8.2.3 Environmental exposure controls:**

See Section 12.

## Section 9 Physical and chemical properties

### 9.1 Information on basic physical and chemical properties:

<b>Appearance:</b>	Solid
<b>Physical state:</b>	Solid
<b>Odour:</b>	Pleasant small
<b>Odour threshold:</b>	Not available
<b>PH(20°C):</b>	10.0 -10.9
<b>Melting point/range (°C):</b>	Not available
<b>Freezing point/range (°C):</b>	Not available
<b>Boiling point/range (°C):</b>	Not available
<b>Flash point (°C):</b>	Not available
<b>Evaporation rate:</b>	Not available
<b>Flammability:</b>	Not flammable
<b>Upper/lower/explosive limits:</b>	Not available
<b>Vapour pressure (kPa):</b>	Not available
<b>Vapour density(Air=1):</b>	Not available
<b>Water solubility (g/l):</b>	Soluble
<b>Relative Density(Water=1):</b>	Not available
<b>Partition coefficient n-octanol/water:</b>	Not available
<b>Auto-ignition temperature:</b>	Not available
<b>Decomposition temperature:</b>	Not available
<b>Viscosity (cSt):</b>	Not available
<b>Explosive properties:</b>	Not available
<b>Molecular Weight(g/mol):</b>	Not available
<b>Taste:</b>	Not available
<b>Explosive properties:</b>	Not available
<b>Oxidising properties:</b>	Not available

Surface Tension(Dyn/cm or mN/m):	Not available
Volatile Component(% vol):	Not available
Gas group:	Not available
PH as a solution(1%):	Not available
VOC g/L:	Not available

## 9.2. Other information:

Not available

## Section 10 Stability and reactivity

10.1 Reactivity:	See section 7.2
10.2 Chemical stability:	Product is considered stable and hazardous polymerisation will not occur.
10.3 Possibility of hazardous reactions:	See section 7.2
10.4 Conditions to avoid:	See section 7.2
10.5 Incompatible materials:	See section 7.2
10.6 Hazardous decomposition products:	See section 5.3

## Section 11 Toxicological information

### 11.1 Information on toxicological effects

#### Acute toxicity:

#### Glycerin (CAS No.: 56-81-5):

LD50(Oral, guinea pig):	7750 mg/kg [2]
LD50(Oral, mouse):	4090 mg/kg [2]
LC50(Oral, rat):	1200 mg/kg [2]

#### Sodium Chloride (CAS No.: 7647-14-5):

LC50(Oral, rat):	3000 mg/kg [2]
------------------	----------------

#### Citric Acid (CAS No.: 5949-29-1):

LD50(Oral, mouse):	5790 mg/kg [2]
LC50(Dermal, rat):	> 2000 mg/kg [1]

#### Tetrasodium Etidronate (CAS No.: 3794-83-0):

LC50(Oral, rat):	1340 mg/kg [2]
------------------	----------------

Skin corrosion/Irritation:	No skin irritation.
Serious eye damage/irritation:	No serious eye irritation.
Respiratory or skin sensitization:	No data available.
Germ cell mutagenicity:	No data available.
Carcinogenicity:	Not classified
Reproductive toxicity:	Not classified
STOT- single exposure:	No data available.
STOT-repeated exposure:	No data available.

**Legend:** 1. Value obtained from Europe ECHA Registered Substance – Acute toxicity. 2. Value obtained from the SDS from raw material suppliers. Unless otherwise specified data extracted from RTECS – Register of Toxic Effect of chemical Substance.

## Section 12 Ecological information

### 12.1 Toxicity:

Soap: No data available for the mixture.

### 12.2 Persistence and degradability:

Ingredient	Persistence: Water/Soil	Persistence: Air
------------	-------------------------	------------------

Water	Low	Low
Glycerin	Low	Low
Sodium Chloride	Low	Low

### 12.3 Bioaccumulative potential

Ingredient	Bioaccumulation
Water	Low(LogKOW)= - 1.38
Glycerin	Low(LogKOW)= - 1.76
Sodium Chloride	Low(LogKOW)= - 0.4608

### 12.4 Mobility in soil

Ingredient	Bioaccumulation
Water	Low(KOC=14.3)
Glycerin	High(KOC=1.0)
Sodium Chloride	Low(KOC=14.3)

### 12.5 Results of PBT and vPvB assessment

	P	B	T
Relevant available data	Not Applicable	Not Applicable	Not Applicable
PBT Criteria fulfilled	Not Applicable	Not Applicable	Not Applicable

### 12.6 Other adverse effects

No data available

## Section 13 Disposal considerations

### 13.1 Waste treatment methods:

**Product/Packing disposal:** **DON NOT** allow wash water from cleaning or process equipment to enter drains. It may be necessary to collect all wash water for treatment before disposal.

**Waste treatment options:** Not Available

**Sewage disposal options:** Not Available

## Section 14 Transport information

### Label Required

**Marine Pollutant:** No

**HAZCHEM:** Not Applicable

### Land transport(ADR): NOT REGULATED FOR TRANSPORT OF DANGEROUS GOODS

14.1. UN Number: Not Applicable

14.2. UN proper shipping name: Not Applicable

14.3. Transport hazard class(es): Class: Not Applicable; Subrisk: Not Applicable

14.4. Packing group: Not Applicable

14.5. Environmental hazard: Not Applicable

14.6. Special precautions for user:

Hazard identification(Kemler): Not Applicable

Classification code: Not Applicable

Hazard Label: Not Applicable

Special provisions: Not Applicable

Limited quantity: Not Applicable

### Air transport(ICAO-IATA/DGR): NOT REGULATED FOR TRANSPORT OF DANGEROUS GOODS

14.1. UN Number: Not Applicable

14.2. UN proper shipping name: Not Applicable

<b>14.3. Transport hazard class(es):</b>	
ICAO/IATA Class:	Not Applicable
ICAO/IATA Subrisk:	Not Applicable
ERG Code:	Not Applicable
<b>14.4. Packing group:</b>	Not Applicable
<b>14.5. Environmental hazard:</b>	Not Applicable
<b>14.6. Special precautions for user:</b>	
Special provision:	Not Applicable
Cargo Only Packing Instructions:	Not Applicable
Cargo Only Maximum Qty/Pack:	Not Applicable
Passenger and Cargo Packing Instructions:	Not Applicable
Passenger and Cargo Maximum Qty/Pack:	Not Applicable
Passenger and Cargo Limited Quantity Packing Instructions:	Not Applicable
Passenger and Cargo Limited Maximum Qty/Pack:	Not Applicable

**Sea transport(IMDE-Code/GGVSee): NOT REGULATED FOR TRANSPORT OF DANGEROUS GOODS**

<b>14.1. UN Number:</b>	Not Applicable
<b>14.2. UN proper shipping name:</b>	Not Applicable
<b>14.3. Transport hazard class(es):</b>	
IMDG Class:	Not Applicable
IMDG Subrisk:	Not Applicable
<b>14.4. Packing group:</b>	Not Applicable
<b>14.5. Environmental hazard:</b>	Not Applicable
<b>14.6. Special precautions for user:</b>	
EMS:	Not Applicable
Special provision:	Not Applicable
Limited Quantities:	Not Applicable

**Inland waterways transport(ADN): NOT REGULATED FOR TRANSPORT OF DANGEROUS GOODS**

<b>14.1. UN Number:</b>	Not Applicable
<b>14.2. UN proper shipping name:</b>	Not Applicable
<b>14.3. Transport hazard class(es):</b>	Not Applicable
<b>14.4. Packing group:</b>	Not Applicable
<b>14.5. Environmental hazard:</b>	Not Applicable
<b>14.6. Special precautions for user:</b>	
Classification code:	Not Applicable
Special provision:	Not Applicable
Limited quantity:	Not Applicable
Equipment required:	Not Applicable
Fires cones number:	Not Applicable

**14.7. Transport in bulk according to Annex II of MARPOL and the IBC code**  
Not Applicable

**Section 15 Regulation information**

**15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture:**

**SODIUM PALMATE(CAS NO.: 61790-79-2) IS FOUND ON THE FOLLOWING REGULATORY LISTS**

*European Union – European Inventory of Existing Commercial Chemical Substance(EINECS)*

**SODIUM PALM KERNELATE(CAS NO.: 61789-89-7) IS FOUND ON THE FOLLOWING REGULATORY LISTS**

*European Union – European Inventory of Existing Commercial Chemical Substance(EINECS)*

**WATER(CAS NO.: 7732-18-5) IS FOUND ON THE FOLLOWING REGULATORY LISTS**

*European Union – European Inventory of Existing Commercial Chemical Substance(EINECS)*

*EU REACH Regulation (EC)No. 1907/2006 – Annex IV – Exemptions from the Obligation to Register in Accordance with Article 2(7)(a)*

*European Customs Inventory of Chemical Substance ECICS*

**Glycerin(CAS NO.: 56-81-5) IS FOUND ON THE FOLLOWING REGULATORY LISTS**

*European Union – European Inventory of Existing Commercial Chemical Substance(EINECS)*



European Customs Inventory of Chemical Substance ECICS

**SODIUM CHLORIDE(CAS NO.: 7647-14-5) IS FOUND ON THE FOLLOWING REGULATORY LISTS**

European Customs Inventory of Chemical Substance ECICS

**Citric Acid(CAS NO.: 5949-29-1) IS FOUND ON THE FOLLOWING REGULATORY LISTS**

European Customs Inventory of Chemical Substance ECICS

**Tetrasodium Etidronate(CAS NO.: 3794-83-0) IS FOUND ON THE FOLLOWING REGULATORY LISTS**

European Customs Inventory of Chemical Substance ECICS

European Union – European Inventory of Existing Commercial Chemical Substance(EINECS)

This safety data sheet is in compliance with the following EU legislation and its adaptations – as far as applicable - :

Directives 98/24/EC, -92/85/EEC, -94/33/EC, - 2008/98/EC, - 2010/75/EU;

Commission Regulation (EU) No. 1272/2008 as updated through ATPs.

### 15.2 Chemical safety assessment

No Chemical Safety Assessment has been carried out for this substance/mixture by the supplier.

## Section 16 Other information

### 16.1 Full text Risk and Hazard codes

H302: Harmful if swallowed

H319: Causes serious eye irritation

### 16.2 Other information

The SDS is a Hazard Communication tool and should be used to assist in the Risk Assessment. Many factors determine whether the reported Hazards are Risks in the workplace or other settings.

For detailed advice on Personal Protective Equipment, refer to the following EU CEN Standards:

EN 166 Personal eye-protection

EN 340 Protective clothing

EN 374 Protective gloves against chemicals and micro-organisms

EN 13832 Footwear protecting against chemicals

EN 133 Respiratory protective devices

### 16.3 Definitions and abbreviations

<b>PC—TWA:</b>	Permissible Concentration – Time Weighted Average
<b>PC—STEL:</b>	Permissible Concentration – Short Term Exposure Limit
<b>IARC:</b>	International Agency for Research on Cancer
<b>ACGIH:</b>	American Conference of Governmental Industrial Hygienists
<b>STEL:</b>	Short Term Exposure Limit
<b>TEEL:</b>	Temporary Emergency Exposure Limit
<b>IDLH:</b>	Immediately Dangerous to Life or Health Concentrations
<b>OSF:</b>	Odour Safety Factor
<b>NOAEL:</b>	No Observed Adverse Effect Level
<b>LOAEL:</b>	Lower Observed Adverse Effect Level
<b>TLV:</b>	Threshold Limit Value
<b>LOD:</b>	Limit of Detection
<b>OTV:</b>	Odour Threshold Value
<b>BCF:</b>	Bioconcentration Factors
<b>BEI:</b>	Biological Exposure Index.

### 16.4 Disclaimer:

The health and safety information contained in this MSDS is believed to be true and correct. However because Jiangsu Oppeal Daily Cosmetics Corp., Ltd. has no control over the method of use of this product, all statements or suggestions are made without warranty, expressed or implied, regarding the reliability of the information, or the hazards resulting from the use of the material. Every user should consider the information given in this MSDS in the context of how this product will be used in the user's workplace, including the effects of other products on the premises.