

# ALBION<sup>®</sup>

## CASTERS AND WHEELS

# Die Cast Casters & Mounts

- Zinc Die-Cast Body and Hood
- Concealed Axle

**Applications:** Seating, Electronic Equipment, Store Fixtures, Office Equipment



### Bodies

Wheel Dia. (In.)	Wheel Width (In.)	Load Rating (lbs.)	Overall Height (In.)	For Surface Type	Body Finish	Tread Type	Swivel Part Number	Swivel w/Brake Part Number
2	1-13/16	75	2-1/4	Carpeted	Black	Nylon	202NY02041S002	202NY02041S003
2	1-13/16	75	2-1/4	Carpeted	Chrome	Nylon	202NY02041S004	202NY02041S001
2	1-13/16	75	2-1/4	Hard	Black	Polyurethane	202XG02041S002	NA
2	1-13/16	75	2-1/4	Hard	Chrome	Polyurethane	202XG02041S001	NA
2-1/2	2	90	2-3/4	Carpeted	Black	Nylon	202NY02X041S005	NA
2-1/2	2	90	2-3/4	Carpeted	Chrome	Nylon	202NY02X041S004	NA
2-1/2	2	90	2-3/4	Hard	Black	Polyurethane	202XG02X041S002	NA
2-1/2	2	90	2-3/4	Hard	Chrome	Polyurethane	202XG02X041S001	NA

### Mounting Options

Wheel Dia. (In.)	Mount Type	Mount Dimensions	Mount Part Number	Wheel Dia. (In.)	Mount Type	Mount Dimensions	Mount Part Number
2	Plate	1" x 1"	KITSXS70001	2-1/2	Plate	1" x 1"	KITSXS70
2	Plate	13/16" x 1-9/16"	KITSXS71001	2-1/2	Grip Neck Stem	5/16" x 1-1/2"	KITSXS80
2	Grip Neck Stem	5/16" x 1-1/2"	KITSXS80001	2-1/2	Friction Ring Stem	3/8" x 1"	KITSXS23
2	Friction Ring Stem	3/8" x 1"	KITSXS23001	2-1/2	Friction Ring Stem	7/16" x 7/8"	KITSXS24
2	Friction Ring Stem	7/16" x 7/8"	KITSXS24001	2-1/2	Friction Ring Stem	7/16" x 1-3/8"	KITSXS21
2	Friction Ring Stem	7/16" x 1-3/8"	KITSXS21001	2-1/2	Threaded Stem	3/8"-16 x 1"	KITSXS11
2	Threaded Stem	3/8"-16 x 1"	KITSXS11001				