

MODEL: HAULER 800

TYPE: ELECTRIC 48V POWERED TRUCK

MODEL YEAR: 2014

Part No: 618840



PRODUCT SPECIFICATION

CONFIGURATION HIGHLIGHTS

Programmable to any golf course terrain, with expanded regenerative braking function, and vehicle charger lockout TrueCourse Technology:

- Solid State continuously variable separately excited speed controller
- Dash mounted direction selector switch (Forward-Neutral-Reverse)
- Anti-roll back, walkaway braking and alarm
- Programmable regenerative braking, acceleration and speed

 Handheld vehicle diagnostics and rounds tracking **Battery Charger:** 48 Volt DC high frequency, fully line compensating. 10ft (3m) DC Cord. Underwriters Lab. (U.L.) Listed, (C.S.A. Certified)

 Input: 120 Volts AC, 50/60Hz, 8 amps Output: 48 Volts DC at 13 amps

Motor: 48 Volt DC shunt wound, brazed armature, solid copper windings

Drive Train: Direct motor shaft connected to transaxle pinion shaft

Electrical System: 48 Volt DC, six, 8 volt deep cycle batteries (110 minute minimum, 160 amp-hour @ 20 hr. discharge rate)

Transaxle: Differential with helical gears

Brakes: Dual rear wheel mechanical self-adjusting drum brakes. Automatic single point park brake release with self-compensating system

Cargo Bed: Roto-molded cross-linked polyethylene. Lifts for access to powertrain. Removable hinged multi-position tailgate requires no latch mechanism

PRODUCT OVERVIEW

Dimensions	
Overall Length	107 in (272 cm)
Overall Width	49.5 in (128 cm)
Overall Height (No Canopy)	46.5 in (118 cm) (Top of steering wheel)
Overall Height (With Canopy)	70.0 in (178 cm)
Wheel Base	65.5 in (166 cm)
Front Wheel Track	37.0 in (94 cm)
Rear Wheel Track	38.0 in (97 cm)
Gnd Clearance @ Differential	4.3 in (11 cm)
Cargo Box Width (inside)	44.5 in (113 cm)
Cargo Box Length (inside)	30.5 in (77 cm)
Cargo Box Depth (inside)	7.5 in (19 cm)
Cargo Box Capacity	5.9 cu ft (0.17 m3)
Cargo Box material	Roto-molded polyethylene
Vehicle Power	

V	е	n	C	е	Power
	. –				

Motor Type 48 VDC, Shunt Wound 3.0 HP (2.2kW) Continuous Horsepower (kW)

Electrical System 48 Volt

Batteries (Qty, Type) Six, 8 Volt Deep Cycle

Key or Pedal Start Pedal Start

Battery Charger 48 Volt DC, 120 VAC input, UL/CSA Speed Controller 250 Amp Solid State Controller Drive Train Motor Shaft Direct Drive

Transaxle and Ratio Differential with helical gears, 12.44:1 Ratio Gear Selection Forward-Neutral-Reverse Dash Mounted Switch

Performance	
Seating Capacity	2 Persor

Six, 8 Volt Deep Cycle Batteries

Inductive throttle sensor

Full torque, reduced speed reverse

Dry Weight 747 lb (339 kg) (Without Batteries)

Curb Weight 1,112 lb (504 kg) **Bed Load Capacity** 500 lb (226 kg) Vehicle load capacity 800 lb (360 kg) **Outside Clearance Circle** 18.9 ft (5.76 m)

Intersecting Aisle Clearance

Speed (Level Ground) 10.2-14.8 mph (16.4-23.8 kph) **Towing Capacity** 475 lb (215 kg) max load

Steering & Suspension

Steering	Self-compensating rack and pinion
Front Suspension	Leaf springs with hydraulic shock absorbers
Rear Suspension	Leaf springs with hydraulic shock absorbers
Service Brake	Rear wheel mechanical self-adjusting drum
Parking Brake	Self-compensating, single point engagement
Front Tires	Links 18 x 8.50 - 8 (4 Ply Rated)

Turf Saver 18 x 8.50 - 8 (Load Range B) Rear Tires

Body & Chassis

Welded steel with DuraShield™ powder coat Frame

Front Body & Finish Injection molded TPO, Painted Rear Body & Finish Steel. Polyester Powder coat

Standard Color Forest Green

Some items shown may be optional equipment



Item	Std	Opt Fld	Item	Std	Opt F	- Ic
TIRES & WHEELS:			Electrical Other		П	Π
Front:			DC Converter	Х		
Links 18 x 8.50 - 8 (4 Ply Rated)	Х		Horn	Х		
USA Trail 18 x 8.50 - 8 (Load Range C)		Х	State of Charge Meter	Х		
Turf Saver 18 x 8.50 - 8 (Load Range B)		Х	Hour Meter		Х	
Rear:	•		Unique Individual Key Switch		Х	
Turf Saver 18 x 8.50 - 8 (Load Range B)	Х			•		
USA Trail 18 x 8.50 - 8 (Load Range C)		Х	HAULING & TOWING:			
Links 18 x 8.50 - 8 (4 Ply Rated)		Х	36" Poly Bed w/Manual Dump	Χ		
Wheel Covers:	<u> </u>		36" Poly Bed w/Elec Dump		Х	
Spoke, Black & Gold		Х	2 in (5 cm) Receiver (Rear)		Х	
Spoke, Black & Silver		Х	1 7/8 in (48 mm) Ball (Rcvr Reqd)		Х	
COLORS:	-		1 7/8 in (48 mm) Ball, Drop (Rcvr Reqd)		Х	
Body Color - Forest Green	Х		Angle (Rcvr Reqd)		Х	
Body Color - Ivory		Х	Angle, Drop (Rcvr Reqd)		Х	
Body Color - Bright White		Х	Clevis (Rcvr Reqd)		Х	
Body Color - Patriot Blue		Х	Clevis, Drop (Rcvr Reqd)		Х	
Body Color - Orange		Х		•		
Seating:	<u> </u>		TRANSAXLE:			
Seat Color - Grey	Х		Limited Slip Differential		Х	
Seat Color - Oyster		Х		•	•	
Seat Color - White		Х				
			WEATHER PROTECTION:			
OTHER PERFORMANCE:			Sun Canopy (Top) Black			Χ
Front Bumper & Fascia - Black	Х		Windshield Fold Down			Χ
Ash Tray		Х	Weather Enclosure, (3 Side, Top & Windshield Req'd)			Χ
Differential Guard		Х	Windshield Flat			Χ
Front Hydraulic Disc Brakes		Х			-	
Glove Box Door (Locking) Driver Side		Х	VEHICLE CAB:			
Glove Box Door (Locking) Passenger Side		Х	Steel Cab without doors (Tan):			Χ
VPS vehicle Performance System		Х	Steel Cab without doors (White):			Χ
Fender Flares (International)		Х	Doors (Steel) Tan (Cab Required)			Χ
ELECTRICAL:			Doors (Steel) White (Cab Required)			Χ
Battery Chargers and Batteries:			Defroster/Cooling Fab			Χ
48VDC 10 ft (3.0 m) DC Cord	Χ		Beacon, Amber (Cab Required)			Χ
48VDC 18 ft (5.5 m) DC Cord		Х	Defroster/Fan (Cab Required)			Χ
World Charger 48VDC 10 ft (3.0 m) DC Cord		Х	Canopy Grab Handle			Χ
World Charger 48VDC 18 ft (5.5 m) DC Cord		Х	Doors (Vinyl), Tan (Cab Required)			Χ
T8V Battery	Х		Doors (Vinyl), White (Cab Required)			Χ
T8V Battery w/Battery Fill System		Х	Strobe Light (Cab Required)			Χ
T890 Battery (HD)		Х	Switch Panel & Fuse kit (Cab Required)			Χ
T890 Battery (HD) w/Battery Fill System		Х	Windshield Wiper (Cab Required)			Χ
Lighting Package:	11		Work Light (Cab Required)			Χ
Headlights	Х					_

Headlights & Taillights

Turn Signals with 4-Way Flashers