

TUG

ELECTRIC TOW TRACTOR

Up to 5,000 lb Towing Capacity

4.9-sq-ft Cargo Deck

36-volt DC Powertrain

5000^{lb}_{MAX}
TOW

450^{lb}_{MAX}
LOAD

36v
ELECTRIC



Features and specifications of vehicles subject to change without notice.
Vehicle as photographed may include options not included on base model.



CUSHMAN™



CUSHMAN™
LET'S WORK.®

Pulling your weight effortlessly.

If you need a vehicle with exceptional towing capability, look no further than the Cushman Tug. It's built to pull loads of up to 5,000 pounds across indoor facilities and hard-surface areas with ease. The Tug's silent, zero-emissions 36-volt DC powertrain, three-wheel hydraulic brakes and simple, ergonomic controls make it an ideal choice for factories, distribution centers and other facilities that need to move materials safely and efficiently. No matter the load, you can count on the Tug to pull its weight.



TUG ELECTRIC UTILITY VEHICLE

| DIMENSIONS | |
|--------------------------------------|--|
| Overall Length | 76.0 in (193 cm) |
| Overall Width | 34.5 in (87.6 cm) |
| Overall Height (Top of Handlebars) | 37.0 in (94 cm) |
| Wheel Base | 52.5 in (133.4 cm) |
| Front Wheel Track | N/A |
| Rear Wheel Track | 29.7 in (75.4 cm) |
| Cargo Box Width (Inside) | 33.5 in (85 cm) |
| Cargo Box Length (Inside) | 21.0 in (53 cm) |
| Cargo Box Depth (Inside) | 1.75 in (4.4 cm) |
| POWER | |
| Powertrain | 36-Volt DC Series Wound |
| Horsepower (kW) | 11.1 hp (8.28 kW) @ 1942 rpm |
| Electrical System | 36-Volt DC |
| Batteries (Qty, Type) | Six, 6V Deep Cycle |
| Battery Charger | 36 VDC On-Board |
| Speed Controller | 350 Amp Programmable. SRO Capable |
| Drivetrain | Triple 'V' belt connected to differential pinion shaft |
| Differential | Worm Gear Driven |
| Gear Selection | Forward-Neutral-Reverse |
| Gear Shift Location | Dash Mounted |
| Rear Axle Ratio | 15.67:1 |
| PERFORMANCE | |
| Seating Capacity & Style | 1-Person |
| Dry Weight (w/o Batteries) | 571 lb (259 kg) |
| Curb Weight | 940 lb (426 kg) |
| Vehicle Load Capacity | 450 lbs (200 kg) |
| Inside Clearance Circle (Handlebar) | Turnabout Rear Wheel |
| Outside Clearance Circle (Handlebar) | 9 ft (2.8 m) |
| Towing Capacity | Up to 5000 lb (2275 kg) |
| Speed (level ground) | Up to 7.8 mph (12.6 kmh) |
| STEERING & SUSPENSION | |
| Steering | Handlebar |
| Front Suspension | Coil Spring |
| Rear Suspension | Coil Springs with Hydraulic Shock Absorber |
| Service Brake | 3 Wheel Hydraulic Drum |
| Parking Brake | Hand Lever, Mechanical Rear Brakes |
| Front & Rear Tires | USA Trail 4.80 x 8 (Load Range B) |
| FRAME & COLOR | |
| Frame & Body | Welded Steel with Powder-Coat Protection |
| Body & Finish | Diamond Plate. Polyester Primer and Acrylic |
| Standard Color | Safety Yellow |

Factory Installed Options & Field Accessories

- Steering Wheel
- Foam Filled Tires
- Portable Charger
- Certification Module EE
- Hour Meter
- Headlight
- Lift-out Battery Tray
- Heavy-duty Battery Upgrade
- CE Certification
- Clevis or Pintle Hitch