

# LX Series Designer LED Exit Sign

### **FEATURES**

### **Application**

The LX Series offers bright and even LED EXIT panel illumination with Green or Red letters and attractive UV stable thermo-plastic housing. Features include AC or Emergency operation with optional Spectron® self-test/self diagnostic circuitry. Housing designed for quick and easy installation with low energy consumption. Damp location listed. Accepts 120 or 277 VAC input.

#### Construction

The precision-molded thermoplastic housing is impact resistant and scratch resistant, corrosion proof and UL stabilized to resist discoloration. Available in white or black finish. Innovative snap-together design. Includes additional face-plate for single or double face applications. Snap-in directional chevrons. Exit stencil with 6" letters and 34" stroke. Includes push-in wire connectors for easy installation.

#### Installation

Universal mounting (ceiling, end, wall) to standard 3 ½" or 4" octagon or square electrical box by use of easily removed, template configured knockouts. Canopy and universal mounting plate included. All mounting hardware is fully concealed.

#### Illumination

Exit face illumination is provided by energy saving, long-life red or green LED's. Exceeds UL 924 requirements for brightness and uniformity. UL listed LED run-time of 120 minutes. 10 year LED life.

#### **Compliances**

UL 924 Listed (Meets1998 brightness and uniformity requirments) **UL Damp Location Listed** NFPA-70 NFPA-101 US Patent No. D402,316, and D406,863.


#### Warranty

Unit and electronics: 5 years full





### **ORDERING GUIDE**



-FAP Fire Alarm Panel Interface 1, 3, 5, 6

-FM Flasher Module 1, 6

Audible/Flasher Module 1, 6

**-DC** Remote DC Operation <sup>2, 4, 5</sup>

-24K 220-240 VAC, 60Hz Operation

### ACCESSORIES (order separately)

VRS-3 Vandal Resistant Shield

FCM-R Kit Converts AC red letter models to emergency operation Kit Converts AC green letter models to emergency operation 12 ½" Pendant Mounting Kit (white) FCM-G

**PMLXW** 12 ½" Pendant Mounting Kit (black) **PMLXB** 

WGLX Wire Guard (wall mount) WGLXC Wire Guard (ceiling mount) WGLXE Wire Guard (end mount)

### **FEATURES**

- (1) For use with Spectron® self-diagnostic models only.
- (2) For use with AC models only.
- (3) Operates with 24-volt AC or DC fire alarm panels.
- (4) For emergency illumination of sign from remote 6-24 VDC power sources.
- (5) -DC option may not be specified with -2C or -FAP options.
- (6) -AF, -FM and -FAP options may not be specified together.







## **SPECIFICATIONS**

#### **Electronics**

Available with AC, emergency and Spectron® self-diagnostic/self-testing electronics option. Emergency and self-diagnostic models equipped with isolation transformer and fully automatic constant current solid-state charger with sealed maintenance-free nickel-cadmium battery. All components mounted inside housing. Includes test switch and AC-on indicator. Transient/ surge protection, low-voltage disconnect and AC lock –out features included. Battery re-charge within UL time standards. Includes prestripped AC input pigtail leads.UL listed LED run-time of 120 minutes.

### **Power Consumption**

	120VAC	277VAC
Red AC Only Models:	2.64 watts	2.70 watts
Green AC Only Models:	2.24 watts	2.24 watts
Red Emergency Models:	3.81 watts	3.80 watts
Green Emergency Models:	3.50 watts	3.50 watts

<sup>\*</sup> Wattage figures include LED lamps, transformer and electronics power requirements. LED lamp assemblies (red or green) consume less than 1 watt.

Power Factor, Average: .8 (lagging)

Battery Type: Maintenance-free sealed nickel cadmium battery

AC Input: 120/277VAC, 60 Hz. (all models)

**Operating Temperature Range:** 0°C to 40°C (32°F to 104°F)

### **DIMENSIONS**

