




# Material Safety Data Sheet

| HAZARD WARNINGS   | RISK PHRASES   | PROTECTIVE CLOTHING   |
|---|--|---|
|   | <p><b>Corrosive to eyes and skin on contact.</b><br/> <b>Toxic compound, do not ingest or inhale. Avoid all contact with this material.</b><br/> <b>Air sensitive material.</b><br/> <b>Hygroscopic -- keep container tightly sealed.</b><br/> <b>Store under inert gas.</b></p> |  |

## Section I. Chemical Product and Company Identification

|                  |   |                                 |   |
|------------------|---|---------------------------------|---|
| Chemical Name    | <b>Lithium Hydroxide Anhydrous</b><br>[for General Organic Chemistry] |                                 |   |
| Catalog Number   | L0225   | Supplier                        | TCI America<br>9211 N. Harborgate St.<br>Portland OR<br>1-800-423-8616                    |
| Synonym          | Lithium hydroxide (Li(OH)) (CA INDEX NAME)                            |                                 |   |
| Chemical Formula | LiOH  |                                 |   |
| CAS Number       | 1310-65-2   | In case of<br>Emergency<br>Call | <b>Chemtrec®</b><br><b>(800) 424-9300 (U.S.)</b><br><b>(703) 527-3887 (International)</b> |

## Section II. Composition and Information on Ingredients

| Chemical Name   | CAS Number | Percent (%)   | TLV/PEL        | Toxicology Data   |
|---|------------|---------------|----------------|---|
| Lithium Hydroxide Anhydrous<br><small>(for General Organic Chemistry)</small> | 1310-65-2  | Min. 98.0 (T) | Not available. | Rat LD <sub>50</sub> (oral) 210 mg/kg<br>Rat LD <sub>50</sub> (inhalation) 960 mg/m <sup>3</sup> /4H<br>Rat LD <sub>50</sub> (intratracheal) 8200 ug/kg |

## Section III. Hazards Identification

|                        |  |
|------------------------|--|
| Acute Health Effects   | Corrosive to skin, eyes, and respiratory system. Liquid or spray mist may produce tissue damage, particularly in mucous membranes of the eyes, mouth and respiratory tract. Skin contact may produce burns. Eye contact can result in corneal damage or blindness. Inhalation of the spray mist may produce severe irritation of respiratory tract, characterized by coughing, choking, or shortness of breath. Corrosive materials may cause serious injury if ingested. Toxic if ingested or inhaled. Avoid prolonged contact with this material. Overexposure may result in serious illness or death. Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound. |
| Chronic Health Effects | <p><b>CARCINOGENIC EFFECTS</b> : Not available.<br/> <b>MUTAGENIC EFFECTS</b> : Not available.<br/> <b>TERATOGENIC EFFECTS</b> : Not available.<br/> <b>DEVELOPMENTAL TOXICITY</b>: Not available.</p> <p>Repeated exposure of the eyes to a low level of dust can produce eye irritation. Repeated skin exposure can produce local skin destruction, or dermatitis. Repeated inhalation of dust can produce varying degree of respiratory irritation or lung damage. Repeated exposure to an highly toxic material may produce general deterioration of health by an accumulation in one or many human organs.</p>  |

## Section IV. First Aid Measures

|              |   |
|--------------|---|
| Eye Contact  | Check for and remove any contact lenses. In case of contact, immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.  |
| Skin Contact | In case of contact, immediately flush skin with plenty of water for at least 15 minutes while removing contaminated clothing and shoes. Wash clothing before reuse. Thoroughly clean shoes before reuse. Get medical attention immediately.   |
| Inhalation   | If the victim is not breathing, perform mouth-to-mouth resuscitation. Loosen tight clothing such as a collar, tie, belt or waistband. If breathing is difficult, oxygen can be administered. Seek medical attention if respiration problems do not improve.   |
| Ingestion    | DO NOT INDUCE VOMITING. Loosen tight clothing such as a collar, tie, belt or waistband. If the victim is not breathing, perform mouth-to-mouth resuscitation. Examine the lips and mouth to ascertain whether the tissues are damaged, a possible indication that the toxic material was ingested; the absence of such signs, however, is not conclusive. |

## Section V. Fire and Explosion Data

|                                      |   |                  |                |
|--------------------------------------|---|------------------|----------------|
| Flammability                         | May be combustible at high temperature.   | Auto-Ignition    | Not available. |
| Flash Points                         | Not available.  | Flammable Limits | Not available. |
| Combustion Products                  | Some metallic oxides.   |                  |                |
| Fire Hazards                         | Not available.  |                  |                |
| Explosion Hazards                    | Risks of explosion of the product in presence of mechanical impact: Not available.<br>Risks of explosion of the product in presence of static discharge: Not available. |                  |                |
| Fire Fighting Media and Instructions |   |                  |                |

Continued on Next Page

Emergency phone number (800) 424-9300

[for General Organic Chemistry]

SMALL FIRE: Use DRY chemical powder.  
 LARGE FIRE: Use water spray, fog or foam. DO NOT use water jet.  
 Consult with local fire authorities before attempting large scale fire-fighting operations.

## Section VI. Accidental Release Measures

Spill Cleanup Instructions Corrosive material. Toxic material. Air sensitive material. Hygroscopic material. Stop leak if without risk. DO NOT get water inside container. DO NOT touch spilled material. Use water spray to reduce vapors. Prevent entry into sewers, basements or confined areas; dike if needed. Eliminate all sources of ignition. Consult federal, state, and/or local authorities for assistance on disposal.

## Section VII. Handling and Storage

Handling and Storage Information CORROSIVE. TOXIC. AIR SENSITIVE. HYGROSCOPIC. STORE UNDER INERT GAS. Keep locked up. Keep container dry. Keep away from heat. Mechanical exhaust required. When not in use, tightly seal the container and store in a dry, cool place. Avoid excessive heat and light. DO NOT ingest. Do not breathe dust. Never add water to this product. Wear suitable protective clothing. If ingested, seek medical advice immediately and show the container or the label. Treat symptomatically and supportively. Always store away from incompatible compounds such as oxidizing agents, acids, moisture.

## Section VIII. Exposure Controls/Personal Protection

Engineering Controls Use process enclosures, local exhaust ventilation, or other engineering controls to keep airborne levels below recommended exposure limits. If user operations generate dust, fume or mist, use ventilation to keep exposure to airborne contaminants below the exposure limit.

Personal Protection Face shield. Lab coat. Dust respirator. Boots. Gloves. A MSHA/NIOSH approved respirator must be used to avoid inhalation of the product. Suggested protective clothing might not be sufficient; consult a specialist BEFORE handling this product.



Exposure Limits Not available.

## Section IX. Physical and Chemical Properties

|                       |                         |                       |  |
|-----------------------|-------------------------|-----------------------|--|
| Physical state @ 20°C | Solid. (White powder.)  | Solubility            | Soluble in water (12.8g/100mL @ 20°C). Slightly soluble in alcohol, ethanol. |
| Specific Gravity      | 2.54 (water=1)          |                       |  |
| Molecular Weight      | 23.95                   | Partition Coefficient | Not available.   |
| Boiling Point         | 924°C (1695.2°F) (dec.) | Vapor Pressure        | Not applicable.  |
| Melting Point         | 471°C (879.8°F)         | Vapor Density         | Not available.   |
| Refractive Index      | Not available.          | Volatility            | Not available.   |
| Critical Temperature  | Not available.          | Odor                  | Odorless.  |
| Viscosity             | Not available.          | Taste                 | Not available.   |

## Section X. Stability and Reactivity Data

Stability This material is stable if stored under proper conditions. (See Section VII for instructions)

Conditions of Instability Avoid excessive heat and light. Air sensitive. Hygroscopic; keep container tightly closed. Store under inert gas.

Incompatibilities Reactive with oxidizing agents, acids, moisture.

## Section XI. Toxicological Information

RTECS Number OJ6307070

Routes of Exposure Eye Contact. Ingestion. Inhalation. Skin contact.

Toxicity Data  
 Rat LD<sub>50</sub> (oral) 210 mg/kg  
 Rat LD<sub>50</sub> (inhalation) 960 mg/m<sup>3</sup>/4H  
 Rat LD<sub>50</sub> (intratracheal) 8200 ug/kg

Chronic Toxic Effects  
**CARCINOGENIC EFFECTS** : Not available.  
**MUTAGENIC EFFECTS** : Not available.  
**TERATOGENIC EFFECTS** : Not available.  
**DEVELOPMENTAL TOXICITY** : Not available.  
 Repeated exposure of the eyes to a low level of dust can produce eye irritation. Repeated skin exposure can produce local skin destruction, or dermatitis. Repeated inhalation of dust can produce varying degree of respiratory irritation or lung damage. Repeated exposure to an highly toxic material may produce general deterioration of health by an accumulation in one or many human organs.

Acute Toxic Effects Corrosive to skin, eyes, and respiratory system. Liquid or spray mist may produce tissue damage, particularly in mucous membranes of the eyes, mouth and respiratory tract. Skin contact may produce burns. Eye contact can result in corneal damage or blindness. Inhalation of the spray mist may produce severe irritation of respiratory tract, characterized by coughing, choking, or shortness of breath. Corrosive materials may cause serious injury if ingested. Toxic if ingested or inhaled. Avoid prolonged contact with this material. Overexposure may result in serious illness or death. Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.

Continued on Next Page

Emergency phone number (800) 424-9300


**Section XII. Ecological Information**

|                    |                |
|--------------------|----------------|
| Ecotoxicity        | Not available. |
| Environmental Fate | Not available. |

**Section XIII. Disposal Considerations**

|                |   |
|----------------|---|
| Waste Disposal | Recycle to process, if possible. Consult your local regional authorities. You may be able to dissolve or mix material with a combustible solvent and burn in a chemical incinerator equipped with an afterburner and scrubber system. Observe all federal, state and local regulations when disposing of the substance. |
|----------------|---|

**Section XIV. Transport Information**

|                      |   |
|----------------------|---|
| DOT Classification   | DOT Class 8: Corrosive material   |
| PIN Number           | UN2680  |
| Proper Shipping Name | Lithium hydroxide   |
| Packing Group (PG)   | II  |
| DOT Pictograms       |  |

**Section XV. Other Regulatory Information and Pictograms**

|                               |   |
|-------------------------------|---|
| TSCA Chemical Inventory (EPA) | This compound is <b>ON</b> the EPA Toxic Substances Control Act (TSCA) inventory list.                            |
| WHMIS Classification (Canada) | CLASS D-1B: Material causing immediate and serious toxic effects (TOXIC).<br>CLASS E: Corrosive solid.<br>On DSL. |
| EINECS Number (EEC)           | 215-183-4   |
| EEC Risk Statements           | R23/24/25- Toxic by inhalation, in contact with skin and if swallowed.<br>R34- Causes burns.                      |
| Japanese Regulatory Data      | ENCS No. 1-712  |

**Section XVI. Other Information**

**Version 1.0**  
**Validated on 10/1/2009.**  
**Printed 10/1/2009.**

**Notice to Reader**

TCI laboratory chemicals are for research purposes only and are NOT intended for use as drugs, food additives, households, or pesticides. The information herein is believed to be correct, but does not claim to be all inclusive and should be used only as a guide. Neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All chemical reagents must be handled with the recognition that their chemical, physiological, toxicological, and hazardous properties have not been fully investigated or determined. All chemical reagents should be handled only by individuals who are familiar with their potential hazards and who have been fully trained in proper safety, laboratory, and chemical handling procedures. Although certain hazards are described herein, we can not guarantee that these are the only hazards which exist. Our MSDS sheets are based only on data available at the time of shipping and are subject to change without notice as new information is obtained. Avoid long storage periods since the product is subject to degradation with age and may become more dangerous or hazardous. It is the responsibility of the user to request updated MSDS sheets for products that are stored for extended periods. Disposal of unused product must be undertaken by qualified personnel who are knowledgeable in all applicable regulations and follow all pertinent safety precautions including the use of appropriate protective equipment (e.g. protective goggles, protective clothing, breathing equipment, facial mask, fume hood). For proper handling and disposal, always comply with federal, state, and local regulations.