

# POWER MIG® 140C



## Processes

MIG, Flux-Cored

## Product Number

K2471-2

See back for complete specs

## Input Power

120/1/60

## Input Current at Rated Output

20A

## Rated Output Current/Voltage/Duty Cycle

90A/19.5V/20%

## Output Range

30-140 Amps DC, Max. OCV: 33

## Wire Feed Speed Range

50-500 ipm (1.3-12.7 m/min)

## Weight/Dimensions (H x W x D)

58 lbs. (26.3 kg)

14 x 10.15 x 18.6 in.  
(357 x 258 x 472 mm)

## POWER MIG® The Professional's Choice.™

Home projects and repair, sheet metal autobody work, farm and small shop welding—the POWER MIG® 140C designed for 120 volt household power does it all!

### FEATURES

- ▶ **Diamond Core Technology™** – Delivers a forgiving arc, excellent out-of-position arc action, low spatter and a wide voltage sweet spot at a given wire feed speed for steel, stainless steel or aluminum.
- ▶ **Industrial Cast Aluminum Drive** – Dual gear-driven drive rolls deliver positive traction. Patented split wire guides ensure optimal wire alignment and a brass-to-brass gun connection aids critical conductivity. A large industrial closed-design drive motor improves torque and enhances trouble-free performance.
- ▶ **No Hassle Tool-less Design** – For input power changes, wire spool mounting, wire drive service and polarity changes.
- ▶ **Spool Gun Ready** – Just remove the standard MIG gun and plug in the economical Magnum® PRO 100SG spool gun (optional) for enhanced aluminum wire feeding performance.
- ▶ **Toughest PC Board Protection in the Industry** – 'Potted' to seal sensitive components from the environment, 'trayed' in a tough plastic tray to add rigidity and shock resistance.

### APPLICATIONS

- ▶ Metal Fabrication
- ▶ Maintenance and Repair
- ▶ Autobody/Farm
- ▶ Light Industrial



Shown: K2471-2

### WHAT'S INCLUDED

#### K2471-2 Includes:

- ▶ Magnum® PRO 100L gun, 10 ft. (3.0 m)
- ▶ Gas and Gasless Nozzles
- ▶ Cable Liner
- ▶ .025 in. (0.6 mm) and .035 in. (0.9 mm) Contact Tips
- ▶ Work Cable and Clamp
- ▶ Adjustable Gas Regulator and Hose
- ▶ Spindle Adapter
- ▶ Sample Spool of .025 in. (0.6 mm) SuperArc® L-56 Mild Steel MIG Wire
- ▶ Sample Spool of .035 in. (0.9 mm) Innershield® NR-211-MP Flux-Cored Wire
- ▶ Learn-To-Use DVD
- ▶ .025 in. (0.6 mm) and .025 - .030 in. (0.6 - 0.7 mm) Drive Rolls
- ▶ .030 - .045 in. (0.7 - 1.1 mm) Knurled Drive Roll
- ▶ .025 - .035 in. (0.6 - 0.9 mm) and .035 - .045 in. (0.9 - 1.1 mm) Wire Guides

#### INPUT



#### OUTPUT



Two Year Extended  
Warranty Available in  
the U.S.A. and Canada



**PERFORMANCE PLUS**

**POWER MIG® 140C Welding Capabilities**

Process	Wire Dia. (in.)	Wire Gauge / Diameter																		
		24ga.	22ga.	20ga.	18ga.	16ga.	14ga.	12ga.	10ga.	3/16"	1/4"	5/16"	3/8"	1/2"						
Flux-Cored Welding – Steel	.030															INNERSHIELD® NR-211-MP	SP	MP		
	.035															INNERSHIELD® NR-211-MP	SP	MP		
MIG Welding – Steel	.025	SUPERARC® L-56													SP					
	.030															SUPERARC® L-56		SP		
	.035															SUPERARC® L-56		SP		
MIG Welding – Aluminum	.035	SUPERGLAZE® 4043														SP				SP = Single Pass MP = Multiple Pass

L12603-4



KP2529-2 Shown

DRIVE ROLL AND WIRE GUIDES		
Product Number	Wire Diameter in. (mm)	Type/Process
<b>Drive Rolls</b> KP2529-1 KP2529-2 KP2529-3	.025 - .030 (0.6 - 0.8) .035 (0.9) .030 - .045 (0.8 - 1.1)	Smooth/MIG Smooth/MIG Knurled/Flux-Cored
<b>Inner Wire Guides</b> KP2531-1 KP2531-2	.025 - .035 (0.6 - 0.9) .045 (1.1)	All All

**RECOMMENDED ACCESSORIES**

**GENERAL OPTIONS**



**Welding Cart**  
Full-featured cart is designed to store and transport a welder, 80 cubic foot gas cylinder, welding cables and accessories. Includes an angled top shelf for easy access to welder controls, a lower tray for added storage space, a sturdy handle and a convenient cable wrap hanger.  
**Order K2275-1**



**Utility Cart**  
Heavy duty cart stores and transports welder, 150 cubic foot shielding gas cylinder, welding cables and accessories. Includes stable platforms for welder and gas bottle platform, lower tray for added storage capacity and adjustable height handle.  
**Order K520**



**Small Canvas Cover**  
Protect your welder when not in use. Made from attractive red canvas that is flame retardant, mildew resistant and water repellent. Includes a convenient side pocket to hold your welding torch or gun.  
**Order K2377-1**



**Spot Timer Kit**  
This timer allows you to set a fixed weld time of up to 10 seconds that is initiated when you pull the gun trigger. Ideal for making consistent spot welds on thin sheet metal.  
**Order K2525-1**



**Accessory Bag**  
Canvas bag can be used to store your welding accessories and tools.  
**Order K3071-1**



**WIRE FEEDER OPTIONS**

**Magnum® PRO 100SG Spool Gun**  
Designed to easily feed 4 in. (102 mm) diameter 1 lb. (0.45 kg) spools of .030 in. (0.8 mm) or .035 in. (0.9 mm) diameter SuperGlaze® aluminum MIG wire. Includes gun, adapter kit, .035 in. (0.9 mm) contact tips (qty. 3), gas nozzle, and a 1 lb. (0.45 kg) spool of SuperGlaze® 4043 .035 in. (0.9 mm) MIG wire. Packaged in a convenient carrying case.  
**Order K3269-1**



**Welding Fume Extractors**  
Lincoln offers a wide variety of welding fume extraction environmental system solutions, ranging from portable systems easily wheeled around the shop to shop-wide central systems servicing many dedicated welding stations.  
**Request Publication E13.40**

**PRODUCT SPECIFICATIONS**

Product Name	Product Number	Input Power	Rated Output Current/Voltage/Duty Cycle	Input Current @ Rated Output	Output Range	H x W x D inches (mm)	Net Weight lbs. (kg)
POWER MIG® 140C	K2471-2	120/1/60	90A/19.5V/20%	20A	30-140 Amps DC 50-500 ipm WFS (1.3-12.7 m/min) Max. OCV: 33	14 x 10.15 x 18.6 (357 x 258 x 472)	58 (26.3)

For best welding results with Lincoln Electric equipment, always use Lincoln Electric consumables. Visit [www.lincolnelectric.com](http://www.lincolnelectric.com) for more details.

**CUSTOMER ASSISTANCE POLICY**

The business of The Lincoln Electric Company is manufacturing and selling high quality welding equipment, consumables, and cutting equipment. Our challenge is to meet the needs of our customers and to exceed their expectations. On occasion, purchasers may ask Lincoln Electric for information or advice about their use of our products. Our employees respond to inquiries to the best of their ability based on information provided to them by the customers and the knowledge they may have concerning the application. Our employees, however, are not in a position to verify the information provided or to evaluate the engineering requirements for the particular weldment. Accordingly, Lincoln Electric does not warrant or guarantee or assume any liability with respect to such information or advice. Moreover, the provision of such information or advice does not create, expand, or alter any warranty on our products. Any express or implied warranty that might arise from the information or advice, including any implied warranty of merchantability or any warranty of fitness for any customers' particular purpose is specifically disclaimed.

Lincoln Electric is a responsive manufacturer, but the selection and use of specific products sold by Lincoln Electric is solely within the control of, and remains the sole responsibility of the customer. Many variables beyond the control of Lincoln Electric affect the results obtained in applying these types of fabrication methods and service requirements.

Subject to Change – This information is accurate to the best of our knowledge at the time of printing. Please refer to [www.lincolnelectric.com](http://www.lincolnelectric.com) for any updated information.

