

FEATURES & SPECIFICATIONS

PRODUCT OVERVIEW

Building-mounted light for entrances, stairwells, corridors and other pedestrian areas.

Non-cutoff, and cutoff configurations.

CONSTRUCTION

Rugged, corrosion-resistant, die-cast aluminum back housing and hinged door frame. Castings are sealed with a one-piece gasket to inhibit the entrance of contaminants.

Dark bronze housing configured for mounting directly over a standard 4" outlet box or for surface wiring via any of three convenient 1/2" threaded conduit entry hubs. Anodized aluminum reflector.

ELECTRICAL SYSTEM

Ballast — Quad-tap, pulse start, 100% factory-tested, high power factor for 250W MH and 400W MH. Meets or exceeds the minimum efficiency required by the Energy Independence and Security Act of 2007 (EISA). Quad-tap, high-reactance, high power factor ballast for 150W.

Socket — Mogul-base socket for 250W and 400W MH. Medium-base socket for 150W.

LISTINGS

Listed and labeled to UL standards for wet locations.

25°C maximum ambient temperature.

WARRANTY

Fixtures are covered by Lithonia Lighting 24-month warranty against mechanical defects in manufacture.

Note: Specifications subject to change without notice.

Catalog Number
Notes
Type

Contractor Select

Building Mounted




TWR1




TWR2C

150-400W




TWR1




250W Depth: 9-3/8 (23.8) 400W Depth: 12-1/2 (31.8)

TWR2



TWR1C



TWR2C

All dimensions are inches (centimeters).

ORDERING INFORMATION

Catalog Number	UPC	Description	Wattage	Lamp Source	Voltage	Finish	Lamp Included	Approx. Weight (lbs)	Pallet Qty	Standard Carton Qty
TWR1 150M TB LPI	745975146000	Non-cutoff	150	MH	120/208/240/277	Dark bronze	Y	18	36	1
TWR1 150S TB LPI	784231137017	Non-cutoff	150	HPS	120/208/240/277	Dark bronze	Y	18	36	1
TWR1C 150M TB LPI	745975151004	Cutoff	150	MH	120/208/240/277	Dark bronze	Y	18	32	1
TWR2 250M TB SCWA LPI	745975145324	Non-cutoff	250 ¹	MH	120/208/240/277	Dark bronze	Y	26	24	1
TWR2C 250M TB SCWA LPI	745975145379	Cutoff	250 ¹	MH	120/208/240/277	Dark bronze	Y	21	16	1
TWR2 400M TB SCWA LPI	745975145348	Non-cutoff	400 ¹	MH	120/208/240/277	Dark bronze	Y	31	24	1
TWR2C 400M TB SCWA LPI	745975145423	Cutoff	400 ¹	MH	120/208/240/277	Dark bronze	Y	25	16	1

Notes

¹ These wattages do not comply with California Title 20 regulations.

Building-Mounted Lighting
