



Material Safety Data Sheet

HAZARD WARNINGS	RISK PHRASES	PROTECTIVE CLOTHING
	Highly toxic; do not ingest or inhale. Avoid all contact with this material. Hygroscopic -- keep container tightly sealed.	

Section I. Chemical Product and Company Identification

Chemical Name	Nicotine		
Catalog Number	N0079	Supplier	TGI America 9211 N. Harborage St. Portland OR 1-800-423-8616
Synonym	(-)-Nicotine		
Chemical Formula	C ₁₀ H ₁₄ N ₂		
CAS Number	54-11-5	In case of Emergency Call	Chemtec® (800) 424-9300 (U.S.) (703) 527-3887 (International)

Section II. Composition and Information on Ingredients

Chemical Name	CAS Number	Percent (%)	TLV/PEL	Toxicology Data
Nicotine	54-11-5	Min. 95.0 (GC)	Not available.	Rat LD ₅₀ (oral) 50mg/kg Rat LD ₅₀ (dermal) 140mg/kg Mouse LD ₅₀ (oral) 3340mg/kg

Section III. Hazards Identification

Acute Health Effects	Highly toxic if ingested or inhaled. Avoid prolonged contact with this material. Overexposure may result in serious illness or death. Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.
Chronic Health Effects	<p>CARCINOGENIC EFFECTS : Not available.</p> <p>MUTAGENIC EFFECTS : Not available.</p> <p>TERATOGENIC EFFECTS : Not available.</p> <p>DEVELOPMENTAL TOXICITY Reproductive effects: Rat TDLo (implant) 125mg/kg, female 6-12 Days of pregnancy. Specific developmental abnormalities - Cardiofacial (including nose and tongue) Rat TDLo (implant) 125mg/kg, female 6-12 Days of pregnancy. Specific developmental abnormalities - Cardiovascular (circulatory) system. Specific developmental abnormalities - Respiratory system. Woman TDLo (Oral) 40µg/kg, female 24 weeks of pregnancy. Specific developmental abnormalities - Cardiovascular (circulatory) system. Repeated exposure to an highly toxic material may produce general deterioration of health by an accumulation in one or many human organs.</p>

Section IV. First Aid Measures

Eye Contact	Check for and remove any contact lenses. In case of contact, immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.
Skin Contact	In case of contact, immediately flush skin with plenty of water. Remove contaminated clothing and shoes. Wash clothing before reuse. Thoroughly clean shoes before reuse. Get medical attention.
Inhalation	If the victim is not breathing, perform mouth-to-mouth resuscitation. Loosen tight clothing such as a collar, tie, belt or waistband. If breathing is difficult, oxygen can be administered. Seek medical attention if respiration problems do not improve.
Ingestion	INDUCE VOMITING by sticking finger in throat. Lower the head so that the vomit will not reenter the mouth and throat. Loosen tight clothing such as a collar, tie, belt or waistband. If the victim is not breathing, perform mouth-to-mouth resuscitation. Examine the lips and mouth to ascertain whether the tissues are damaged, a possible indication that the toxic material was ingested; the absence of such signs, however, is not conclusive. SEEK IMMEDIATE MEDICAL ATTENTION in case of ingestion of a radioactive material.

Section V. Fire and Explosion Data

Flammability	May be combustible at high temperature.	Auto-Ignition	Not available.
Flash Points	101°C (213.8°F).	Flammable Limits	Not available.
Combustion Products	These products are toxic carbon oxides (CO, CO ₂), nitrogen oxides (NO, NO ₂).		
Fire Hazards	Not available.		
Explosion Hazards	Risks of explosion of the product in presence of mechanical impact: Not available. Risks of explosion of the product in presence of static discharge: Not available.		
Fire Fighting Media and Instructions	SMALL FIRE: Use DRY chemical powder. LARGE FIRE: Use water spray, fog or foam. DO NOT use water jet.		


Section VI. Accidental Release Measures

Spill Cleanup Instructions	Highly toxic liquid. Stop leak if without risk. DO NOT get water inside container. DO NOT touch spilled material. Use water spray to reduce vapors. Prevent entry into sewers, basements or confined areas; dike if needed. Eliminate all sources of ignition. Consult federal, state, and/or local authorities for assistance on disposal.
----------------------------	--

Section VII. Handling and Storage

Handling and Storage Information	HIGHLY TOXIC. Keep locked up.. Keep away from heat. Mechanical exhaust required. When not in use, tightly seal the container and store in a dry, cool place. Avoid excessive heat and light. DO NOT ingest. Do not breathe gas/fumes/vapor/spray. Wear suitable protective clothing. If ingested, seek medical advice immediately and show the container or the label. Treat symptomatically and supportively. Always store away from incompatible compounds such as oxidizing agents, moisture.
----------------------------------	---

Section VIII. Exposure Controls/Personal Protection

Engineering Controls	Provide exhaust ventilation or other engineering controls to keep the airborne concentrations of vapors below their respective threshold limit value. Ensure that eyewash station and safety shower is proximal to the work-station location.
Personal Protection	Splash goggles. Lab coat. Vapor respirator. Boots. Gloves. Suggested protective clothing might not be sufficient; consult a specialist BEFORE handling this product. Be sure to use a MSHA/NIOSH approved respirator or equivalent.
	
Exposure Limits	Not available.

Section IX. Physical and Chemical Properties

Physical state @ 20°C	Liquid. (Colorless to pale yellow, oily.)	Solubility	Miscible with water below 60°C. Very soluble in alcohol, chloroform, ether, petroleum ether, kerosene, oils.
Specific Gravity	1.0097 (water=1)	Partition Coefficient	Not available.
Molecular Weight	162.23	Vapor Pressure	0 kPa (@ 20°C)
Boiling Point	247°C (476.6°F) (partial decomposition)	Vapor Density	5.61 (Air = 1)
Melting Point	-79°C (-110.2°F)	Volatility	Not available.
Refractive Index	1.5282 @ 20°C	Odor	Slightly fishy, develops odor of pyridine.
Critical Temperature	Not available.	Taste	Acrid, Burning.
Viscosity	Not available.		

Section X. Stability and Reactivity Data

Stability	This material is stable if stored under proper conditions. (See Section VII for instructions)
Conditions of Instability	Avoid excessive heat and light.
Incompatibilities	Reactive with oxidizing agents, moisture.

Section XI. Toxicological Information

RTECS Number	QS5250000
Routes of Exposure	Eye Contact. Ingestion. inhalation.
Toxicity Data	Rat LD ₅₀ (oral) 50mg/kg Rat LD ₅₀ (dermal) 140mg/kg Mouse LD ₅₀ (oral) 3340mg/kg
Chronic Toxic Effects	CARCINOGENIC EFFECTS : Not available. MUTAGENIC EFFECTS : Not available. TERATOGENIC EFFECTS : Not available. DEVELOPMENTAL TOXICITY Reproductive effects: Rat TDLo (implant) 125mg/kg, female 6-12 Days of pregnancy. Specific developmental abnormalities - Cardiofacial (including nose and tongue) Rat TDLo (implant) 125mg/kg, female 6-12 Days of pregnancy. Specific developmental abnormalities - Cardiovascular (circulatory) system. Specific developmental abnormalities - Respiratory system. Woman TDLo (Oral) 40µg/kg, female 24 weeks of pregnancy. Specific developmental abnormalities - Cardiovascular (circulatory) system. Repeated exposure to an highly toxic material may produce general deterioration of health by an accumulation in one or many human organs.
Acute Toxic Effects	Highly toxic if ingested or inhaled. Avoid prolonged contact with this material. Overexposure may result in serious illness or death. Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.


Section XII. Ecological Information

Ecotoxicity	Not available.
Environmental Fate	Not available.

Section XIII. Disposal Considerations

Waste Disposal	Recycle to process, if possible. Consult your local regional authorities. You may be able to dissolve or mix material with a combustible solvent and burn in a chemical incinerator equipped with an afterburner and scrubber system. Observe all federal, state and local regulations when disposing of the substance.
----------------	---

Section XIV. Transport Information

DOT Classification	CLASS 6.1: Poisonous material.
PIN Number	UN1654
Proper Shipping Name	Nicotine.
Packing Group (PG)	II
DOT Pictograms	

Section XV. Other Regulatory Information and Pictograms

TSCA Chemical Inventory (EPA)	This compound is ON the EPA Toxic Substances Control Act (TSCA) inventory list.
WHMIS Classification (Canada)	CLASS D-1A: Material causing immediate and serious toxic effects (VERY TOXIC).
EINECS Number (EEC)	200-193-3
EEC Risk Statements	R23/24/25- Toxic by inhalation, in contact with skin and if swallowed.
Japanese Regulatory Data	Not available.

Section XVI. Other Information**Version 1.0****Validated on 12/19/2000.****Printed 2/26/2005.****Notice to Reader**

TCI laboratory chemicals are for research purposes only and are NOT intended for use as drugs, food additives, households, or pesticides. The information herein is believed to be correct, but does not claim to be all inclusive and should be used only as a guide. Neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All chemical reagents must be handled with the recognition that their chemical, physiological, toxicological, and hazardous properties have not been fully investigated or determined. All chemical reagents should be handled only by individuals who are familiar with their potential hazards and who have been fully trained in proper safety, laboratory, and chemical handling procedures. Although certain hazards are described herein, we can not guarantee that these are the only hazards which exist. Our MSDS sheets are based only on data available at the time of shipping and are subject to change without notice as new information is obtained. Avoid long storage periods since the product is subject to degradation with age and may become more dangerous or hazardous. It is the responsibility of the user to request updated MSDS sheets for products that are stored for extended periods. Disposal of unused product must be undertaken by qualified personnel who are knowledgeable in all applicable regulations and follow all pertinent safety precautions including the use of appropriate protective equipment (e.g. protective goggles, protective clothing, breathing equipment, facial mask, fume hood). For proper handling and disposal, always comply with federal, state, and local regulations.

Printed 2/26/2005.