

NEW

Milwaukee[®]

M18 FUEL[™]

DRIVEN TO OUTPERFORM.[™]



POWER TO GRIND

UP TO
2X
MORE
RUN-TIME

UP TO
10X
LONGER
TOOL LIFE

4-1/2" / 5" Grinder
Paddle Switch,
No-Lock Kit

45L202

4-1/2" / 5" Grinder
Slide Switch,
Lock-On Kit

45L198

RED LITHIUM[™]
XC4.0




DRIVEN TO OUTPERFORM.™

M18 FUEL™ is engineered for the most demanding tradesmen in the world. Delivering unrivaled performance in a compact structure, all M18 FUEL™ products feature three Milwaukee®-exclusive innovations — the POWERSTATE™ Brushless Motor, REDLITHIUM™ Battery Pack and REDLINK PLUS™ Intelligence Hardware and Software — that deliver unmatched power, run-time and durability. Simply put, the M18 FUEL™ Grinder is the world's first true cordless grinder on the market that delivers on its promise.

M18 FUEL


1 POWERSTATE™ BRUSHLESS MOTOR

- Milwaukee® Designed and Built Brushless Motor
- Outperforms All Leading Competitors
- Up to 10X Longer Motor Life



2 REDLINK PLUS™ INTELLIGENCE

- Most Advanced Electronic System on the Market for Maximum Performance
- Total System Communication with Overload Protection Increases Tool Life
- Built-in Fuel Gauge Displays Remaining Charge



3 REDLITHIUM™ XC4.0 BATTERY PACK

- Up to 2X Run-Time
- Up to 2X More Recharges than Leading Competitor
- Operates Below -18° C / 0° F




POWER TO GRIND

UP TO 2X MORE RUN-TIME

UP TO 10X LONGER TOOL LIFE

POWER TO GRIND

WORLD'S FIRST CORDLESS GRINDER WITH CORDED PERFORMANCE




APPLICATION	CORDLESS CUT-OFF TOOLS	M18 FUEL & CORDED GRINDERS
Cutting	✓	✓
Grinding	X	✓
Surface Prep	X	✓

MORE RUN-TIME



- REDLITHIUM™ XC4.0 Batteries deliver 2X more run-time per charge than any competitive lithium-ion battery
- POWERSTATE™ Brushless Motor creates less friction and sparking, providing a more efficient use of battery power

LONGER TOOL LIFE



- Premium Gearing System has the same metal housing and gearing system as high performance corded grinders
- POWERSTATE™ Brushless Motor has no wearable parts, which keeps the motor running longer without needing service
- REDLINK PLUS™ Intelligence has total system communication with overload protection and electronic clutch

SPECIFICATIONS AND MODELS

	45L202	45L198
	Paddle Switch, No-Lock	Slide Switch, Lock-On
Wheel Diameter	4-1/2" / 5"	4-1/2" / 5"
Spindle	5/8" – 11"	5/8" – 11"
Speed	8,500 RPM	8,500 RPM
Overload Protection	YES	YES
Electronic Clutch	YES	YES
Anti-Vibration Handle	YES	YES
100% Tool-Free Accessory Change	YES	YES
100% Tool-Free Adjustable Guard	YES	YES
Available Options	<p>45L202 TOOL-ONLY: 2780-20 4-1/2" / 5" Grinder Paddle Switch, No-Lock</p> <p>45L201 KIT – 1 BATTERY: 2780-20 4-1/2" / 5" Grinder Paddle Switch, No-Lock; (1) M18™ REDLITHIUM™ XC4.0 Extended Capacity Battery Pack, M12™ and M18™ Multi-Voltage Charger, and Carrying Case</p> <p>45L199 KIT – 2 BATTERIES: 2780-20 4-1/2" / 5" Grinder Paddle Switch, No-Lock; (2) M18™ REDLITHIUM™ XC4.0 Extended Capacity Battery Packs, M12™ and M18™ Multi-Voltage Charger, and Carrying Case</p>	<p>45L198 TOOL-ONLY: 2781-20 4-1/2" / 5" Grinder Slide Switch, Lock-On</p> <p>45L197 KIT – 1 BATTERY: 2781-20 4-1/2" / 5" Grinder Slide Switch, Lock-On; (1) M18™ REDLITHIUM™ XC4.0 Extended Capacity Battery Pack, M12™ and M18™ Multi-Voltage Charger, and Carrying Case</p> <p>45L196 KIT – 2 BATTERIES: 2781-20 4-1/2" / 5" Grinder Slide Switch, Lock-On; (2) M18™ REDLITHIUM™ XC4.0 Extended Capacity Battery Packs, M12™ and M18™ Multi-Voltage Charger, and Carrying Case</p>



