

# NOR-LAKE<sup>®</sup> SCIENTIFIC COMPACT TABLE TOP ALL-REFRIGERATOR OR FREEZER

Designed to meet the demanding requirements for scientific and laboratory research. Advanced engineered design incorporates the latest in cabinet, refrigeration, temperature control and monitoring features. Provides energy efficient, convenient, safe and reliable performance for optimal storage temperature environments necessary for a wide range of life science, pharmacy, biological, medical and clinical and industrial applications.

#### Refrigerator Standard Product Features Model LR021WWW/0:

- Adjustable temperature control range +2°C to +8°C
- Automatic defrost
- Front-mounted lock
- Fully-finished white cabinet
- Leveling feet (2)
- R134a refrigerant
- Removable wire shelf (1)
- Reversible door
- 100% CFC free
- Warranties: 12 months parts

#### Freezer Standard Product Features Model LF021WWW/0M:

- Adjustable temperature control range -10°C to -20°C
- Front-mounted lock
- Fully finished white cabinet
- Leveling feet (2)
- Manual defrost
- One piece interior liner
- R134a refrigerant
- Removable wire shelf (1)
- Reversible door
- 100% CFC free
- Warranties: 12 months parts

#### OPTIONAL FEATURES

- Digital Thermometer Monitor With Alarm (Field Install)



FRONT VIEW



Optional Digital Thermometer  
Monitor With Alarm



INTERIOR VIEW

NORLAKE<sup>®</sup> SCIENTIFIC




Committed to our environment




Nor-Lake, Inc  
Registered to ISO 9001:2008  
File No. 10001816

NOR-LAKE SCIENTIFIC  
A Division of  
NOR-LAKE, INCORPORATED  
727 Second Street  
P.O. Box 248  
Hudson, Wisconsin 54016  
800-477-5253  
715-386-2323  
800-388-5253 PARTS  
715-386-4290 FAX  
[www.norlakescientific.com](http://www.norlakescientific.com)



TOP VIEW  
LR021WWW/0  
LF021WWW/0



FRONT VIEW  
LR021WWW/0  
LF021WWW/0

Models	SPECIFICATIONS	
	LR021WWW/0	LF021WWW/0M
	Refrigerator	Freezer
Crated Height (in) (cm)	22 (56)	22 (56)
Crated Width (in) (cm)	18 (46)	18 (46)
Crated Depth (in) (cm)	20 (51)	20 (51)
Crated Weight (lbs) (kg)	55 (25)	55 (25)
Interior Height (in) (cm)	16.5 (42)	14.63 (37)
Interior Width (in) (cm)	14.18 (36)	12.38 (31)
Interior Depth (in) (cm)	14.5 (37)	14.5 (37)
Overall Height (in) (cm)	20.18 (51)	20.18 (51)
Overall Width (in) (cm)	17.38 (44)	17.38 (44)
Overall Depth (in) (cm)	19.0 (48)	19.0 (48)
Gross Cubage (ft <sup>3</sup> ) (L)	1.6 (45.3)	1.42 (40.2)
Number of Shelves	1	1
Shelf Area (ft <sup>2</sup> ) (m <sup>2</sup> )	1.1 (.1)	1.0 (.09)
Number of Leveling Feet	2	2
Condensing Unit Size	1/12 HP	1/10 HP
Refrigerant	R-134a	R-134a
Electrical Characteristics	115/60/1	115/60/1
Cord and Plug Supplied	6' (5-15P)	6' (5-15P)
Maximum Fuse Size	15 Amps	15 Amps
Total Amp Draw /0	1.2	1.2

Specifications subject to change without notice.

Voltage Model Suffix Code	Voltage Description	NEMA Plug	NEMA Receptacle
0/	115V, 1PH, 60Hz	5-15P	5-15R



NORLAKE SCIENTIFIC

Revision Date: 04/13  
©2013 NOR-LAKE, INC.  
Printed in the U.S.A.  
Part Number: 151527

