



PROTECTIVE INDUSTRIAL PRODUCTS

17-SD200 Specification Sheet

UNCOATED GLOVES WITH DYNEEMA®

PRODUCT DESCRIPTION:

Gloves with 100% spun Dyneema®, 13 gauge, light weight.

- Washable.
- Seamless construction.
- Can be used as glove liners.
- Color coded hems for easy size identification.
- Made from component materials that comply with Federal Regulations for food contact 21CFR, 170-199.
- Dyneema® is a brand of polyethylene fibers that are 10 to 15 times stronger than steel, more durable than polyester and a strength that is 40% greater than aramid fiber.

Applications:

Ideal for food processing. Can also be used as glove liners.

TECHNICAL DATA:

Material: Dyneema®

Construction: 13 gauge

Color: White

Cuff Style: Continuous knit

Available Sizes: XS - XL

Packaging: 12 pairs per dozen, 6 dozen per case

Case Dimensions: (cm) 50.8 x 33 x 40.6 / (in): 20.0 x 13.0 x 16.0

Case Weight: 5.1 lbs / 2.3 kg

Country of Origin/Harmonization Code: USA/6116.93.8800

Laundering Instructions:

Recommend washing gloves in slightly warm water not exceeding 40° C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Hang dry; tumble dry is not recommended.

CUT RESISTANCE PROPERTIES:


- Method ASTM F1790-04
- 518 GRAMS
- ANSI/ISEA 105-2000 Level 2 Cut Resistance
- EN388 Level 3 Cut Resistance

BARCODE #	DOZEN	CASE
17-SD200/XL	01616314065353	02616314065352
17-SD200/L	01616314059178	02616314059177
17-SD200/M	01616314065339	02616314065338
17-SD200/S	01616314065346	02616314065345
17-SD200/XS	01616314065360	02616314065369



DIMENSIONS:

Size Available	XS	S	M	L	XL
Over Length (cm) – A	17.8	19.1	22.9	24.1	25.4
(in)	7.0	7.5	9.0	9.5	10.0
Palm Width (cm) – B	8.9	8.9	10.2	10.2	10.8
(in)	3.5	3.5	4.0	4.0	4.25
Hem Color	Blue	White	Red	Yellow	Green



This document is the property of PIP and the information contained herein is proprietary to PIP.