



PROFESSIONAL



PROFESSIONAL

Clean Floors...No Problem

Automatic Floor Scrubber Solution Concentrate

When you're trying to eliminate soot, smoke damage or other tough grime from floors, reach for this heavy-duty formulation designed for use in floor scrubbing machines and pressure washers. Ideal for removing soil from smoke and fire damage, it contains special optical brighteners to brighten surfaces as it cleans.

Benefits:

- Cleans all hard surface flooring
• Concentrated, industrial strength formula
• Controlled-foam formulation
• Excellent for cleaning up after fire/smoke damage

Applications:

- Masonry floors
• Warehouses
• Building exteriors

Directions for Use:

General industrial applications: Dilute 1 part product with 5 to 10 parts hot or cold water and spray or mop on surface. Allow contact time of 3 to 5 minutes and scrub. Rinse with water.

Smoke and fire damage: Dilute 1 part product with 3 parts hot water. Apply to soot or carbon soils with brush or low pressure spray. Amount of solution required depends upon degree of soil and porosity of the surface. Rinse with water to prevent re-deposition of soils.

Industrial floors and concrete: Dilute 1 part product with 3 to 5 parts hot water and apply with mop or pressure sprayer. Scrub using a floor machine or deck brush. Allow a contact time of 5 to 10 minutes, but do not allow to dry. Pick up solution with wet pick-up vacuum; a mop and wringer; or flush to floor drain. Rinse floor thoroughly.



Base Code: R030

For use in automatic scrubbers: Add to the solution tank at a dilution of one part product with up to 64 parts water, depending on amount of soil. Extremely soiled areas should be pre-treated with product mixed 1 part with 10 parts water, before scrubbing. Pick up all residues of detergent solution and dissolved soils with vacuum pick-up or rinse thoroughly with mop and wringer.

Companion Products:

Base Code

- Exterior/Interior Masonry Floor SealerR041
Sweeping CompoundR035
Heavy-Duty Alkaline Cleaner.....R085



1-877-7ZEPRO | www.zepprofessional.com

Hard Floor Care



Specifications:

Physical Form	Thin, water-based liquid
Color	Clear, lavender
Odor	Mild, clean
pH	12.5 - 13.0
pH (use dilution of 1:10)	12.0 - 12.5
Density - Specific Gravity	9.08 lbs./gal. - 1.089
Flash Point (TCC)	None
Shelf Life	1 year minimum
D.O.T. Shipping Label	None



Packaging Information:

SKU	Package Quantity	Weight (lbs)	Length (")	Height (")	Width (")
R03024	4-1 gal/case	40	13.00	13.00	12.50
R03035	5 gal pail	48	12.00	14.50	12.00
R03050	20 gal drum	191	16.00	27.50	16.00
R03085	55 gal drum	519	23.50	35.10	23.50

Safety:

Please make sure you have read and understand the product label and MSDS before using this product. MSDSs are available at www.zepprofessional.com. Avoid contact with eyes, skin and clothing. Do not ingest. Avoid breathing vapors, spray or mists. Use only with adequate ventilation. Keep container closed. Wash thoroughly after handling. Wash contaminated clothing before reusing. Observe label precautions.

