





# Material Safety Data Sheet

HAZARD WARNINGS	RISK PHRASES	PROTECTIVE CLOTHING
  	<p><b>Corrosive to eyes and skin on contact.</b>  <b>Toxic compound, do not ingest or inhale. Avoid all contact with this material.</b>  <b>Combustible material; avoid heat and sources of ignition.</b>  <b>CARCINOGEN. MINIMIZE EXPOSURE.</b>  <b>Desiccant.</b></p>	

## Section I. Chemical Product and Company Identification

Chemical Name	<b>2-Allylphenol</b>		
Catalog Number	A0233	Supplier	TCI America 9211 N. Harborgate St. Portland OR 1-800-423-8616
Synonym	Not available.		
Chemical Formula	CH <sub>2</sub> :CHCH <sub>2</sub> C <sub>6</sub> H <sub>4</sub> OH		
CAS Number	1745-81-9	In case of Emergency Call	<b>Chemtrec®</b> <b>(800) 424-9300 (U.S.)</b> <b>(703) 527-3887</b> <b>(International)</b>

## Section II. Composition and Information on Ingredients

Chemical Name	CAS Number	Percent (%)	TLV/PEL	Toxicology Data
2-Allylphenol	1745-81-9	Min. 97.0 (GC)	This chemical is classified as a carcinogen. There is no acceptable exposure limit for a carcinogen.	Rat LD <sub>50</sub> (oral) 205 mg/kg

## Section III. Hazards Identification

Acute Health Effects	<p>Corrosive to skin, eyes, and respiratory system. Liquid or spray mist may produce tissue damage, particularly in mucous membranes of the eyes, mouth and respiratory tract. Skin contact may produce burns. Eye contact can result in corneal damage or blindness. Inhalation of the spray mist may produce severe irritation of respiratory tract, characterized by coughing, choking, or shortness of breath. Corrosive materials may cause serious injury if ingested. Toxic if ingested or inhaled. Avoid prolonged contact with this material. Overexposure may result in serious illness or death.</p> <p>Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.</p>
Chronic Health Effects	<p><b>CARCINOGENIC EFFECTS</b> : Carcinogenic by RTECS criteria.  <b>MUTAGENIC EFFECTS</b> : Not available.  <b>TERATOGENIC EFFECTS</b> : Tumorigenic Effects.            Mouse TD Skin 3360 mg/kg/12 weeks intermittent  <b>TOXIC Effects:</b>            Tumorigenic - Neoplastic by RTECS criteria            Skin and Appendages - Tumors            Mouse TDLo Skin 8400 mg/kg/30 weeks intermittent  <b>TOXIC Effects:</b>            Tumorigenic - Carcinogenic by RTECS criteria            Skin and Appendages - Tumors  <b>DEVELOPMENTAL TOXICITY</b> : Not available.</p>

## Section IV. First Aid Measures

Eye Contact	Check for and remove any contact lenses. In case of contact, immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.
Skin Contact	In case of contact, immediately flush skin with plenty of water. Remove contaminated clothing and shoes. Wash clothing before reuse. Thoroughly clean shoes before reuse. Get medical attention.
Inhalation	If the victim is not breathing, perform mouth-to-mouth resuscitation. Loosen tight clothing such as a collar, tie, belt or waistband. If breathing is difficult, oxygen can be administered. Seek medical attention if respiration problems do not improve.
Ingestion	DO NOT INDUCE VOMITING. Loosen tight clothing such as a collar, tie, belt or waistband. If the victim is not breathing, perform mouth-to-mouth resuscitation. Examine the lips and mouth to ascertain whether the tissues are damaged, a possible indication that the toxic material was ingested; the absence of such signs, however, is not conclusive.

**Section V. Fire and Explosion Data**

Flammability	Combustible.	Auto-Ignition	Not available.
Flash Points	88°C (190.4°F).	Flammable Limits	Not available.
Combustion Products	These products are toxic carbon oxides (CO, CO <sub>2</sub> ).		
Fire Hazards	Not available.		
Explosion Hazards	Risks of explosion of the product in presence of mechanical impact: Not available. Risks of explosion of the product in presence of static discharge: Not available.		
Fire Fighting Media and Instructions	Combustible liquid. SMALL FIRE: Use DRY chemical powder. LARGE FIRE: Use water spray, fog or foam. DO NOT use water jet. Consult with local fire authorities before attempting large scale fire-fighting operations.		


**Section VI. Accidental Release Measures**

Spill Cleanup Instructions	Corrosive material. Toxic material. Combustible material. Carcinogenic material. Desiccate. Keep away from heat. Mechanical exhaust required. Stop leak if without risk. Absorb with DRY earth, sand or other non-combustible material. DO NOT get water inside container. DO NOT touch spilled material. Use water spray curtain to divert vapor drift. Prevent entry into sewers, basements or confined areas; dike if needed. Consult federal, state, and/or local authorities for assistance on disposal.
----------------------------	--

**Section VII. Handling and Storage**

Handling and Storage Information	CORROSIVE. TOXIC. COMBUSTIBLE. CARCINOGEN. DESICCANT. Keep container dry. Keep away from heat. Mechanical exhaust required. Avoid excessive heat and light. Do not breathe gas/fumes/vapor/spray. Never add water to this product. Wear suitable protective clothing. If you feel unwell, seek medical attention and show the label when possible. Treat symptomatically and supportively.
----------------------------------	--

**Section VIII. Exposure Controls/Personal Protection**

Engineering Controls	Provide exhaust ventilation or other engineering controls to keep the airborne concentrations of vapors below their respective threshold limit value. Ensure that eyewash station and safety shower is proximal to the work-station location.
Personal Protection	Splash goggles. Lab coat. Vapor respirator. Boots. Gloves. Suggested protective clothing might not be sufficient; consult a specialist BEFORE handling this product. Be sure to use a MSHA/NIOSH approved respirator or equivalent.
	
Exposure Limits	This chemical is classified as a carcinogen. There is no acceptable exposure limit for a carcinogen.

**Section IX. Physical and Chemical Properties**

Physical state @ 20°C	Liquid. (Clear, Light Yellow.)	Solubility	Not available.
Specific Gravity	1.02 (water=1)		
Molecular Weight	134.18	Partition Coefficient	Not available.
Boiling Point	220°C (428°F)	Vapor Pressure	Not available.
Melting Point	Not available.	Vapor Density	Not available.
Refractive Index	1.543 - 1.547	Volatility	Not available.
Critical Temperature	Not available.	Odor	Not available.
Viscosity	Not available.	Taste	Not available.

**Section X. Stability and Reactivity Data**

Stability	This material is stable if stored under proper conditions. (See Section VII for instructions)
Conditions of Instability	Avoid excessive heat and light.
Incompatibilities	Reactive with strong oxidizing agents, acid chlorides, and acid anhydrides.

**Section XI. Toxicological Information**

RTECS Number	SJ3850000
Routes of Exposure	Eye Contact. Ingestion. Inhalation. Skin contact.
Toxicity Data	Rat LD <sub>50</sub> (oral) 205 mg/kg
Chronic Toxic Effects	<p><b>CARCINOGENIC EFFECTS</b> : Carcinogenic by RTECS criteria.  <b>MUTAGENIC EFFECTS</b> : Not available.  <b>TERATOGENIC EFFECTS</b> : Tumorigenic Effects.            Mouse TD Skin 3360 mg/kg/12 weeks intermittent            TOXIC Effects:            Tumorigenic – Neoplastic by RTECS criteria            Skin and Appendages – Tumors            Mouse TDLo Skin 8400 mg/kg/30 weeks intermittent            TOXIC Effects:            Tumorigenic – Carcinogenic by RTECS criteria            Skin and Appendages – Tumors  <b>DEVELOPMENTAL TOXICITY</b> : Not available.</p>
Acute Toxic Effects	<p>Corrosive to skin, eyes, and respiratory system. Liquid or spray mist may produce tissue damage, particularly in mucous membranes of the eyes, mouth and respiratory tract. Skin contact may produce burns. Eye contact can result in corneal damage or blindness. Inhalation of the spray mist may produce severe irritation of respiratory tract, characterized by coughing, choking, or shortness of breath. Corrosive materials may cause serious injury if ingested.            Toxic if ingested or inhaled. Avoid prolonged contact with this material. Overexposure may result in serious illness or death.            Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.</p>



**Section XII. Ecological Information**

Ecotoxicity	Not available.
Environmental Fate	Not available.

**Section XIII. Disposal Considerations**

Waste Disposal	Recycle to process, if possible. Consult your local regional authorities. You may be able to dissolve or mix material with a combustible solvent and burn in a chemical incinerator equipped with an afterburner and scrubber system. Observe all federal, state and local regulations when disposing of the substance.
----------------	---

**Section XIV. Transport Information**

DOT Classification	DOT Class 8: Corrosive material DOT Class 6.1: Toxic material
PIN Number	UN2922
Proper Shipping Name	Corrosive liquids, toxic, n.o.s.
Packing Group (PG)	III
DOT Pictograms	 

**Section XV. Other Regulatory Information and Pictograms**

TSCA Chemical Inventory (EPA)	This compound is <b>ON</b> the EPA Toxic Substances Control Act (TSCA) inventory list.
WHMIS Classification (Canada)	<p>CLASS B-3: Combustible liquid with a flash point between 37.8°C (100°F) and 93.3°C (200°F).            CLASS D-2B: Material causing other toxic effects (TOXIC).            CLASS E: Corrosive liquid.            On DSL</p>
EINECS Number (EEC)	217-119-0
EEC Risk Statements	<p>R23/24/25- Toxic by inhalation, in contact with skin and if swallowed.            R34- Causes burns.</p>
Japanese Regulatory Data	ENCS No. 3-2740 ; 3-2840

**Section XVI. Other Information**

**Version 1.0**  
**Validated on 2/20/2007.**  
**Printed 2/20/2007.**

**Notice to Reader**

TCI laboratory chemicals are for research purposes only and are NOT intended for use as drugs, food additives, households, or pesticides. The information herein is believed to be correct, but does not claim to be all inclusive and should be used only as a guide. Neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All chemical reagents must be handled with the recognition that their chemical, physiological, toxicological, and hazardous properties have not been fully investigated or determined. All chemical reagents should be handled only by individuals who are familiar with their potential hazards and who have been fully trained in proper safety, laboratory, and chemical handling procedures. Although certain hazards are described herein, we can not guarantee that these are the only hazards which exist. Our MSDS sheets are based only on data available at the time of shipping and are subject to change without notice as new information is obtained. Avoid long storage periods since the product is subject to degradation with age and may become more dangerous or hazardous. It is the responsibility of the user to request updated MSDS sheets for products that are stored for extended periods. Disposal of unused product must be undertaken by qualified personnel who are knowledgeable in all applicable regulations and follow all pertinent safety precautions including the use of appropriate protective equipment (e.g. protective goggles, protective clothing, breathing equipment, facial mask, fume hood). For proper handling and disposal, always comply with federal, state, and local regulations.

Printed 2/20/2007.