



# Material Safety Data Sheet

| HAZARD WARNINGS   | RISK PHRASES   | PROTECTIVE CLOTHING   |
|---|--|---|
|  | Harmful compound, minimize exposure.<br>Irritating to skin, eyes, and the respiratory system.<br>Light sensitive.<br>Stabilized with copper. |  |

## Section I. Chemical Product and Company Identification

|                  |   |                                 |   |
|------------------|---|---------------------------------|---|
| Chemical Name    | <b>Perfluorooctyl Iodide</b>                      |                                 |   |
| Catalog Number   | P1084   | Supplier                        | TCl America<br>9211 N. Harborgate St.<br>Portland OR<br>1-800-423-8616                    |
| Synonym          | Heptadecafluoro-1-iodoctane                       |                                 |   |
| Chemical Formula | CF <sub>3</sub> (CF <sub>2</sub> ) <sub>7</sub> I |                                 |   |
| CAS Number       | 507-63-1  | In case of<br>Emergency<br>Call | <b>Chemtrec®</b><br><b>(800) 424-9300 (U.S.)</b><br><b>(703) 527-3887 (International)</b> |

## Section II. Composition and Information on Ingredients

| Chemical Name         | CAS Number | Percent (%)       | TLV/PEL        | Toxicology Data                                   |
|-----------------------|------------|-------------------|----------------|---|
| Perfluorooctyl Iodide | 507-63-1   | Min. 98.0<br>(GC) | Not available. | Mouse LD <sub>50</sub> (intravenous)<br>7500mg/kg |

## Section III. Hazards Identification

|                        |   |
|------------------------|---|
| Acute Health Effects   | Harmful if ingested or inhaled. Minimize exposure to this material. Severe overexposure can result in injury or death. Irritating to eyes and skin on contact. Inhalation causes irritation of the lungs and respiratory system. Inflammation of the eye is characterized by redness, watering, and itching. Skin inflammation is characterized by itching, scaling, reddening, or, occasionally, blistering. Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound. |
| Chronic Health Effects | <b>CARCINOGENIC EFFECTS</b> : Not available.<br><b>MUTAGENIC EFFECTS</b> : Not available.<br><b>TERATOGENIC EFFECTS</b> : Not available.<br><b>DEVELOPMENTAL TOXICITY</b> Not available.<br>There is no known effect from chronic exposure to this product. Repeated or prolonged exposure to this compound is not known to aggravate existing medical conditions.  |

## Section IV. First Aid Measures

|              |   |
|--------------|---|
| Eye Contact  | Check for and remove any contact lenses. DO NOT use an eye ointment. Flush eyes with running water for a minimum of 15 minutes, occasionally lifting the upper and lower eyelids. Seek medical attention. Treat symptomatically and supportively.   |
| Skin Contact | After contact with skin, wash immediately with plenty of water. Gently and thoroughly wash the contaminated skin with running water and non-abrasive soap. Be particularly careful to clean folds, crevices, creases and groin. Cover the irritated skin with an emollient. Seek medical attention. Treat symptomatically and supportively. Wash any contaminated clothing before reusing.  |
| Inhalation   | If the victim is not breathing, perform artificial respiration. Loosen tight clothing such as a collar, tie, belt or waistband. If breathing is difficult, oxygen can be administered. Seek medical attention. Treat symptomatically and supportively.  |
| Ingestion    | INDUCE VOMITING by sticking finger in throat. Lower the head so that the vomit will not reenter the mouth and throat. Loosen tight clothing such as a collar, tie, belt, or waistband. If the victim is not breathing, administer artificial respiration. Examine the lips and mouth to ascertain whether the tissues are damaged, a possible indication that the toxic material was ingested; the absence of such signs, however, is not conclusive. Seek immediate medical attention and, if possible, show the chemical label. Treat symptomatically and supportively. |

## Section V. Fire and Explosion Data

|                     |   |                  |                |
|---------------------|---|------------------|----------------|
| Flammability        | Combustible.  | Auto-Ignition    | Not available. |
| Flash Points        | Not available.  | Flammable Limits | Not available. |
| Combustion Products | These products include toxic carbon oxides (CO,CO <sub>2</sub> ), halogenated compounds.<br>WARNING: Highly toxic HF gas is produced during combustion.   |                  |                |
| Fire Hazards        | No specific information is available regarding the flammability of this compound in the presence of various materials.  |                  |                |
| Explosion Hazards   | Risks of explosion of the product in presence of mechanical impact: Not available.<br>Risks of explosion of the product in presence of static discharge: Not available.<br>No additional information is available regarding the risks of explosion. |                  |                |

Continued on Next Page

Emergency phone number (800) 424-9300

Fire Fighting Media  
and Instructions

SMALL FIRE: Use DRY chemicals, CO<sub>2</sub>, water spray or foam.  
LARGE FIRE: Use water spray, fog or foam. DO NOT use water jet.

### Section VI. Accidental Release Measures

Spill Cleanup  
Instructions

Harmful material. Irritating material.  
Keep away from heat and sources of ignition. Mechanical exhaust required. Stop leak if without risk. If the product is in its solid form: Use a shovel to put the material into a convenient waste disposal container. If the product is in its liquid form: Absorb with an inert material and put the spilled material in an appropriate waste disposal. Finish cleaning the spill by rinsing any contaminated surfaces with copious amounts of water. Consult federal, state, and/or local authorities for assistance on disposal.

### Section VII. Handling and Storage

Handling and Storage  
Information

HARMFUL. IRRITANT. Keep away from heat and sources of ignition. Mechanical exhaust required. When not in use, tightly seal the container and store in a dry, cool place. Avoid excessive heat and light. DO NOT ingest. Do not breathe gas, fumes, vapor or spray. In case of insufficient ventilation, wear suitable respiratory equipment. If ingested, seek medical advice immediately and show the container or the label. Treat symptomatically and supportively. Avoid contact with skin and eyes.  
Always store away from incompatible compounds such as oxidizing agents, alkalis (bases).

### Section VIII. Exposure Controls/Personal Protection

Engineering Controls

Provide exhaust ventilation or other engineering controls to keep the airborne concentrations of vapors below their respective threshold limit value. Ensure that eyewash station and safety shower is proximal to the work-station location.

Personal Protection

Splash goggles. Lab coat. Vapor respirator. Boots. Gloves. A MSHA/NIOSH approved respirator must be used to avoid inhalation of the product. Suggested protective clothing might not be sufficient; consult a specialist BEFORE handling this product.



Exposure Limits

Not available.

### Section IX. Physical and Chemical Properties

|                       |                               |                       |                |
|-----------------------|-------------------------------|-----------------------|----------------|
| Physical state @ 20°C | Colorless liquid.             | Solubility            | Not available. |
| Specific Gravity      | Not available.                |                       |                |
| Molecular Weight      | 545.97                        | Partition Coefficient | Not available. |
| Boiling Point         | 160 to 161°C (320 to 321.8°F) | Vapor Pressure        | Not available. |
| Melting Point         | 21°C (69.8°F)                 | Vapor Density         | Not available. |
| Refractive Index      | Not available.                | Volatility            | Not available. |
| Critical Temperature  | Not available.                | Odor                  | Not available. |
| Viscosity             | Not available.                | Taste                 | Not available. |

### Section X. Stability and Reactivity Data

|                           |   |
|---------------------------|---|
| Stability                 | This material is stable if stored under proper conditions. (See Section VII for instructions) |
| Conditions of Instability | May discolor on exposure to light. Avoid excessive heat and light.                            |
| Incompatibilities         | Reactive with strong oxidizing agents, strong alkalis (bases).                                |

### Section XI. Toxicological Information

|                       |   |
|-----------------------|---|
| RTECS Number          | RG9700050   |
| Routes of Exposure    | Eye contact. Inhalation. Ingestion. Skin contact.   |
| Toxicity Data         | Mouse LD <sub>50</sub> (intravenous) 7500mg/kg  |
| Chronic Toxic Effects | <b>CARCINOGENIC EFFECTS</b> : Not available.<br><b>MUTAGENIC EFFECTS</b> : Not available.<br><b>TERATOGENIC EFFECTS</b> : Not available.<br><b>DEVELOPMENTAL TOXICITY</b> Not available.<br>There is no known effect from chronic exposure to this product. Repeated or prolonged exposure to this compound is not known to aggravate existing medical conditions.  |
| Acute Toxic Effects   | Harmful if ingested or inhaled. Minimize exposure to this material. Severe overexposure can result in injury or death. Irritating to eyes and skin on contact. Inhalation causes irritation of the lungs and respiratory system. Inflammation of the eye is characterized by redness, watering, and itching. Skin inflammation is characterized by itching, scaling, reddening, or, occasionally, blistering. Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound. |

Continued on Next Page

Emergency phone number (800) 424-9300


**Section XII. Ecological Information**

|                    |                |
|--------------------|----------------|
| Ecotoxicity        | Not available. |
| Environmental Fate | Not available. |

**Section XIII. Disposal Considerations**

|                |  |
|----------------|--|
| Waste Disposal | Recycle to process, if possible. Consult your local or regional authorities. You may be able to dissolve or mix material with a combustible solvent and burn in a chemical incinerator equipped with an afterburner and scrubber system. Observe all federal, state, and local regulations when disposing of this substance. |
|----------------|--|

**Section XIV. Transport Information**

|                      |   |
|----------------------|---|
| DOT Classification   | Not a DOT controlled material (United States).                                    |
| PIN Number           | Not applicable.   |
| Proper Shipping Name | Not applicable.   |
| Packing Group (PG)   | Not applicable.   |
| DOT Pictograms       |  |

**Section XV. Other Regulatory Information and Pictograms**

|                               |   |
|-------------------------------|---|
| TSCA Chemical Inventory (EPA) | This compound is <b>ON</b> the EPA Toxic Substances Control Act (TSCA) inventory list.  |
| WHMIS Classification (Canada) | Not available.  |
| EINECS Number (EEC)           | 208-079-5   |
| EEC Risk Statements           | R20/21/22- Harmful by inhalation, in contact with skin and if swallowed.<br>R36/37/38- Irritating to eyes, respiratory system and skin. |
| Japanese Regulatory Data      | Not available.  |

**Section XVI. Other Information**

**Version 1.0**  
**Validated on 1/26/1998.**  
**Printed 3/19/2005.**

**Notice to Reader**

TCI laboratory chemicals are for research purposes only and are NOT intended for use as drugs, food additives, household, or pesticides. The information herein is believed to be correct, but does not claim to be all inclusive and should be used only as a guide. Neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All chemical reagents must be handled with the recognition that their chemical, physiological, toxicological, and hazardous properties have not been fully investigated or determined. All chemical reagents should be handled only by individuals who are familiar with their potential hazards and who have been fully trained in proper safety, laboratory, and chemical handling procedures. Although certain hazards are described herein, we can not guarantee that these are the only hazards which exist. Our MSDS sheets are based only on data available at the time of shipping and are subject to change without notice as new information is obtained. Avoid long storage periods since the product is subject to degradation with age and may become more dangerous or hazardous. It is the responsibility of the user to request updated MSDS sheets for products that are stored for extended periods. Disposal of unused product must be undertaken by qualified personnel who are knowledgeable in all applicable regulations and follow all pertinent safety precautions including the use of appropriate protective equipment (e.g. protective goggles, protective clothing, breathing equipment, facial mask, fume hood). For proper handling and disposal, always comply with federal, state, and local regulations.