



zogics.com
888.623.0088
hello@zogics.com
309 Pittsfield Road
Lenox, MA 01240

MATERIAL SAFETY DATA SHEET

DATE: SEPTEMBER 24, 2019

ZOGICS, LLC. HONEY & COCONUT BODY LOTION

SECTION 1: PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME: HONEY & COCONUT BODY LOTION
SYNONYMS: BODY LOTION

DISTRIBUTED BY: ZOGICS, LLC
ADDRESS: 309 PITTSFIELD RD, LENOX, MA 01240

PHONE: 888.623.0088

CHEMICAL NAME: N/A

PRODUCT USE: PERSONAL CARE

SECTION 1 NOTES:

SECTION 2: HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW: THE INGREDIENTS IN THIS MATERIAL ARE NOT LISTED AS CARCINOGENS BY IARC, NIP, OSHA, OR ACGIH.

POTENTIAL HEALTH EFFECTS

EYES: EYE IRRITANT

SKIN: MAY CAUSE IRRITATION IN SENSITIVE INDIVIDUALS

ACUTE HEALTH HAZARDS: N/A

CHRONIC HEALTH HAZARDS: N/A

OTHER:

SECTION 2 NOTES:

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

INGREDIENTS: THIS PRODUCT CONTAINS NO HAZARDOUS SUBSTANCE LISTED ON THE MASSACHUSETTS SUBSTANCE LIST OF OSHA HAZARD COMMUNICATION PROGRAM.

CAS NO. % WT % VOL SARA 313 REPORTABLE: N/A
PPM MG/M3

OSHA PEL-TWA: N/A
OSHA PEL STEL: N/A
OSHA PEL CEILING: N/A

SECTION 3 NOTES:

SECTION 4: FIRST AID MEASURES

EYES: IN CASE OF EYE CONTACT, FLUSH WITH WATER FOR AT LEAST 15 MINUTES. SEEK MEDICAL ATTENTION IF IRRITATION PERSISTS.

SKIN: FLUSH WITH COOL WATER. WASH WITH SOAP AND WATER. SEEK MEDICAL ATTENTION IF IRRITATION PERSISTS.

INGESTION: DO NOT INDUCE VOMITING. NEVER GIVE ANYTHING BY MOUTH IF UNCONSCIOUS OR CONVULSING. SEEK MEDICAL ATTENTION IMMEDIATELY IF SYMPTOMS DEVELOP.

INHALATION: IF SYMPTOMS DEVELOP, MOVE INDIVIDUAL TO FRESH AIR. SEEK MEDICAL ATTENTION IF SYMPTOMS PERSISTS.

GENERAL ADVICE: IF YOU FEEL UNWELL, SEEK MEDICAL ADVICE. AVOID CONTACT WITH EYES. KEEP OUT OF REACH OF CHILDREN.

SECTION 4 NOTES:

SECTION 5: FIRE-FIGHTING MEASURES

FLAMMABLE LIMITS IN AIR, UPPER: N/A
(% BY VOLUME) LOWER:

FLASH POINT: N/A

F:

C:

METHOD USED: N/A

AUTOIGNITION TEMPERATURE: N/A

F:

C:

EXTINGUISHING MEDIA: CARBON DIOXIDE, WATER, DRY CHEMICALS

SPECIAL FIRE FIGHTING PROCEDURES: NONE

UNUSUAL FIRE AND EXPLOSION HAZARDS: NONE

HAZARDOUS DECOMPOSITION PRODUCTS: NONE

SECTION 5 NOTES:

SECTION 6: ACCIDENTAL RELEASE MEASURES

ACCIDENTAL RELEASE MEASURES: CATCH SPILL AND RETURN TO CONTAINER. USE ABSORBENT TO REMOVE REMAINDER OF SPILL. PLACE ABSORBENT IN STEEL CONTAINER. PLACE CONTAINER IN SAFE PLACE TO AWAIT PROPER DISPOSAL.

SECTION 6 NOTES:

SECTION 7: HANDLING AND STORAGE

HANDLING AND STORAGE: STORE AT ROOM TEMPERATURE

OTHER PRECAUTIONS: KEEP FROM EXTREME HEAT AND FREEZING

SECTION 7 NOTES:

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

VENTILATION: NONE

RESPIRATORY PROTECTION: NONE

EYE PROTECTION: WHEN POURING LIQUID, WEAR SAFETY GLASSES

SKIN PROTECTION: NONE

OTHER PROTECTIVE CLOTHING OR EQUIPMENT: WEAR SAFETY GLASSES IF REPOURING THIS MATERIAL

SECTION 8 NOTES:

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE: VISCOUS WHITE LOTION

ODOR: CHARACTERISTIC

PHYSICAL STATE: LIQUID

PH AS SUPPLIED: OF- CONCENTRATION: 5.5 – 7.0

BOILING POINT:

F: 212°

C:

FREEZING POINT:

F: 32°

C:

SPECIFIC GRAVITY (H₂O = 1): 0.96 – 0.98

F: 68°

C:

EVAPORATION RATE: 1

BASIS (=1):

SOLUBILITY IN WATER: COMPLETE

PERCENT VOLATILE:

BY VOL @ 55-70:

SECTION 9 NOTES:

SECTION 10: STABILITY AND REACTIVITY

STABLE UNSTABLE

STABILITY: STABLE UNDER NORMAL CONDITIONS

CONDITIONS TO AVOID (STABILITY): STRONG OXIDIZING AGENTS

INCOMPATIBILITY (MATERIAL TO AVOID): STRONG OXIDIZING AGENTS

HAZARDOUS DECOMPOSITION OR BY-PRODUCTS: WILL NOT OCCUR

HAZARDOUS POLYMERIZATION: MATERIAL WILL NOT POLYMERIZE

CONDITIONS TO AVOID (POLYMERIZATION): N/A

SECTION 10 NOTES:

SECTION 11: TOXICOLOGICAL INFORMATION

TOXICOLOGICAL INFORMATION: N/A

SECTION 11 NOTES:

SECTION 12: ECOLOGICAL INFORMATION

ECOLOGICAL INFORMATION: N/A

SECTION 12 NOTES:

SECTION 13: DISPOSAL CONSIDERATIONS

WASTE DISPOSAL METHOD: FOLLOW LOCAL, STATE AND FEDERAL GUIDELINES

RCRA HAZARD CLASS: N/A

SECTION 13 NOTES:

SECTION 14: TRANSPORT INFORMATION

HAZARD CLASS: NOT REGULATED – US D.O.T.

SECTION 14 NOTES:

SECTION 15: REGULATORY INFORMATION

U.S. FEDERAL REGULATIONS

TSCA (TOXIC SUBSTANCE CONTROL ACT): N/A

STATE REGULATIONS: N/A

INTERNATIONAL REGULATIONS: N/A

SECTION 15 NOTES:

SECTION 16: OTHER INFORMATION

DISCLAIMER: INFORMATION CONTAINED HEREIN WAS OBTAINED FROM SOURCES CONSIDERED TECHNICALLY ACCURATE AND RELIABLE. WHILE EVERY EFFORT HAS BEEN MADE TO ENSURE FULL DISCLOSURE OF PRODUCT HAZARDS, IN SOME CASES DATA IS NOT AVAILABLE AND SO IS STATED. NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE AND SUPPLIER WILL NOT BE LIABLE FOR ANY LOSSES, INJURIES OR CONSEQUENTIAL DAMAGES WHICH MAY RESULT FROM THE USE OF OR RELIANCE ON ANY INFORMATION CONTAINED IN THIS DOCUMENT.