

SAFETY DATA SHEET



Date of issue/Date of revision 18 May 2020

Version 9

Section 1. Identification

Product name : 4555 PRO GRADE - AEROSOL WALL TEXTURE OIL BASED - ORANGE PEEL
Product code : 00384835
Other means of identification : Not available.
Product type : Aerosol.

Relevant identified uses of the substance or mixture and uses advised against

Product use : Consumer applications, Professional applications, Used by spraying.
Use of the substance/mixture : Coating.
Uses advised against : Not applicable.

Manufacturer : PPG Industries, Inc.
One PPG Place
Pittsburgh, PA 15272
Emergency telephone number : (412) 434-4515 (U.S.)
(514) 645-1320 (Canada)
01-800-00-21-400 or + 52 55 5559 1588 (Mexico)

Technical Phone Number : 1-800-441-9695 (8:00 am to 5:00 pm EST)

Section 2. Hazards identification

OSHA/HCS status : This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Classification of the substance or mixture : FLAMMABLE AEROSOLS - Category 1
GASES UNDER PRESSURE - Compressed gas
EYE IRRITATION - Category 2A
SKIN SENSITIZATION - Category 1
CARCINOGENICITY - Category 1A
TOXIC TO REPRODUCTION - Category 1B
SPECIFIC TARGET ORGAN TOXICITY (REPEATED EXPOSURE) - Category 2
 Percentage of the mixture consisting of ingredient(s) of unknown acute toxicity: 20.9% (Oral), 46.6% (Dermal), 15.7% (Inhalation)

GHS label elements

Hazard pictograms :



Section 2. Hazards identification

Signal word	: Danger
Hazard statements	: F Extremely flammable aerosol. Contains gas under pressure; may explode if heated. May cause an allergic skin reaction. Causes serious eye irritation. May cause cancer. May damage fertility or the unborn child. May cause damage to organs through prolonged or repeated exposure.
Precautionary statements	
Prevention	: P Obtain special instructions before use. Wear protective gloves. Wear protective clothing. Wear eye or face protection. Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Do not spray on an open flame or other ignition source. Do not breathe dust or mist. Wash thoroughly after handling. Pressurized container: Do not pierce or burn, even after use.
Response	: R If exposed or concerned: Get medical advice or attention. Wash contaminated clothing before reuse. IF ON SKIN: Wash with plenty of water. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice or attention.
Storage	: S Store locked up. Do not expose to temperatures exceeding 50 °C/122 °F.
Disposal	: Dispose of contents and container in accordance with all local, regional, national and international regulations.
Supplemental label elements	: C Contents under pressure. In a fire or if heated, a pressure increase will occur and the container may burst or explode. Do not puncture or incinerate. Keep away from heat and direct sunlight. Sanding and grinding dusts may be harmful if inhaled. This product contains crystalline silica which can cause lung cancer or silicosis. The risk of cancer depends on the duration and level of exposure to dust from sanding surfaces or mist from spray applications. Avoid contact with skin and clothing. Wash thoroughly after handling. Emits toxic fumes when heated.
Hazards not otherwise classified	: Prolonged or repeated contact may dry skin and cause irritation.

Section 3. Composition/information on ingredients

Substance/mixture	: Mixture
Product name	: 4555 PRO GRADE - AEROSOL WALL TEXTURE OIL BASED - ORANGE PEEL

Ingredient name	%	CAS number
F imestone	≥20 - ≤50	1317-65-3
ethanol	≥10 - ≤20	64-17-5
Wollastonite	≥5.0 - ≤10	13983-17-0
Isobutane	≥5.0 - ≤10	75-28-5
4-hydroxy-4-methylpentan-2-one	≥5.0 - ≤10	123-42-2
propane	≥1.0 - ≤5.0	74-98-6
Isopropyl alcohol	≥1.0 - ≤5.0	67-63-0
Fatty acids, C14-18 and C16-18 unsatd., maleated	≥1.0 - ≤5.0	Not available.
xylene	≥1.0 - ≤3.2	1330-20-7
ethylbenzene	<1.0	100-41-4
crystalline silica, respirable powder (<10 microns)	<1.0	14808-60-7
N-methyl-2-pyrrolidone	<1.0	872-50-4

Section 3. Composition/information on ingredients

maleic anhydride	<0.10	108-31-6
------------------	-------	----------

SUB codes represent substances without registered CAS Numbers.

Any concentration shown as a range is to protect confidentiality or is due to batch variation.

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

Occupational exposure limits, if available, are listed in Section 8.

Section 4. First aid measures

If ingestion, irritation, any type of overexposure or symptoms of overexposure occur during or persists after use of this product, contact a POISON CONTROL CENTER, EMERGENCY ROOM OR PHYSICIAN immediately; have Safety Data Sheet information available. Never give anything by mouth to an unconscious or convulsing person.

Description of necessary first aid measures

- Eye contact** : Remove contact lenses, irrigate copiously with clean, fresh water, holding the eyelids apart for at least 10 minutes and seek immediate medical advice.
- Inhalation** : Remove to fresh air. Keep person warm and at rest. If not breathing, if breathing is irregular or if respiratory arrest occurs, provide artificial respiration or oxygen by trained personnel.
- Skin contact** : Remove contaminated clothing and shoes. Wash skin thoroughly with soap and water or use recognized skin cleanser. Do NOT use solvents or thinners.
- Ingestion** : If swallowed, seek medical advice immediately and show this container or label. Keep person warm and at rest. Do NOT induce vomiting.

Most important symptoms/effects, acute and delayed

Potential acute health effects

- Eye contact** : Causes serious eye irritation.
- Inhalation** : No known significant effects or critical hazards.
- Skin contact** : Defatting to the skin. May cause skin dryness and irritation. May cause an allergic skin reaction.
- Ingestion** : No known significant effects or critical hazards.

Over-exposure signs/symptoms

- Eye contact** : Adverse symptoms may include the following:
pain or irritation
watering
redness
- Inhalation** : Adverse symptoms may include the following:
respiratory tract irritation
coughing
reduced fetal weight
increase in fetal deaths
skeletal malformations

Section 4. First aid measures

- Skin contact** : Adverse symptoms may include the following:
irritation
redness
dryness
cracking
reduced fetal weight
increase in fetal deaths
skeletal malformations
- Ingestion** : Adverse symptoms may include the following:
reduced fetal weight
increase in fetal deaths
skeletal malformations

Indication of immediate medical attention and special treatment needed, if necessary

- Notes to physician** : Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.
- Specific treatments** : No specific treatment.
- Protection of first-aiders** : No action shall be taken involving any personal risk or without suitable training. If it is suspected that fumes are still present, the rescuer should wear an appropriate mask or self-contained breathing apparatus. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation. Wash contaminated clothing thoroughly with water before removing it, or wear gloves.

See toxicological information (Section 11)

Section 5. Fire-fighting measures

Extinguishing media

- Suitable extinguishing media** : Use an extinguishing agent suitable for the surrounding fire.
- Unsuitable extinguishing media** : None known.

Specific hazards arising from the chemical : Extremely flammable aerosol. In a fire or if heated, a pressure increase will occur and the container may burst, with the risk of a subsequent explosion. Vapors may accumulate in low or confined areas or travel a considerable distance to a source of ignition and flash back. Gas may accumulate in low or confined areas or travel a considerable distance to a source of ignition and flash back, causing fire or explosion. Bursting aerosol containers may be propelled from a fire at high speed. Runoff to sewer may create fire or explosion hazard.

Hazardous thermal decomposition products : Decomposition products may include the following materials:
carbon oxides
metal oxide/oxides

Special protective actions for fire-fighters : Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training. Move containers from fire area if this can be done without risk. Use water spray to keep fire-exposed containers cool.

Section 5. Fire-fighting measures

Special protective equipment for fire-fighters : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode.

Section 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

- For non-emergency personnel** : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. In the case of aerosols being ruptured, care should be taken due to the rapid escape of the pressurized contents and propellant. If a large number of containers are ruptured, treat as a bulk material spillage according to the instructions in the clean-up section. Do not touch or walk through spilled material. Shut off all ignition sources. No flares, smoking or flames in hazard area. Avoid breathing vapor or mist. Provide adequate ventilation. Wear appropriate respirator when ventilation is inadequate. Put on appropriate personal protective equipment.
- For emergency responders** : If specialized clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".
- Environmental precautions** : Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

Methods and materials for containment and cleaning up

- Small spill** : Stop leak if without risk. Move containers from spill area. Use spark-proof tools and explosion-proof equipment. Dilute with water and mop up if water-soluble. Alternatively, or if water-insoluble, absorb with an inert dry material and place in an appropriate waste disposal container. Dispose of via a licensed waste disposal contractor.
- Large spill** : Stop leak if without risk. Move containers from spill area. Use spark-proof tools and explosion-proof equipment. Approach release from upwind. Prevent entry into sewers, water courses, basements or confined areas. Wash spillages into an effluent treatment plant or proceed as follows. Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations (see Section 13). Dispose of via a licensed waste disposal contractor. Contaminated absorbent material may pose the same hazard as the spilled product. Note: see Section 1 for emergency contact information and Section 13 for waste disposal.

Section 7. Handling and storage

Precautions for safe handling

- Protective measures** : Put on appropriate personal protective equipment (see Section 8). Persons with a history of skin sensitization problems should not be employed in any process in which this product is used. Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use. Avoid exposure - obtain special instructions before use. Avoid exposure during pregnancy. Do not handle until all safety precautions have been read and understood. Do not get in eyes or on skin or clothing. Do not breathe vapor or mist. Do not ingest. Avoid breathing gas. Use only with adequate ventilation. Wear appropriate respirator when ventilation is inadequate. Store and use away from heat, sparks, open flame or any other ignition source. Use explosion-proof electrical (ventilating, lighting and material handling)

Section 7. Handling and storage

- equipment. Use only non-sparking tools. Empty containers retain product residue and can be hazardous.
- Special precautions** : Vapors may accumulate in low or confined areas or travel a considerable distance to a source of ignition and flash back. Vapors are heavier than air and may spread along floors. If this material is part of a multiple component system, read the Safety Data Sheet(s) for the other component or components before blending as the resulting mixture may have the hazards of all of its parts.
- Advice on general occupational hygiene** : Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. Remove contaminated clothing and protective equipment before entering eating areas. See also Section 8 for additional information on hygiene measures.
- Conditions for safe storage, including any incompatibilities** : Do not store above the following temperature: 50°C (122°F). Store in accordance with local regulations. Store away from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Protect from sunlight. Store locked up. Eliminate all ignition sources. Use appropriate containment to avoid environmental contamination.

Section 8. Exposure controls/personal protection

Control parameters

Occupational exposure limits

Ingredient name	Exposure limits
☑ Limestone	OSHA PEL (United States, 5/2018). TWA: 5 mg/m ³ 8 hours. Form: Respirable fraction
ethanol	TWA: 15 mg/m ³ 8 hours. Form: Total dust ACGIH TLV (United States, 3/2019). STEL: 1000 ppm 15 minutes.
Wollastonite	OSHA PEL (United States, 5/2018). TWA: 1900 mg/m ³ 8 hours. TWA: 1000 ppm 8 hours. ACGIH TLV (United States, 3/2019). TWA: 1 mg/m ³ 8 hours. Form: Inhalable fraction
Isobutane	ACGIH TLV (United States, 3/2019). Explosive potential. STEL: 1000 ppm 15 minutes.
4-hydroxy-4-methylpentan-2-one	ACGIH TLV (United States, 3/2019). TWA: 238 mg/m ³ 8 hours. TWA: 50 ppm 8 hours. OSHA PEL (United States, 5/2018). TWA: 240 mg/m ³ 8 hours. TWA: 50 ppm 8 hours.
propane	OSHA PEL (United States, 5/2018). TWA: 1800 mg/m ³ 8 hours. TWA: 1000 ppm 8 hours. ACGIH TLV (United States, 3/2019). Oxygen Depletion [Asphyxiant]. Explosive potential.
Isopropyl alcohol	ACGIH TLV (United States, 3/2019).

Section 8. Exposure controls/personal protection

Fatty acids, C14-18 and C16-18 unsatd., maleated xylene	<p>STEL: 400 ppm 15 minutes. TWA: 200 ppm 8 hours. OSHA PEL (United States, 5/2018). TWA: 980 mg/m³ 8 hours. TWA: 400 ppm 8 hours. None. ACGIH TLV (United States, 3/2019). STEL: 651 mg/m³ 15 minutes. STEL: 150 ppm 15 minutes. TWA: 434 mg/m³ 8 hours. TWA: 100 ppm 8 hours. OSHA PEL (United States, 5/2018). TWA: 435 mg/m³ 8 hours. TWA: 100 ppm 8 hours. ACGIH TLV (United States, 3/2019). TWA: 20 ppm 8 hours. OSHA PEL (United States, 5/2018). TWA: 435 mg/m³ 8 hours. TWA: 100 ppm 8 hours. ACGIH TLV (United States, 3/2019). TWA: 0.025 mg/m³ 8 hours. Form: Respirable OSHA PEL Z3 (United States, 6/2016). TWA: 10 mg/m³ / (%SiO₂+2) 8 hours. Form: Respirable TWA: 250 mppcf / (%SiO₂+5) 8 hours. Form: Respirable OSHA PEL (United States, 5/2018). TWA: 50 µg/m³ 8 hours. Form: Respirable dust IPEL (PPG). Absorbed through skin. TWA: 10 ppm STEL: 20 ppm ACGIH TLV (United States, 3/2019). Skin sensitizer. Inhalation sensitizer. TWA: 0.01 mg/m³ 8 hours. Form: Inhalable fraction and vapor OSHA PEL (United States, 5/2018). TWA: 1 mg/m³ 8 hours. TWA: 0.25 ppm 8 hours.</p>
ethylbenzene	
crystalline silica, respirable powder (<10 microns)	
N-methyl-2-pyrrolidone	
maleic anhydride	

Key to abbreviations

A	= Acceptable Maximum Peak	S	= Potential skin absorption
ACGIH	= American Conference of Governmental Industrial Hygienists.	SR	= Respiratory sensitization
C	= Ceiling Limit	SS	= Skin sensitization
F	= Fume	STEL	= Short term Exposure limit values
IPEL	= Internal Permissible Exposure Limit	TD	= Total dust
OSHA	= Occupational Safety and Health Administration.	TLV	= Threshold Limit Value
R	= Respirable	TWA	= Time Weighted Average
Z	= OSHA 29 CFR 1910.1200 Subpart Z - Toxic and Hazardous Substances		

Consult local authorities for acceptable exposure limits.

Section 8. Exposure controls/personal protection

- Recommended monitoring procedures** : If this product contains ingredients with exposure limits, personal, workplace atmosphere or biological monitoring may be required to determine the effectiveness of the ventilation or other control measures and/or the necessity to use respiratory protective equipment. Reference should be made to appropriate monitoring standards. Reference to national guidance documents for methods for the determination of hazardous substances will also be required.
- Appropriate engineering controls** : Use only with adequate ventilation. If user operations generate dust, fumes, gas, vapor or mist, use process enclosures, local exhaust ventilation or other engineering controls to keep worker exposure to airborne contaminants below any recommended or statutory limits. The engineering controls also need to keep gas, vapor or dust concentrations below any lower explosive limits. Use explosion-proof ventilation equipment.
- Environmental exposure controls** : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.
- Individual protection measures**
- Hygiene measures** : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Contaminated work clothing should not be allowed out of the workplace. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.
- Eye/face protection** : Chemical splash goggles.
- Skin protection**
- Hand protection** : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary. Considering the parameters specified by the glove manufacturer, check during use that the gloves are still retaining their protective properties. It should be noted that the time to breakthrough for any glove material may be different for different glove manufacturers. In the case of mixtures, consisting of several substances, the protection time of the gloves cannot be accurately estimated.
- Gloves** : Butyl rubber
- Body protection** : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product. When there is a risk of ignition from static electricity, wear anti-static protective clothing. For the greatest protection from static discharges, clothing should include anti-static overalls, boots and gloves.
- Other skin protection** : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Respiratory protection** : Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator. If workers are exposed to concentrations above the exposure limit, they must use appropriate, certified respirators. Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary.

Section 9. Physical and chemical properties

Appearance

Physical state	: Liquid. Aerosol.
Color	: White.
Odor	: Characteristic.
Odor threshold	: Not available.
pH	: Not available.
Melting point	: Not available.
Boiling point	: <35°C (<95°F)
Flash point	: Closed cup: -94.4°C (-137.9°F)
Auto-ignition temperature	: Not available.
Decomposition temperature	: Not available.
Flammability (solid, gas)	: Not available.
Lower and upper explosive (flammable) limits	: Not available.
Evaporation rate	: Not available.
Vapor pressure	: Not available.
Vapor density	: Not available.
Relative density	: 1.32
Density (lbs / gal)	: 11.02
Solubility	: Insoluble in the following materials: cold water.
Partition coefficient: n-octanol/water	: Not available.
Viscosity	: Kinematic (40°C (104°F)): >0.21 cm ² /s (>21 cSt)
Volatility	: 63% (v/v), 34.35% (w/w)
% Solid. (w/w)	: 65.65

Aerosol product

Type of aerosol	: Spray
Heat of combustion	: 6.332 kJ/g

Section 10. Stability and reactivity

Reactivity	: No specific test data related to reactivity available for this product or its ingredients.
Chemical stability	: The product is stable.
Possibility of hazardous reactions	: Under normal conditions of storage and use, hazardous reactions will not occur.
Conditions to avoid	: When exposed to high temperatures may produce hazardous decomposition products. Refer to protective measures listed in sections 7 and 8.

Section 10. Stability and reactivity

Incompatible materials : Keep away from the following materials to prevent strong exothermic reactions: oxidizing agents, strong alkalis, strong acids.

Hazardous decomposition products : Decomposition products may include the following materials: carbon monoxide, carbon dioxide, smoke, oxides of nitrogen.

Section 11. Toxicological information

Information on toxicological effects

Acute toxicity

Product/ingredient name	Result	Species	Dose	Exposure
Limestone ethanol	LD50 Oral	Rat	6450 mg/kg	-
	LC50 Inhalation Vapor	Rat	124700 mg/m ³	4 hours
	LD50 Dermal	Rat	17100 mg/kg	-
Isobutane	LD50 Oral	Rat	7 g/kg	-
	LC50 Inhalation Vapor	Rat	658000 mg/m ³	4 hours
	LD50 Dermal	Rabbit	13500 mg/kg	-
4-hydroxy-4-methylpentan-2-one	LD50 Oral	Rat	3002 mg/kg	-
	LC50 Inhalation Vapor	Rat	72600 mg/m ³	4 hours
	LD50 Dermal	Rabbit	12800 mg/kg	-
Isopropyl alcohol	LD50 Oral	Rat	5045 mg/kg	-
	LD50 Dermal	Rabbit	>1.7 g/kg	-
	LD50 Oral	Rat	4.3 g/kg	-
xylene	LC50 Inhalation Vapor	Rat	17.8 mg/l	4 hours
	LD50 Dermal	Rabbit	17.8 g/kg	-
	LD50 Oral	Rat	3.5 g/kg	-
ethylbenzene	LC50 Inhalation Dusts and mists	Rat	>5100 mg/m ³	4 hours
	LD50 Dermal	Rabbit	8 g/kg	-
	LD50 Oral	Rat	3.914 g/kg	-
N-methyl-2-pyrrolidone	LD50 Dermal	Rabbit	2620 mg/kg	-
	LD50 Oral	Rat	400 mg/kg	-
	LD50 Oral	Rat		

Conclusion/Summary : There are no data available on the mixture itself.

Irritation/Corrosion

Product/ingredient name	Result	Species	Score	Exposure	Observation
xylene	Skin - Moderate irritant	Rabbit	-	24 hours 500 mg	-

Conclusion/Summary

Skin : There are no data available on the mixture itself.

Eyes : There are no data available on the mixture itself.

Respiratory : There are no data available on the mixture itself.

Sensitization

Conclusion/Summary

Skin : There are no data available on the mixture itself.

Respiratory : There are no data available on the mixture itself.

Mutagenicity

Conclusion/Summary : There are no data available on the mixture itself.

Section 11. Toxicological information

Carcinogenicity

Conclusion/Summary : There are no data available on the mixture itself.

Classification

Product/ingredient name	OSHA	IARC	NTP
Wollastonite	-	3	-
Isopropyl alcohol	-	3	-
xylene	-	3	-
ethylbenzene	-	2B	-
crystalline silica, respirable powder (<10 microns)	-	1	Known to be a human carcinogen.

Carcinogen Classification code:

IARC: 1, 2A, 2B, 3, 4

NTP: Known to be a human carcinogen; Reasonably anticipated to be a human carcinogen

OSHA: +

Not listed/not regulated: -

Reproductive toxicity

Conclusion/Summary : There are no data available on the mixture itself.

Teratogenicity

Conclusion/Summary : There are no data available on the mixture itself.

Specific target organ toxicity (single exposure)

Name	Category	Route of exposure	Target organs
4-hydroxy-4-methylpentan-2-one	Category 3	-	Respiratory tract irritation
Isopropyl alcohol	Category 3	-	Narcotic effects
xylene	Category 3	-	Respiratory tract irritation
N-methyl-2-pyrrolidone	Category 3	-	Respiratory tract irritation

Specific target organ toxicity (repeated exposure)

Name	Category	Route of exposure	Target organs
propane	Category 2	-	-
ethylbenzene	Category 2	-	hearing organs
crystalline silica, respirable powder (<10 microns)	Category 1	inhalation	-
N-methyl-2-pyrrolidone	Category 2	-	-
maleic anhydride	Category 1	inhalation	respiratory system

Target organs

: Contains material which causes damage to the following organs: brain.
Contains material which may cause damage to the following organs: blood, kidneys, lungs, the nervous system, the reproductive system, liver, spleen, upper respiratory tract, skin, central nervous system (CNS), eye, lens or cornea.

Aspiration hazard

Section 11. Toxicological information

Name	Result
xylene ethylbenzene	ASPIRATION HAZARD - Category 1 ASPIRATION HAZARD - Category 1

Information on the likely routes of exposure

Potential acute health effects

- Eye contact** : Causes serious eye irritation.
- Inhalation** : No known significant effects or critical hazards.
- Skin contact** : Defatting to the skin. May cause skin dryness and irritation. May cause an allergic skin reaction.
- Ingestion** : No known significant effects or critical hazards.

Over-exposure signs/symptoms

- Eye contact** : Adverse symptoms may include the following:
pain or irritation
watering
redness
- Inhalation** : Adverse symptoms may include the following:
respiratory tract irritation
coughing
reduced fetal weight
increase in fetal deaths
skeletal malformations
- Skin contact** : Adverse symptoms may include the following:
irritation
redness
dryness
cracking
reduced fetal weight
increase in fetal deaths
skeletal malformations
- Ingestion** : Adverse symptoms may include the following:
reduced fetal weight
increase in fetal deaths
skeletal malformations

Delayed and immediate effects and also chronic effects from short and long term exposure

- Conclusion/Summary** : There are no data available on the mixture itself. This product contains crystalline silica which can cause lung cancer or silicosis. The risk of cancer depends on the duration and level of exposure to dust from sanding surfaces or mist from spray applications. Exposure to component solvent vapor concentrations in excess of the stated occupational exposure limit may result in adverse health effects such as mucous membrane and respiratory system irritation and adverse effects on the kidneys, liver and central nervous system. Symptoms and signs include headache, dizziness, fatigue, muscular weakness, drowsiness and, in extreme cases, loss of consciousness. Solvents may cause some of the above effects by absorption through the skin. There is some evidence that repeated exposure to organic solvent vapors in combination with constant loud noise can cause greater hearing loss than expected from exposure to noise alone. If splashed in the eyes, the liquid may cause irritation and reversible damage. Ingestion may cause nausea, diarrhea and vomiting. This takes into account, where known, delayed and immediate effects and also chronic effects of components from short-term and long-term exposure by oral, inhalation and dermal routes of exposure and eye contact.

Section 11. Toxicological information

Short term exposure

Potential immediate effects : There are no data available on the mixture itself.

Potential delayed effects : There are no data available on the mixture itself.

Long term exposure

Potential immediate effects : There are no data available on the mixture itself.

Potential delayed effects : There are no data available on the mixture itself.

Potential chronic health effects

General : May cause damage to organs through prolonged or repeated exposure. Prolonged or repeated contact can defat the skin and lead to irritation, cracking and/or dermatitis. Once sensitized, a severe allergic reaction may occur when subsequently exposed to very low levels.

Carcinogenicity : May cause cancer. Risk of cancer depends on duration and level of exposure.

Mutagenicity : No known significant effects or critical hazards.

Teratogenicity : May damage the unborn child.

Developmental effects : No known significant effects or critical hazards.

Fertility effects : No known significant effects or critical hazards.

Numerical measures of toxicity

Acute toxicity estimates

Product/ingredient name	Oral (mg/kg)	Dermal (mg/kg)	Inhalation (gases) (ppm)	Inhalation (vapors) (mg/l)	Inhalation (dusts and mists) (mg/l)
<input checked="" type="checkbox"/> 4555 PRO GRADE - AEROSOL WALL TEXTURE OIL BASED - ORANGE PEEL	40712.3	58126.3	N/A	916.8	125
Limestone	6450	N/A	N/A	N/A	N/A
ethanol	7000	17100	N/A	124.7	N/A
Isobutane	N/A	N/A	N/A	658	N/A
4-hydroxy-4-methylpentan-2-one	3002	13500	N/A	N/A	N/A
Isopropyl alcohol	5045	12800	N/A	72.6	N/A
xylene	4300	1100	N/A	11	1.5
ethylbenzene	3500	17800	N/A	17.8	1.5
N-methyl-2-pyrrolidone	3914	8000	N/A	N/A	N/A
maleic anhydride	400	2620	N/A	N/A	N/A

Section 12. Ecological information

Toxicity

Product/ingredient name	Result	Species	Exposure
<input checked="" type="checkbox"/> Limestone	Acute LC50 >56000 mg/l	Fish	96 hours
ethanol	Acute EC50 7640 mg/l Fresh water	Daphnia - Daphnia magna	48 hours
4-hydroxy-4-methylpentan-2-one	Acute LC50 >100 mg/l	Fish	96 hours
Isopropyl alcohol	Acute EC50 10100 mg/l Fresh water	Daphnia - Daphnia magna	48 hours
ethylbenzene	Acute LC50 150 to 200 mg/l Fresh water	Fish	96 hours

Section 12. Ecological information

Persistence and degradability

Product/ingredient name	Test	Result	Dose	Inoculum
4-hydroxy-4-methylpentan-2-one	OECD 301A	98.5 % - Readily - 28 days	-	-

Product/ingredient name	Aquatic half-life	Photolysis	Biodegradability
ethanol	-	-	Readily
4-hydroxy-4-methylpentan-2-one	-	-	Readily
xylene	-	-	Readily
ethylbenzene	-	-	Readily
N-methyl-2-pyrrolidone	-	-	Readily

Bioaccumulative potential

Product/ingredient name	LogP _{ow}	BCF	Potential
ethanol	-0.31	-	low
Isobutane	2.8	-	low
4-hydroxy-4-methylpentan-2-one	-0.14 to 1.03	-	low
propane	2.36	-	low
Isopropyl alcohol	0.05	-	low
xylene	3.16	7.4 to 18.5	low
ethylbenzene	3.15	79.43	low
N-methyl-2-pyrrolidone	-0.38	3.16	low

Mobility in soil

Soil/water partition coefficient (K_{oc}) : Not available.

Section 13. Disposal considerations

Disposal methods : The generation of waste should be avoided or minimized wherever possible. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible. This material and its container must be disposed of in a safe way. Empty containers or liners may retain some product residues. Do not puncture or incinerate container.

Disposal should be in accordance with applicable regional, national and local laws and regulations.

Refer to Section 7: HANDLING AND STORAGE and Section 8: EXPOSURE CONTROLS/PERSONAL PROTECTION for additional handling information and protection of employees. Section 6. Accidental release measures

14. Transport information

	DOT	IMDG	IATA
UN number	UN1950	UN1950	UN1950
UN proper shipping name	AEROSOLS	AEROSOLS	Aerosols, flammable
Transport hazard class (es)	2.1	2.1	2.1
Packing group	-	-	-
Environmental hazards	No.	No.	No.
Marine pollutant substances	Not applicable.	Not applicable.	Not applicable.
Product RQ (lbs)	9889.8	Not applicable.	Not applicable.
RQ substances	(xylene)	Not applicable.	Not applicable.

Additional information

- DOT** : Package sizes shipped in quantities less than the product reportable quantity are not subject to the RQ (reportable quantity) transportation requirements.
- IMDG** : None identified.
- IATA** : None identified.

Special precautions for user : **Transport within user's premises:** always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

Transport in bulk according to IMO instruments : Not applicable.

Section 15. Regulatory information**United States**

United States inventory (TSCA 8b) : Not determined.

United States - TSCA 5(a)2 - Proposed significant new use rules:

-methyl-2-pyrrolidone

Listed

SARA 302/304

SARA 304 RQ : Not applicable.

Composition/information on ingredients

No products were found.

SARA 311/312

Section 15. Regulatory information

Classification : **FLAMMABLE AEROSOLS - Category 1**
GASES UNDER PRESSURE - Compressed gas
EYE IRRITATION - Category 2A
SKIN SENSITIZATION - Category 1
CARCINOGENICITY - Category 1A
TOXIC TO REPRODUCTION - Category 1B
SPECIFIC TARGET ORGAN TOXICITY (REPEATED EXPOSURE) - Category 2
HNOC - Defatting irritant

Composition/information on ingredients

Name	%	Classification
ethanol	≥10 - ≤20	FLAMMABLE LIQUIDS - Category 2 EYE IRRITATION - Category 2A HNOC - Defatting irritant
4-hydroxy-4-methylpentan-2-one	≥5.0 - ≤10	FLAMMABLE LIQUIDS - Category 3 EYE IRRITATION - Category 2A SPECIFIC TARGET ORGAN TOXICITY (SINGLE EXPOSURE) (Respiratory tract irritation) - Category 3
propane	≥1.0 - ≤5.0	FLAMMABLE GASES - Category 1 GASES UNDER PRESSURE - Compressed gas SPECIFIC TARGET ORGAN TOXICITY (REPEATED EXPOSURE) - Category 2
Isopropyl alcohol	≥1.0 - ≤5.0	FLAMMABLE LIQUIDS - Category 2 EYE IRRITATION - Category 2A SPECIFIC TARGET ORGAN TOXICITY (SINGLE EXPOSURE) (Narcotic effects) - Category 3
Fatty acids, C14-18 and C16-18 unsatd., maleated	≥1.0 - ≤5.0	SKIN IRRITATION - Category 2 SKIN SENSITIZATION - Category 1B
xylene	≥1.0 - ≤3.2	FLAMMABLE LIQUIDS - Category 3 ACUTE TOXICITY (dermal) - Category 4 ACUTE TOXICITY (inhalation) - Category 4 SKIN IRRITATION - Category 2 EYE IRRITATION - Category 2A SPECIFIC TARGET ORGAN TOXICITY (SINGLE EXPOSURE) (Respiratory tract irritation) - Category 3
ethylbenzene	<1.0	ASPIRATION HAZARD - Category 1 FLAMMABLE LIQUIDS - Category 2 ACUTE TOXICITY (inhalation) - Category 4 CARCINOGENICITY - Category 2 SPECIFIC TARGET ORGAN TOXICITY (REPEATED EXPOSURE) - Category 2 ASPIRATION HAZARD - Category 1 HNOC - Defatting irritant
crystalline silica, respirable powder (<10 microns)	<1.0	CARCINOGENICITY - Category 1A SPECIFIC TARGET ORGAN TOXICITY (REPEATED EXPOSURE) - Category 1
N-methyl-2-pyrrolidone	<1.0	SKIN IRRITATION - Category 2 EYE IRRITATION - Category 2A TOXIC TO REPRODUCTION - Category 1B SPECIFIC TARGET ORGAN TOXICITY (SINGLE EXPOSURE) (Respiratory tract irritation) - Category 3 SPECIFIC TARGET ORGAN TOXICITY (REPEATED EXPOSURE) - Category 2

Section 15. Regulatory information

maleic anhydride	<0.10	EXPOSURE) - Category 2 HNOC - Defatting irritant COMBUSTIBLE DUSTS ACUTE TOXICITY (oral) - Category 4 SKIN CORROSION - Category 1B SERIOUS EYE DAMAGE - Category 1 RESPIRATORY SENSITIZATION - Category 1A SKIN SENSITIZATION - Category 1A SPECIFIC TARGET ORGAN TOXICITY (REPEATED EXPOSURE) - Category 1
------------------	-------	---

SARA 313

Supplier notification	Chemical name	CAS number	Concentration
	xylene	1330-20-7	0.5 - 1.5
	ethylbenzene	100-41-4	0.1 - 1

SARA 313 notifications must not be detached from the SDS and any copying and redistribution of the SDS shall include copying and redistribution of the notice attached to copies of the SDS subsequently redistributed.

Additional environmental information is contained on the Environmental Data Sheet for this product, which can be obtained from your PPG representative.

California Prop. 65

 **WARNING:** Cancer and Reproductive Harm - www.P65Warnings.ca.gov.

Section 16. Other information

Hazardous Material Information System (U.S.A.)

Health : 2 * Flammability : 4 Physical hazards : 0

(*) - Chronic effects

Caution: HMIS® ratings are based on a 0-4 rating scale, with 0 representing minimal hazards or risks, and 4 representing significant hazards or risks. Although HMIS® ratings and the associated label are not required on MSDSs or products leaving a facility under 29 CFR 1910.1200, the preparer may choose to provide them. HMIS® ratings are to be used with a fully implemented HMIS® program. HMIS® is a registered trademark and service mark of the American Coatings Association, Inc.

The customer is responsible for determining the PPE code for this material. For more information on HMIS® Personal Protective Equipment (PPE) codes, consult the HMIS® Implementation Manual.

National Fire Protection Association (U.S.A.)

Health : 2 Flammability : 4 Instability : 0

Date of previous issue : 12/6/2019

Organization that prepared the MSDS : EHS

Key to abbreviations : ATE = Acute Toxicity Estimate
BCF = Bioconcentration Factor
GHS = Globally Harmonized System of Classification and Labelling of Chemicals
IATA = International Air Transport Association
IBC = Intermediate Bulk Container
IMDG = International Maritime Dangerous Goods
LogPow = logarithm of the octanol/water partition coefficient
MARPOL = International Convention for the Prevention of Pollution From Ships, 1973 as modified by the Protocol of 1978. ("Marpol" = marine pollution)
N/A = Not available

Section 16. Other information

SGG = Segregation Group

UN = United Nations

✔ Indicates information that has changed from previously issued version.

Disclaimer

The information contained in this data sheet is based on present scientific and technical knowledge. The purpose of this information is to draw attention to the health and safety aspects concerning the products supplied by PPG, and to recommend precautionary measures for the storage and handling of the products. No warranty or guarantee is given in respect of the properties of the products. No liability can be accepted for any failure to observe the precautionary measures described in this data sheet or for any misuse of the products.