

NEW

Lutron energy-saving products



PowPak™ dimming module (actual size)

Radio Powr Savr™ occupancy/vacancy sensor (actual size)

Pico® wireless control (actual size)

Quick Install Energy Solutions


Featuring Energi TriPak™



Energi TriPak is a family of wireless energy-saving products featuring sensors and controls, wallbox dimmers/switches, plug-in modules, junction box mounted devices and fixtures. These components, when combined:

- save up to 60% of lighting electricity usage
- increase occupant comfort and productivity
- control virtually all loads
- reduce installation and programming costs

Annual electricity use in commercial buildings¹



Energi TriPak is designed for new construction and retrofit commercial applications, where lighting accounts for 39% of electricity usage. These spaces, such as K-12/university classrooms and offices, benefit from Energi TriPak's energy savings through strategies like automatic occupancy/vacancy sensing and daylight harvesting.

Studies show that proper lighting is beneficial to a space's occupants. By providing task-appropriate lighting and individual lighting control Energi TriPak improves comfort and occupant satisfaction, resulting in increased productivity.^{2,3,4}

Energi TriPak requires no additional wiring. The components communicate wirelessly via Lutron's reliable Clear Connect™ Radio Frequency (RF) technology. In addition, simple button press programming eliminates the need for factory commissioning.

Energi TriPak design and application guide

- 02** What is Energi TriPak?
- 03** Benefits
- 04** Energy-saving control strategies
- 05** Codes and standards

Applications

- 06** Public restroom application
- 08** Private office application
- 10** Classroom application
- 12** How to design a system

Energi TriPak components

- 14** Radio Powr Savr™ wireless occupancy/vacancy sensors
- 15** Radio Powr Savr wireless daylight sensor
- 16** PowPak™ relay module
- 17** PowPak dimming module with EcoSystem®
- 18** Maestro Wireless® switch
- 19** Maestro Wireless dimmer
- 20** PowPak stairwell fixture
- 21** Maestro Wireless tabletop lamp dimmer and PowPak plug-in dimming module
- 22** PowPak plug-in appliance module
- 23** PowPak relay module with Softswitch®
- 24** PowPak contact closure output module
- 25** Pico® wireless controls
- 26** Pico wireless control accessories

How it works

- 27** Stairwell retrofit solution
- 28** Variable air volume integration
- 29** Plug load control by switching receptacles
- 30** Alternate stand-alone solution
- 32** Sensor coverage diagrams
- 34** Ordering information

What is Energi TriPak?

Energi TriPak consists of transmitting devices that send out radio frequency (RF) commands to the load controllers. The load controllers receive the RF command and perform the appropriate action based on the information received.

Transmitting devices

Sense

Radio Powr Savr™ wireless sensors



Occupancy/vacancy



Daylight

Adjust

Pico® wireless control



Wall-mount



Tabletop



Hand-held

Load controllers

Conserve

NEW PowPak™ load controllers



Dimming module with EcoSystem®



Relay module




Contact closure output module



Plug-in dimming module



Plug-in appliance module



Stairwell fixture

Maestro Wireless®



Dimmer



Switch



Tabletop lamp dimmer

Benefits

Easy to install and program

- All points of control are wireless for simple installation with no new wiring
- Simple button programming for all devices

Saves energy and money

Simply incorporate the following energy-saving control strategies:

- Personal control
- Occupancy/vacancy sensing
- Daylight harvesting
- High-end trim
- Appliance control
- HVAC integration

Cost-effective

- No commissioning required
- Overall labor costs reduced due to wireless communication – no additional wiring


Meets codes and standards

Provides the opportunity to meet the following codes and standards:

- LEED 2009
- ASHRAE Energy Code 90.1-2010
- IECC (International Energy Conservation)
- ASHRAE Green Standard 189.1-2011
- IgCC (International Green Construction Code)
- CEC Title 24 (California Energy Commission)




Single space energy-saving control strategies¹



Personal control

Provide personal choice and control of light levels to accommodate different tasks and activities. Permit control from multiple locations.


Typical lighting energy savings: **10-20%**²



Occupancy/vacancy sensing

Gradually dim lights to a low level or turn lights off when space is unoccupied; turn lights on when someone enters.


Typical lighting energy savings: **20-60%**³



Daylight harvesting

Dim electric light or switch it off during the day to take advantage of available daylight.


Typical lighting energy savings: **20-60%**⁴



High-end trim

Set the maximum light level in space based on customer preference or design requirements.


Typical lighting energy savings: **10-20%**⁵



Appliance control

Automatically switch plug loads off when space is unoccupied.

Typical energy savings: **Variable**



HVAC integration

Control heating, ventilation and air conditioning systems through contact closure.

Typical energy savings: **Variable**

1. Although combined savings for a building from individual room strategies is not additive, solutions that utilize all strategies typically save 60% or more. Glenn Hughes, director of construction for The New York Times Company building in New York City reports 75% lighting energy savings using Lutron systems. Jeff Choma, manager of mechanical and electrical systems at Georgian College in Ontario, Canada reports 70% lighting energy savings using Lutron systems. Lighting energy savings exceeding 60% is frequently reported by customers using Lutron solutions as part of an overall energy-savings design program.

2. Personal control source: Galasiu AD, et al. 2007. Energy saving lighting control systems for open-plan offices: A field study. Leukos. 4(1) pg. 7-29.

3. Occupancy/vacancy sensing source: VonNieda B, Maniccia D, & Tweed A. 2000. An analysis of the energy and cost savings potential of occupancy sensors for commercial lighting systems. Proceedings of the Illuminating Engineering Society. Paper #43.

4. Daylight harvesting source: Brambley MR, et al. 2005. Advanced sensors and controls for building applications: Market assessment and potential R&D pathways. Pacific Northwest National Laboratory; prepared for U.S. Department of Energy.

5. Existing buildings were often designed to much higher light levels than currently recommended. Even in new and newly renovated spaces, unknown room conditions, architectural layout constraints, and design safety factors often create lighted environments that are considerably brighter than needed. High-end trim source: Pacific Gas & Electric Company. 1997. Dimming Controls for Lighting.

Meets codes and standards

LEED NC 2009

Can contribute to:

- SS Credit 8 Light Pollution Reduction (1 point)
- EA Prerequisite 2 Minimum Energy Performance
- EA Credit 1 Optimize Energy Performance (up to 19 points)
- IEQ Controllability of Systems: Lighting (1 point)
- IEQ Daylight and Views: Daylight (1 point)
- Innovation in Design (up to 5 points)
- RP Credit 1 Regional Priority (up to 4 points)

ASHRAE Energy Code 90.1-2010

- Automatic Receptacle Control (8.4.2)
- Automatic Lighting Shut-off (9.4.1.1)
- Space Control (9.4.1.2)
- Automatic Daylight Controls (9.4.1.4 and 9.4.1.5)
- Additional Controls, Stairwell Lighting (9.4.1.6 g)

IECC 2012 (International Energy Conservation Code)

- Interior Lighting Controls (C405.2.1.1)
- Light Reduction Controls (C405.2.1.2)
- Occupancy Sensors (C405.2.2.2)
- Automatic Daylighting (C405.2.2.3.2)
- Multi-level Lighting Controls (C405.2.2.3.3)

ASHRAE Green Standard 189.1-2011

- Occupancy Sensor Controls with Multi-level Switching or Dimming (7.4.6.2)
- Occupancy Sensors (7.4.6.4)

IgCC Public Version 2 (International Energy Conservation Code)

- Interior Light Reduction Controls (609.3)
- Automatic Daylight Controls (609.5)
- Plug-load Controls (609.6)

CEC Title 24 2008 (California Energy Commission)

- Area Controls (131 a)
- Multi-level Lighting Controls (131 b)
- Daylight Areas (131 c)
- Shut-off Controls (131 d)

Energi TriPak™ application: Public restroom

In public spaces, such as restrooms, lights often remain on even when the space is unoccupied.

Automatic lighting control with occupancy sensing is an ideal energy-saving lighting solution.

Energy-saving strategy

Occupancy/vacancy sensing

Potential lighting energy savings:

15%



Radio Powr Savr™ ceiling-mount occupancy/vacancy sensor

communicates with
load controllers to
turn lights on or off





PowPak™ relay module with Softswitch®
switches loads in response to wireless
sensors and controls (mounted in ceiling)



Energi TriPak™ application: Private office

For a private office application, personal control of light levels is of utmost importance. Independent research indicates that occupants are up to 15% more productive when they can tailor the lighting to their needs.*

* Light Consortium. Research Study on the Effects of Lighting on Office Workers. <http://www.lightright.org.research/index.htm>

Energy-saving strategies

- Personal control
- Occupancy/vacancy sensing
- Daylight harvesting
- Appliance control

Potential lighting energy savings:

40%+



Radio Powr Savr™ daylight sensor communicates with load controllers to turn lights on or off based on amount of daylight available



PowPak™ plug-in appliance module turns phantom loads on or off in response to wireless sensors and controls (located under desk)



Radio Powr Savr ceiling-mount occupancy/vacancy sensor

communicates with load controllers to turn lights on or off based on occupancy



Maestro Wireless® switch

provides manual control and switches lighting loads in response to wireless sensors and controls



Pico® wireless control allows manual control of loads; place on tabletop or mount to wall



Maestro Wireless tabletop lamp dimmer

provides manual control and dims table lamps in response to wireless sensors and controls

Energi TriPak™ application: Classroom

A best-practice classroom combines energy efficiency with a high quality learning environment. Classroom lighting plays a particularly critical role because of the direct relationship between good lighting and student performance.*

* Phillips, R. W. (1997). Educational Facility Age and the Academic Achievement of Upper Elementary School Students. Unpublished Doctoral Dissertation. University of Georgia.

Energy-saving strategies

- Personal control
- Occupancy/vacancy sensing
- Daylight harvesting
- High-end trim

Potential lighting energy savings:

60%



PowPak™ dimming module with EcoSystem® dims lighting loads in response to wireless sensors and controls (mounted in ceiling)



Pico® wireless controls allows manual control of loads; place on tabletop or mount to wall

EcoSystem H-Series digital ballast
combines superior 1% dimming performance
and Lutron reliability



**Radio Powr Savr™
daylight sensor**
communicates with load
controllers to dim lights
based on amount
of daylight available



**PowPak contact closure
output module**
integrates with HVAC system
or other 3rd party equipment
through contact closures,
allowing the equipment to
respond to wireless commands
(mounted in ceiling)



**Radio Powr Savr
corner-mount occupancy/
vacancy sensor**
communicates with load
controllers to turn lights on
or off based on occupancy

How to design a system

Define your space

Use the following steps to plan and design an ideal energy-saving solution based on the use of the space and the needs of its occupants.

Step 1 Is occupancy/vacancy sensing required?

Select the style of the Radio Powr Savr™ occupancy/vacancy sensor based on mounting and coverage requirements **pg. 14**



Step 2 Is daylight harvesting required?

Select the Radio Powr Savr daylight sensor..... **pg. 15**



Step 3 Is control of overhead lighting required?

- a. Select the control(s) required based on style and load capacity **pgs. 16-19**
- b. Select the PowPak™ stairwell fixture for stairwell applications..... **pg. 20**



Step 4 Is control of task lighting required?

Select the style of plug-in device required **pg. 21**



Step 5 Is control of plug loads required?

Select the style of plug load controller required **pg. 22**

Step 6 Is 3rd party equipment integration required?

Select the PowPak contact closure output module **pg. 24**

Step 7 Are personal or additional points of control required?

a. Select the style of the Pico® wireless control required **pg. 25**

b. Select accessories for Pico wireless control **pg. 26**



Step 1 Occupancy/vacancy sensor selection

Radio Powr Savr™ wireless occupancy/vacancy sensors

Design statement: Specify a wireless occupancy/vacancy or vacancy-only sensor to turn lights on and/or off based on the space occupancy.



Radio Powr Savr wireless ceiling-mount occupancy/vacancy sensor dimensions

W: 3.57" (89mm)

H: 3.57" (89mm)

D: 1.3" (33mm)



Radio Powr Savr wireless wall/hall/corner-mount occupancy/vacancy sensor dimensions

W: 1.8" (46mm)

H: 4.35" (110mm)

D: 1.35" (34mm)

Features

- New ceiling-mount sensor is 20% smaller than the original version and has the ability to be recess mounted
- Lutron XCT™ signal processing technology greatly enhances the performance of PIR sensors, enabling them to "see" fine motions that other sensors could not previously detect
- Utilizes Lutron reliable Clear Connect™ RF technology to communicate wirelessly with wireless load controllers (wallbox controls, remote-mount modules, fixtures and/or plug-in devices)
- RF range: 60ft (18m) line of sight, or 30ft (9m) through walls
- Vacancy model available to meet CA Title 24 requirements
- 10-year battery life

Benefits

- Front-accessible buttons make set up easy
- Sensors have simple test modes to verify ideal locations during installation

Models

Sensors*

LRF2-OCR2B-P-WH—ceiling-mount occupancy/vacancy sensor

LRF2-OWLB-P-WH—wall-mount occupancy/vacancy sensor

LRF2-OKLB-P-WH—corner-mount occupancy/vacancy sensor

LRF2-OHLB-P-WH—hallway occupancy/vacancy sensor

Accessories

L-CMDPIRKIT—ceiling-mount sensor lens masking kit

L-CRMK-WH—ceiling-mount sensor recess-mounting bracket

WGOMNI-CPN3688—wire guard for ceiling-mount sensor

WGWS-CPN3688—wire guard for wall-mount and hallway sensors

STI-9618-CPN3688—wire guard for corner-mount sensor

* Vacancy-only models available, see page 36



Step 2 Daylight sensor selection

Radio Powr Savr wireless daylight sensor

Design statement: Specify a wireless daylight sensor to dim or switch zones of light in response to available daylight.



Radio Powr Savr wireless daylight sensor dimensions

W: 1.60" (41 mm)
H: 1.60" (41 mm)
D: 0.7" (17 mm)

Features

- Utilizes Lutron reliable Clear Connect RF technology to communicate wirelessly with wireless load controllers (wallbox controls, remote-mount modules, and/or plug-in devices); a load controller can communicate with only one daylight sensor
- RF range: 60 ft (18 m) line of sight, or 30 ft (9 m) through walls
- Features Lutron reliable proportional daylight open loop control
- Has a light range 0-107,000 Lux (0-10,000 fc) and a photopic response that matches the human eye
- Designed to give a linear response to changes in viewed light level
- One sensor is capable of switching and continuous dimming of multiple zones
- 10-year battery life

Benefits

- Simple calibration
- Multiple ceiling-mount methods available for different ceiling materials
- Front accessible test buttons make set up easy

Models

LRF2-DCRB-WH—daylight sensor



Step 3 Overhead light control selection

PowPak™ relay module

Design statement: The PowPak relay module is designed for spaces where local control is not currently available, but is required.



PowPak relay module dimensions

W: 2.89" (48 mm)

H: 3.44" (87 mm)

D: 1.25" (32 mm)

Features

- General purpose switch (all lighting loads; motor loads; receptacles)
- Receives input from up to 9 Pico® wireless controls, 6 Radio Powr Savr™ occupancy/vacancy sensors, and 1 Radio Powr Savr daylight sensor via Lutron reliable Clear Connect™ RF technology
- Model available with a dry contact closure output for integration with 3rd party equipment; contact closure output provides occupancy status
- 16A model features patented Softswitch™ technology that extends relay life to 1,000,000 cycles
- 120 V/277 V input

Benefits

- Save energy with the addition of occupancy sensing, daylight harvesting and personal control without the need for additional wires
- Button press programming to associate the module with the Radio Powr Savr sensors and Pico wireless controls

Mounting

- Mounts through a 1/2" NPT trade-size knock-out to a junction box or to a fixture. Can also be mounted inside of a standard 4" x 4" junction box

Models

RMJ-5R-DV-B—5A lighting loads (1/6HP @ 120V or 1/3HP @ 277V motor loads)

RMJ-5RCCO1-DV-B—5A lighting loads (1/6HP @ 120V or 1/3HP @ 277V motor loads) with (1) contact closure output

RMJ-16R-DV-B—16A lighting loads (1/2HP @ 120V or 1 1/2 HP @ 277V motor loads, 15A 120V receptacles)

RMJ-16RCCO1-DV-B—16A lighting loads (1/2HP @ 120V or 1 1/2HP @ 277V motor loads, 15A 120V receptacles) with (1) contact closure output



PowPak dimming module with EcoSystem®

Design statement: Specify the PowPak dimming module with EcoSystem for the application that requires dimming of fluorescent and LED fixtures and simple reconfiguration of lighting zones.



PowPak dimming module with EcoSystem dimensions

W: 2.89" (48 mm)

H: 3.44" (87 mm)

D: 1.25" (32 mm)

Features

- Controls up to 32 EcoSystem, EcoSystem H-Series or Hi-lume® 3D ballasts, or Hi-lume A-Series LED drivers*
- Receives input from up to 9 Pico wireless controls, 6 Radio Powr Savr occupancy/vacancy sensors, and 1 Radio Powr Savr daylight sensor via Lutron reliable Clear Connect RF technology
- Lutron EcoSystem technology facilitates individual ballast addressing, connection of multiple control devices, and control of ballasts individually or in groups
- 120V/277V input

Benefits

- Enables simple reconfiguration of the space, without having to move a single wire
- Dimming saves money and energy—for every percentage reduction in lighting levels, there is nearly equal reduction in the energy usage of the dimmed light source
- Additional savings can be achieved through high-end trim, occupancy sensing, daylight harvesting and personal control without the need for additional wires
- Button press programming means no commissioning required

Mounting

- Mounts through a 1/2" NPT trade-size knock-out to a junction box or to a fixture. Can also be mounted inside of a standard 4" x 4" junction box

Models

RMJ-ECO32-DV-B—controls up to 32 EcoSystem, EcoSystem H-Series or Hi-lume 3D ballasts, or Hi-lume A-Series LED drivers

* For more information on EcoSystem, EcoSystem H-Series and Hi-lume 3D ballasts, and Hi-lume A-Series LED drivers, please visit www.lutron.com.

Dimming ballasts require rapid start sockets. For more information, see Lutron App Note #122.

Lamp Socket Wiring Tester available to easily troubleshoot ballast wiring issues; see page 37 for ordering information and pricing.



Maestro Wireless® switch

Design statement: Specify a Maestro Wireless switch for applications in which a local switch already exists.



Maestro Wireless switch dimensions

W: 2.94" (75 mm)

H: 4.69" (119 mm)

D: 1.44" (38 mm)

Features

- Digital on/off tap switch
- Utilizes Lutron reliable Clear Connect™ RF technology to communicate wirelessly with up to 9 transmitting devices (Radio Powr Savr™ sensors and/or Pico® wireless controls)
- Models available to control up to 8A of lighting load
- Controls always operate locally, do not require system control
- Available in 27 finishes to complement any décor

Benefits

- Save energy with the addition of occupancy sensing and daylight harvesting without the need for additional wires
- Button press programming to associate the control with Radio Powr Savr sensors and Pico wireless controls

Mounting

- Requires a 1-gang U.S. wallbox. 3 1/2 in (89 mm) deep recommended, 2 1/4 in (57 mm) deep minimum

Models

MRF2-8S-DV-XX—8A lighting, 3A fan (1/10 HP motor, 120V only), spec grade, 120–277V~, no neutral

MRF2-6ANS-XX—6A lighting, 3 A fan (1/10 HP motor), 120 V~

MRF2-8ANS-120-XX—8 A lighting, 5.8A fan (1/4 HP motor), spec grade, 120V~

MRF2-6ANS-277-XX—6A lighting, spec grade, 277 V~

(XX in the model number represents color/finish code; please visit www.lutron.com for color choices.)



Maestro Wireless dimmer

Design statement: Select a Maestro Wireless dimmer for applications in which a local switch already exists and dimming is required.



Maestro Wireless dimmer dimensions

W: 2.94" (75 mm)

H: 4.69" (119 mm)

D: 1.44" (38 mm)

Features

- Digital dimmer with LEDs that indicate light level
- Incorporates advanced features such as fade on/fade off, long fade off, and rapid full on
- Utilizes Lutron reliable Clear Connect RF technology to communicate wirelessly with up to 9 transmitting devices (Radio Powr Savr sensors and/or Pico wireless controls)

Benefits

- Dimming saves money and energy—for every percentage reduction in lighting levels, there is nearly equal reduction in the energy usage of the dimmed light source
- Ability to set high-end trim based on customer requirements
- Button press programming to associate the control with Radio Powr Savr sensors and Pico wireless controls

Mounting

- Requires a 1-gang U.S. wallbox. 3 1/2 in (89 mm) deep recommended, 2 1/4 in (57 mm) deep minimum

Models

MRF2-600M-XX—600 W incandescent/halogen, 120 V~

MRF2-6MLV-XX—600 W/600 VA incandescent/halogen/MLV, 120 V~

MRF2-6ND-120-XX—600 W/600 VA incandescent/halogen/MLV, spec grade, neutral wire, 120 V~

MRF2-10D-120-XX—1000 W/1000 VA incandescent/halogen/MLV, spec grade, 120 V~

MRF2-F6AN-DV-XX—6 A, 3-wire fluorescent, spec grade, 120–277 V~

MRF2-6ELV-120-XX—600 W ELV, 120 V~

(XX in the model number represents color/finish code; please visit www.lutron.com for color choices.)



Step 3 Stairwell fixture selection

PowPak™ stairwell fixture

Design statement: The PowPak stairwell fixture saves energy by reducing light levels when the stairwell is occupied and lowering light levels when it is unoccupied.



NEW PowPak stairwell fixture

W: 51.125" (1299 mm)*

H: 4.375" (111 mm)

D: 3.875" (98 mm)

Features

- Incorporates an integral lighting control device and a Lutron digital dimming ballast that is programmed to occupied and unoccupied light levels specific to the project
- Occupied and unoccupied light levels are field adjustable
- Utilizes Lutron reliable Clear Connect™ RF technology to communicate wirelessly with up to 9 Radio Powr Savr™ occupancy/vacancy sensors
- Available in 2, 3, or 4 ft**, 1 or 2 lamp, and T8, T8 reduced wattage, T5HE, or T5HO lamp options
- Universal input voltage 120/277 V~
- Ceiling or wall surface mount

Benefits

- Sensor is not integral to the fixture, providing the flexibility to group multiple fixtures to a single occupancy/vacancy sensor and/or multiple occupancy/vacancy sensors to a single fixture
- Easy to install, wireless communication between devices means no additional wiring required
- Button press programming to associate fixture with Radio Powr Savr occupancy/vacancy sensors

Models***

FXSW23214HDU51—4 ft, 2 lamp, T8, field adjustable high and low end, factory preset: 50% high-end, 10% low-end, 120/277 V~

FXSW23214HDU82—4 ft, 2 lamp, T8, field adjustable high and low end, factory preset: 80% high-end, 20% low-end, 120/277 V~

* Width provided for 4 ft fixture; consult the product specification submittal for width measurements for 2 and 3 ft fixtures.

** 8 ft fixture available upon request.

*** Partial list only, for complete list of available fixtures, visit www.lutron.com/stairwellfixture.



Step 4 Task lighting control selection

Maestro Wireless® tabletop lamp dimmer and PowPak plug-in dimming module

Design statement: Both the tabletop lamp dimmer and the plug-in dimming module provide control of task lighting and the ability for remote control. Use the tabletop dimmer to provide personal lamp control. Select the plug-in module if you wish to conceal the controller.



Maestro Wireless tabletop lamp dimmer dimensions

W: 2.44" (62 mm)
H: 3.25" (83 mm)
D: 0.94" (24 mm)



PowPak plug-in dimming module dimensions

W: 2.3" (58 mm)
H: 3.3" (84 mm)
D: 1.2" (30 mm)

Features

- Digital dimmer for use with incandescent/halogen table and floor lamps up to 300W
- Configure dimming module to switch non-dimmable lighting loads
- Light levels can be fine-tuned to the desired light level
- Incorporates advanced features such as fade on/fade off, long fade off, and rapid full on
- Utilizes Lutron reliable Clear Connect RF technology to communicate wirelessly with up to 9 transmitting devices (Radio Powr Savr sensors and/or Pico® wireless controls)
- Controls always operate locally, do not require system control
- Available in white or black finish
- Dimming module available in 1- or 3-receptacle models

Benefits

- Easy to install, requires no wires or tools
- Easily incorporate task lighting into lighting solution, while saving energy through dimming
- Button press programming to associate the plug-in dimmer with the same Radio Powr Savr sensors and Pico wireless controls that control the overhead lighting

Models

MRF2-3LD-XX—300W tabletop lamp dimmer, incandescent/halogen, 120V~

MRF2-3PD-1-XX—300W plug-in dimming module, 1-receptacle, incandescent/halogen, 120V~

MRF2-3PD-3-XX—300W plug-in dimming module, 3-receptacle, incandescent/halogen, 120V~

(XX in the model number represents color/finish code; please visit www.lutron.com for color choices.)



Step 5 Plug load control selection

PowPak™ plug-in appliance module

Design statement: Specify a PowPak plug-in appliance module to directly control plug loads, such as computer monitors or printers.



PowPak plug-in appliance module dimensions

W: 2.3" (58mm)
H: 3.3" (84mm)
D: 1.2" (30mm)

Features

- Utilizes Lutron reliable Clear Connect™ RF technology to communicate wirelessly with up to 9 transmitting devices (Radio Powr Savr™ occupancy/vacancy sensors and/or Pico® wireless controls)
- Control up to 15A of general purpose load (1/2 HP motor load); no minimum load required
- Patented Softswitch® technology extends relay life to 1,000,000 cycles
- Can be hidden discretely behind furniture
- Controls always operate locally, do not require system control
- Available in white or black finish, and 1- or 3-receptacle models

Benefits

- Save energy by switching off plug loads when space is unoccupied
- Button press programming to associate the plug-in appliance module with the same Radio Powr Savr occupancy/vacancy sensors and Pico wireless controls that control the overhead lighting

Models

MRF2-15APS-1-XX—15 A plug-in appliance module, 1-receptacle, 120V~

MRF2-15APS-3-XX—15 A plug-in appliance module, 3-receptacle, 120V~

(XX in the model number represents color/finish code; please visit www.lutron.com for color choices.)



PowPak relay module with Softswitch

Design statement: Specify a PowPak relay module with Softswitch to switch receptacles, controlling plug loads which consume energy when space is not in use.



PowPak relay module with Softswitch dimensions

W: 2.89" (48 mm)

H: 3.44" (87 mm)

D: 1.25" (32 mm)

Features

- 16A general purpose switch for control of 15 A 120V receptacles
- Receives input from up to 9 Pico wireless controls, 6 Radio Powr Savr occupancy/vacancy sensors, and 1 Radio Powr Savr daylight sensor via Lutron reliable Clear Connect RF technology
- Model available with a dry contact closure output for integration with 3rd party equipment; contact closure output provides occupancy status
- Patented Softswitch technology extends relay life to 1,000,000 cycles
- 120 V/277 V input

Benefits

- Save energy by switching off power to plug loads when space is unoccupied
- Button press programming to associate the module with the Radio Powr Savr sensors and Pico wireless controls

Mounting

- Mounts through a 1/2" NPT trade-size knock-out to a junction box or to a fixture. Can also be mounted inside of a standard 4" x 4" junction box

Models

RMJ-16R-DV-B—16A general purpose switch (15 A 120V receptacles)

RMJ-16RCCO1-DV-B—16A general purpose switch (15 A 120V receptacles) with (1) contact closure output



Step 6 3rd party integration control selection

PowPak™ contact closure output module

Design statement: A PowPak contact closure output module is designed for spaces where integration with 3rd party equipment through contact closures is desired.



PowPak contact closure output module dimensions

W: 2.89" (48mm)

H: 3.44" (87mm)

D: 1.25" (32mm)

Features

- Single dry contact closure device
- Receives input from up to 9 Pico® wireless controls, 6 Radio Powr Savr™ occupancy/vacancy sensors, and 1 Radio Powr Savr daylight sensor via Lutron reliable Clear Connect™ RF technology
- Voltage: 24V AC/DC
- Maximum load of 1 A @ 24VDC or 0.5A @ 24VAC; no minimum load required
- Maintained output type

Benefits

- Button press programming to associate the module with the Radio Powr Savr sensors and Pico wireless controls

Mounting

- Screw tabs provided for surface mounting. Can also be mounted to a 1/2" NPT trade-size knock-out on a junction box

Models

RMJ-CCO1-24-B—(1) contact closure output



Step 7a Wireless control selection

Pico® wireless controls

Design statement: Use a Pico wireless control anywhere in the space to control loads with a touch of a button.



3-button
with Raise/
Lower



2-button
with Raise/
Lower



3-button



2-button

Pico wireless control dimensions

W: 1.28" (33mm)

H: 2.60" (66mm)

D: 0.33" (8mm)

Features

- Utilizes Lutron reliable Clear Connect RF technology to communicate wirelessly with wireless load controllers (wallbox controls, remote-mount modules, and/or plug-in devices)
- RF range: 100ft (18m) line of sight, or 30ft (9m) through wall
- Available in multiple button configurations with options for preset and raise/lower buttons
- 10-year battery life

Benefits

- Easily add a new and/or additional point of control without the need for new wires
- Easy configuration for use as a handheld control, car visor control, wall-mount control, or tabletop control with use of the optional pedestal

Models

Pico wireless controls

PJ-3BRL-GXX-YYY—3-button with Raise/Lower

PJ-2BRL-GXX-YYY—2-button with Raise/Lower

PJ-3B-GXX-YYY—3-button

PJ-2B-GXX-YYY—2-button

(XX in the model number represents color/finish code and YYY represents labeling options. Please visit www.lutron.com/Pico for more information.)



Lutron® Clear Connect™

Wireless Signal Sent

Step 7b Wireless control accessories selection

Pico® wireless control accessories

Design statement: Use accessories to enhance the flexibility of the Pico wireless control.



Wall-mount with Claro faceplate with Pico faceplate adapter



Wall-mount with Pico single Euro faceplate with adapter



Single and double pedestals



Features

- Pico wireless controls are designed to fit in the opening of a Claro® or Euro Pico faceplate
- Claro faceplates are available in finishes to complement the Pico wireless control
- European-style faceplates with adapters afford an architectural-style appearance and are available in both matte and metal finishes
- Tabletop pedestals are offered to support up to 4 Pico wireless controls and are available in white and black finishes

Benefits

- Pico faceplate adapter and Euro Pico faceplate with adapter allow for easy installation of the Pico wireless control in a faceplate
- Tabletop pedestals help ensure that the Pico wireless control is always within reach

Models

Wall-mount accessories

PICO-FP-ADAPT—Pico faceplate adapter for Claro faceplate

CW-1-XX—Claro 1-gang faceplate

CW-2-XX—Claro 2-gang faceplate

CW-3-XX—Claro 3-gang faceplate

CW-4-XX—Claro 4-gang faceplate

PFP-1-B-FXX-CPN5692—Single Euro Pico faceplate with adapter

PFP-2-B-FXX-CPN5692—Double Euro Pico faceplate with adapter

Tabletop accessories

L-PED1-XX—Single pedestal

L-PED2-XX—Double pedestal

L-PED3-XX—Triple pedestal

L-PED4-XX—Quadruple pedestal

(XX in the model number represents color/finish code; please visit www.lutron.com for color choices.)



Lutron® Clear Connect™


Wireless Signal Sent

How it works




Stairwell Retrofit Solution

The PowPak™ stairwell fixture communicates wirelessly with Radio Powr Savr™ occupancy/vacancy sensors. Based on the stairwell occupancy information received from the sensors, the PowPak stairwell fixture automatically adjusts the light output. The occupied and unoccupied light levels are field adjustable to meet the project's code requirements.

Unoccupied: 10% light level




Occupied: 50% light level




How it works

Variable Air Volume (VAV) integration


In response to information received from a Radio Powr Savr™ occupancy/vacancy sensor, the PowPak™ contact closure output module communicates room occupancy to the VAV terminal unit. By not heating or cooling an unoccupied room, the electricity consumed by the HVAC system can be reduced.



Radio Powr Savr
occupancy/vacancy
sensor (ceiling-mount)




PowPak contact closure
output module




Plug load control by switching receptacles


Plug loads, such as task lighting, computer monitors, and printers, account for 10–15% of commercial energy usage¹. By utilizing the PowPak relay module with Softswitch® and a Radio Powr Savr occupancy/vacancy sensor to switch receptacles, energy savings can be obtained. The occupancy/vacancy sensor communicates room occupancy wirelessly to the relay module. Based on the occupancy status received, the relay module switches the power to the receptacles on or off, reducing the amount of energy consumed.



Radio Powr Savr
occupancy/vacancy
sensor (ceiling-mount)



PowPak relay module
with Softswitch



¹ Energy Information Administration, 2003 Commercial Energy Consumption Survey, released September 2008

Alternate stand-alone solution

Maestro® occupancy/vacancy sensing dimmers and switches*

Design statement: Maestro occupancy/vacancy sensing dimmers and switches are alternate energy-saving solutions for smaller spaces with unobstructed views.



Maestro occupancy/vacancy sensing with switch

W: 2.83" (75m)
H: 4.61" (119m)
D: 1.125" (30mm)



Maestro occupancy/vacancy sensing with dimmer

W: 2.83" (75m)
H: 4.61" (119m)
D: 1.125" (30mm)

Features

- Lutron XCT™ signal processing technology greatly enhances the performance of PIR sensors, enabling them to “see” fine motions that other sensors could not previously detect
- 180° sensor field-of-view, must have unobstructed view
- Up to 30ft x 30ft major motion coverage and 20ft x 20ft minor motion coverage
- Adjustable timeout - 1, 5, 15, or 30 minutes
- High-low sensitivity adjustment
- Vacancy model available to meet CA Title 24 requirements
- Switch models feature ambient light detection
- Available in 27 colors and finishes

Benefits

- Save energy automatically with the simple addition of occupancy/vacancy sensing
- Easy to install, directly replaces an existing control with no new wiring required

Models**

Switch

MS-OPS2-XX—2A lighting, occupancy/vacancy, 120V~

MS-OPS5M-XX—5A lighting, 3A fan (1/10HP motor), occupancy/vacancy, 120V~

MS-OPS6M2-DV-XX—6A lighting, 3A fan (1/10HP motor, 120V only), occupancy/vacancy, 120-277V~

MS-OPS6M2N-DV-XX—6A lighting, 3A fan (1/10HP motor, 120V only), occupancy/vacancy, neutral wire, 120-277V~

Dimmer


MS-OP600M-XX—600W incandescent/halogen, occupancy/vacancy, 120V~

(XX in the model number represents color/finish code; please visit www.lutron.com for color choices.)


* Maestro occupancy/vacancy sensing dimmers and switches are not components of Energi TriPak™ and cannot communicate with Radio Powr Savr™ sensor or Pico® wireless controls.

** Vacancy only models available, see page 37.


Storage room—switching, 1 zone



Product key:



Maestro occupancy/vacancy sensing with switch
(mounted in 1-gang Claro® faceplate)




Switched lighting load

Sensor coverage diagrams


Ceiling-mount, 360°

Coverage varies by ceiling height

Floor view




Top view



Wall-mount*, 180°

1,500 ft²—minor motion; 3,000 ft²—major motion

Top view



Key:

- Minor motions
- Major motion

Ceiling-mount sensor coverage chart (for sensor mounted in center of room)

Ceiling height **Maximum room dimensions for complete floor coverage** **Radius of coverage at floor**

8 ft (2.4 m)	18 x 18 ft (5.5 x 5.5 m)	13 ft (4.0 m)
9 ft (2.7 m)	20 x 20 ft (6.1 x 6.1 m)	14.5 ft (4.4 m)
10 ft (3.0 m)	22 x 22 ft (6.7 x 6.7 m)	16 ft (4.9 m)
12 ft (3.7 m)**	26 x 26 ft (7.9 x 7.9 m)	19 ft (5.8 m)


* Sensor mounting shown at 7 ft (2.1 m). Mounting height should be between 6 and 8 ft (1.6 and 2.4 m).

** 12 ft (3.7 m) is the maximum mounting height allowed.

Corner-mount*, 90°

1,225 ft²—minor motion; 2,500 ft²—major motion


Top view



In-wall, 180°

400 ft² —minor motion; 900 ft²—major motion


Top view



Hallway*, long narrow field of view

Coverage varies by hallway width and length

Top view



Hallway sensor maximum recommended length chart (sensor centered within hallway)

Width of hallway

Length of hallway

6 ft (1.6 m) or less	50 ft (15.2 m)
8 ft (2.4 m)	100 ft (30.5 m)
10 ft (3.0 m) or more	150 ft (45.7 m)

* Sensor mounting shown at 7 ft (2.1 m). Mounting height should be between 6 and 8 ft (1.6 and 2.4 m).

Ordering information

Model number	Description	List Price (US)
Maestro Wireless® switches¹		
MRF2-6ANS-XX	6 A lighting, 3 A fan (1/10 HP motor), 120V~	88.00
MRF2-8ANS-120-XX	8 A lighting, 5.8 A fan (1/4 HP motor), spec grade, 120V~	120.00
MRF2-8S-DV-XX	8 A lighting, 3 A fan (1/10 HP motor, 120 V only), spec grade, 120–277 V~ , no neutral	150.00
MRF2-6ANS-277-XX	6 A lighting, spec grade, 277 V~	170.00
Maestro Wireless switch companions		
MA-AS-XX	Multi-location companion switch, 120V~	35.50
MA-AS-277-XX	Multi-location companion switch, 277V~	44.00
Maestro Wireless dimmers¹		
MRF2-600M-XX	600W incandescent/halogen, 120V~	88.00
MRF2-6MLV-XX	600 W/600 VA incandescent/halogen/MLV, 120V~	100.00
MRF2-6ND-120-XX	600 W/600 VA incandescent/halogen/MLV, spec grade, neutral wire, 120V~	130.00
MRF2-10D-120-XX	1000W/1000 VA incandescent/halogen/MLV, spec grade, 120V~	130.00
MRF2-F6AN-DV-XX	6 A lighting, 3-wire fluorescent, spec grade, 120–277 V~	180.00
MRF2-6ELV-120-XX	600W ELV, 120V~	189.00
Maestro Wireless dimmer companions		
MA-R-XX	Multi-location companion dimmer, 120V~	27.50
MA-R-277-XX	Multi-location companion dimmer, 277 V~	44.00
Maestro Wireless tabletop lamp dimmer		
MRF2-3LD-XX	300 W lamp dimmer, incandescent/halogen, 120V~	130.00
PowPak™ stairwell fixtures²		
FXSW23214HDU51	4 ft, 2 lamp, T8, field adjustable high and low end, factory preset: 50% high-end, 10% low-end, 120/277 V~	390.00
FXSW23214HDU82	4 ft, 2 lamp, T8, field adjustable high and low end, factory preset: 80% high-end, 20% low-end, 120/277 V~	390.00
PowPak™ relay module		
RMJ-5R-DV-B	5 A general purpose switch	89.00
RMJ-5RCCO1-DV-B	5 A general purpose switch with (1) contact closure output	99.00
RMJ-16R-DV-B	16 A general purpose switch	109.00
RMJ-16RCCO1-DV-B	16 A general purpose switch with (1) contact closure output	119.00

Model number	Description	List Price (US)
PowPak dimming module with EcoSystem®		
RMJ-ECO32-DV-B	Controls up to 32 EcoSystem, EcoSystem H-Series or Hi-lume® 3D ballasts, or Hi-lume A-Series LED drivers	170.00
EcoSystem H-Series ballasts³		
EHDT832MU110	T8 linear, 32 W, 1-lamp, 120-277V~, 1.0 ballast factor	79.00
EHDT832MU117	T8 linear, 32 W, 1-lamp, 120-277V~, 1.17 ballast factor	79.00
EHDT832MU210	T8 linear, 32 W, 2-lamp, 120-277V~, 1.0 ballast factor	79.00
EHDT832MU217	T8 linear, 32 W, 2-lamp, 120-277V~, 1.17 ballast factor	79.00
EHDT528MU110	T5 linear, 28 W, 1-lamp, 120-277V~, 1.0 ballast factor	89.00
EHDT528MU210	T5 linear, 28 W, 2-lamp, 120-277V~, 1.0 ballast factor	89.00
EHDT554MU110	T5HO linear, 54W, 1-lamp, 120-277V~, 1.0 ballast factor	89.00
EHDT554MU210	T5HO linear, 54W, 2-lamp, 120-277V~, 1.0 ballast factor	89.00
EHDT817MU110	T8 linear, 17 W, 1-lamp, 120-277V~, 1.0 ballast factor	89.00
EHDT817MU210	T8 linear, 17 W, 2-lamp, 120-277V~, 1.0 ballast factor	89.00
EHDT825MU110	T8 linear, 25 W, 1-lamp, 120-277V~, 1.0 ballast factor	89.00
EHDT825MU210	T8 linear, 25 W, 2-lamp, 120-277V~, 1.0 ballast factor	89.00
EHDT514MU110	T5 linear, 14 W, 1-lamp, 120-277V~, 1.0 ballast factor	89.00
EHDT514MU210	T5 linear, 14 W, 2-lamp, 120-277V~, 1.0 ballast factor	89.00
EHDT521MU110	T5 linear, 21 W, 1-lamp, 120-277V~, 1.0 ballast factor	89.00
EHDT521MU210	T5 linear, 21 W, 2-lamp, 120-277V~, 1.0 ballast factor	89.00
EHDT524MU110	T5HO linear, 24 W, 1-lamp, 120-277V~, 1.0 ballast factor	89.00
EHDT524MU210	T5HO linear, 24 W, 2-lamp, 120-277V~, 1.0 ballast factor	89.00
EHDT539MU110	T5HO linear, 39W, 1-lamp, 120-277V~, 1.0 ballast factor	89.00
EHDT539MU210	T5HO linear, 39W, 2-lamp, 120-277V~, 1.0 ballast factor	89.00
EHDT832GU310	T8 linear, 32 W, 3-lamp, 120-277V~, 1.0 ballast factor	129.00
EHDT832GU317	T8 linear, 32 W, 3-lamp, 120-277V~, 1.17 ballast factor	129.00
PowPak contact closure output module		
RMJ-CCO1-24-B	(1) contact closure output	89.00
PowPak plug-in dimming module		
MRF2-3PD-1-XX	300W, 1-receptacle, incandescent/halogen, 120V~	99.00
MRF2-3PD-3-XX	300W, 3-receptacle, incandescent/halogen, 120V~	99.00

¹ Price indicated for gloss colored products.

² Partial list only, for complete list of available fixtures visit www.lutron.com/stairwellfixture.

³ Dimming ballasts require rapid start sockets. For more information, see Lutron App Note #122.

Ordering information

Model number	Description	List Price (US)
PowPak™ plug-in appliance module		
MRF2-15APS-1-XX	15 A plug-in switch, 1-receptacle, 120V~	99.00
MRF2-15APS-3-XX	15 A plug-in switch, 3-receptacle, 120V~	99.00
Radio Powr Savr™ occupancy/vacancy sensors¹		
LRF2-OCR2B-P-WH	Ceiling-mount, 360° field of view, occupancy/vacancy sensor	85.00
LRF2-VCR2B-P-WH	Ceiling-mount, 360° field of view, vacancy-only sensor	85.00
LRF2-OWLB-P-WH	Wall-mount, 180° field of view, occupancy/vacancy sensor	85.00
LRF2-VWLB-P-WH	Wall-mount, 180° field of view, vacancy-only sensor	85.00
LRF2-OKLB-P-WH	Corner-mount, 90° field of view, occupancy/vacancy sensor	85.00
LRF2-VKLB-P-WH	Corner-mount, 90° field of view, vacancy-only sensor	85.00
LRF2-OHLB-P-WH	Hallway, occupancy/vacancy sensor	85.00
LRF2-VHLB-P-WH	Hallway, vacancy-only sensor	85.00
Simple Energy Retrofit Packages²		
MRF2-1S8A-1OC	(1) Maestro Wireless® 8 A, no neutral switch, 120/277 V~, (1) Claro® 1-gang faceplate, (1) Radio Powr Savr wireless ceiling-mount occupancy/vacancy sensor	198.00
MRF2-1S8A-1VC	(1) Maestro Wireless 8 A, no neutral switch, 120/277 V~, (1) Claro 1-gang faceplate, (1) Radio Powr Savr wireless ceiling-mount vacancy-only sensor	198.00
Radio Powr Savr occupancy/vacancy sensors accessories		
L-CMDPIRKIT	Ceiling-mount sensor lens masking kit	11.80
L-CRMK-WH	Ceiling-mount recess-mounting bracket	17.00
WGOMNI-CPN3688	Wire guard for ceiling-mount sensor, white	80.00
WGWS-CPN3688	Wire guard for wall-mount and hallway sensors, white	80.00
STI-9618-CPN3688	Wire guard for corner-mount sensor, white	80.00
Radio Powr Savr daylight sensor		
LRF2-DCRB-WH	Ceiling-mount daylight sensor	120.00
Pico® wireless controls³		
PJ-3BRL-GWH-YYY	3-button with Raise/ Lower, white only	25.00
PJ-2BRL-GWH-YYY	2-button with Raise/ Lower, white only	25.00
PJ-3B-GWH-YYY	3-button, white only	25.00
PJ-2B-GWH-YYY	2-button, white only	25.00
PJ-3BRL-GXX-YYY	3-button with Raise/ Lower	56.00
PJ-2BRL-GXX-YYY	2-button with Raise/ Lower	56.00
PJ-3B-GXX-YYY	3-button	56.00
PJ-2B-GXX-YYY	2-button	56.00

Model number	Description	List Price (US)
Pico accessories		
L-PED1-XX	Pico wireless control single pedestal	60.00
L-PED2-XX	Pico wireless control double pedestal	80.00
L-PED3-XX	Pico wireless control triple pedestal	100.00
L-PED4-XX	Pico wireless control quadruple pedestal	120.00
PICO-FP-ADAPT	Pico wireless control faceplate adapter	8.00
PFP-1-B-FXX-CPN5692 ⁴	Single Euro Pico faceplate with adapter	40.00
PFP-2-B-FXX-CPN5692 ⁴	Double Euro Pico faceplate with adapter	44.00
Lamp Socket Wiring Tester		
FDB-LSWT-T5/T8	600V, 100KHz, 0.125A max, CAT III	180.00
Maestro® occupancy/vacancy sensing switches⁵		
MS-OPS2-XX	2 A lighting, occupancy/vacancy sensing switch, 120 V~	29.00
MS-VPS2-XX	2 A lighting, vacancy-only sensing switch, 120 V~	29.00
MS-OPS5M-XX	5 A lighting, 3 A fan (1/10HP motor), occupancy/vacancy sensing switch, 120V~	41.00
MS-VPS5M-XX	5 A lighting, 3 A fan (1/10HP motor), vacancy-only sensing switch, 120V~	41.00
MS-OPS6M2-DV-XX	6 A lighting, 3 A fan (1/10HP motor, 120V only), occupancy/vacancy sensing switch, 120-277V~	49.00
MS-VPS6M2-DV-XX	6 A lighting, 3 A fan (1/10HP motor, 120V only), vacancy-only sensing switch, 120-277V~	49.00
MS-OPS6M2N-DV-XX	6 A lighting, 3 A fan (1/10HP motor, 120V only), occupancy/vacancy sensing switch, neutral wire, 120-277V~	49.00
MS-VPS6M2N-DV-XX	6 A lighting, 3 A fan (1/10HP motor, 120V only), vacancy-only sensor, neutral wire, 120-277V~	49.00
Maestro occupancy/vacancy sensing switch companions		
MA-AS-XX	Multi-location companion switch, 120V~	35.50
MA-AS-277-XX	Multi-location companion switch, 277V~	44.00
Maestro occupancy/vacancy sensing dimmers⁵		
MS-OP600M-XX	600W incandescent/halogen, vacancy/vacancy sensing dimmer, 120V~	54.00
MS-VP600M-XX	600W incandescent/halogen, vacancy-only sensing dimmer, 120V~	54.00
Maestro occupancy/vacancy sensing dimmer companions		
MA-R-XX	Multi-location companion dimmer, 120V~	27.50
Faceplates		
CW-1-XX	Claro® 1-gang faceplate	4.90
CW-2-XX	Claro 2-gang faceplate	9.80
CW-3-XX	Claro 3-gang faceplate	15.00
CW-4-XX	Claro 4-gang faceplate	20.00

¹ Vacancy models meet California Title 24 section 119(j) requirements.

² Available in white finish only.

³ Price indicated for light or power text or icon labeling only.

⁴ Price indicated for Artic White and Midnight finishes only, contact Lutron for additional finish options and pricing.

⁵ Price indicated for gloss finish only.



Sources

- 1 Energy Information Administration, 2003 Commercial Buildings Energy Consumption Survey, released April 2009. (www.eia.doe.gov/emeu/cbeecs/cbeecs2003/lighting/lighting1.html)
- 2 Determinants of Lighting Quality II by Newsham, G. and Vetch, J., 1996.
- 3 Light Right Consortium. Research Study on the Effects of Lighting on Office Workers. <http://www.lightright.org.research/index.htm>
- 4 Heschong Mohone Group for the California Energy Commission. Windows and Offices: a study of Office Worker Performance and the Indoor Environment. October 2003.

www.lutron.com

World Headquarters 1.610.282.3800

Technical Support Center 1.800.523.9466 (Available 24/7)

Customer Service/Quotes 1.888.LUTRON1 (1.888.588.7661)

© 04/2012 Lutron Electronics Co., Inc.

P/N 367-2110 REV C

